



Description: Pre-set thermostats to manage temperature in panels. Sensor element thermostatic bimetal. Red one (EFR202) with a normally closed contact for regulating heaters. Blue one (EFR201) with a normally opened contact for regulating cooling devices or signal devices. Mounting clip for 35 mm DIN rail (EN 60715).

Material: Plastic according to UL94 V-0.

Switch capacity: 250V AC, 5 (1.6) A. 120 V AC, 10 (2) A. 24 V DC, 30 W. Value in brackets for inductive load. Max. starting current of 16 A (AC) for 10 seconds.

Operating temperature: -40 °C to +80 °C.

Service life: > 100,000 cycles.

Connection: 2 pole terminal for 2.5 mm², torque 0.8 Nm max.

Protection: IP 20.

Approvals: CE, EAC, cULus_UL Listed.

Finish: Light grey.

Pack quantity: 1 piece.

| Description | Switch on temperature (°C) | Switch off temperature (°C) | Item no. |
|-------------------------|----------------------------|-----------------------------|----------|
| Normally opened contact | +35 | +25 | EFR201 |
| Normally closed contact | +5 | +15 | EFR202 |