



WINTER SAFETY PRODUCT CHART

PLUMBING CHANNEL

SELECT THE RIGHT PRODUCTS		AREA		APPLICATION					ACCESSORIES											CONTROLLERS AND SENSORS																										
		DRY 	WET 	PIPE  Up to 2" diameter	PIPE  Up to 2 1/2" diameter	PIPE  Up to 6" diameter	ROOF  Up to 4" gutter with 1 run Up to 6" gutter with 2 runs	SURFACE SNOW MELT 	9800-FLEXFIT PLUG	9610 APPLICATION TAPE	H900 - POWER CONNECTION	H903 - APPLICATION TAPE	H908 - PLUG-IN CORD W/ GFI	H910 - SPLICE & TEE	H912 - GEL-FILLED END SEAL	H913 - ROOF CLIPS (10)	H914 - ROOF CLIPS (50)	H915 - DOWNSPOUT HANGER	EMK FITTINGS	PIPE**	PIPE**	PIPE**	PIPE**	R&G, SM	R&G, SM	R&G, SM	R&G, SM	R&G	SM																	
																				TC-3 • Ambient sensing. • Fixed 35°F set point • 15 Amp	AMC-F5 • Ambient or line sensing • Fixed set point 40°F 22 A at 125/ 250/ 480 V	AMC-1A • Ambient sensing • Adjustable set point 15°F to 140°F • 22 A at 125/ 250/480 V	EC-TS • Ambient sensing. • Adjustable set point 30°F to 110°F • 30 A at 100 - 277 V	LCD-8 • Snow Switch; operates heaters at temperatures below 38°F • 16 A @ 100 - 240 V	PD-PRO • Snow and ice controller • Single circuit; 120 V • Works with up to 2 sensors	GF-PRO • Snow and ice controller • Single circuit; 30 mA GFEP • Works with up to 2 sensors	SNOW OWL • Aerial snow sensor	GIT-1 • Gutter sensor	SIT-6E • Pavement sensor																	
WINTERGARD <table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>100' TruckPak*</td><td>H311100</td></tr><tr><td>250' Reel</td><td>H311250</td></tr></table> 		Description	Catalog #	100' TruckPak*	H311100	250' Reel	H311250	•	—	•	—	—	—	—	—	•	•	•	•	•	—	—	—		—	• w H900	• w H900	• w H900	—	—	—	—	—	—												
Description	Catalog #																																													
100' TruckPak*	H311100																																													
250' Reel	H311250																																													
WINTERGARD PLUS <table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>50' Box</td><td>H611050</td></tr><tr><td>100' TruckPak*</td><td>H611100</td></tr><tr><td>250' Reel</td><td>H611250</td></tr></table> 		Description	Catalog #	50' Box	H611050	100' TruckPak*	H611100	250' Reel	H611250	•	—	•	•	•	—	—	—	•	•	•	•	•	—	—	—		—	• w H900	• w H900	• w H900	—	—	—	—	—	—										
Description	Catalog #																																													
50' Box	H611050																																													
100' TruckPak*	H611100																																													
250' Reel	H611250																																													
<table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>50' Box</td><td>H621050</td></tr><tr><td>100' TruckPak*</td><td>H621100</td></tr><tr><td>250' Reel</td><td>H621250</td></tr></table> 		Description	Catalog #	50' Box	H621050	100' TruckPak*	H621100	250' Reel	H621250	•	—	•	•	•	—	—	—	•	•	—	•	•	—	—	—		—	• w H900	• w H900	• w H900	—	—	—	—	—	—										
Description	Catalog #																																													
50' Box	H621050																																													
100' TruckPak*	H621100																																													
250' Reel	H621250																																													
WINTERGARD WET <table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>50' Box</td><td>H612050</td></tr><tr><td>100' TruckPak*</td><td>H612100</td></tr><tr><td>250' Reel</td><td>H612250</td></tr><tr><td>500' Reel</td><td>H612500</td></tr><tr><td>1000' Reel</td><td>H6121000</td></tr></table> 		Description	Catalog #	50' Box	H612050	100' TruckPak*	H612100	250' Reel	H612250	500' Reel	H612500	1000' Reel	H6121000	•	•	•	•	•	•	—	—	•	•	•	•	•	•	•	•		—	• w H900	• w H900	• w H900	• w H900	• w H900	• w H900	• w H900	•	•	—					
Description	Catalog #																																													
50' Box	H612050																																													
100' TruckPak*	H612100																																													
250' Reel	H612250																																													
500' Reel	H612500																																													
1000' Reel	H6121000																																													
<table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>50' Box</td><td>H622050</td></tr><tr><td>100' TruckPak*</td><td>H622100</td></tr><tr><td>250' Reel</td><td>H622250</td></tr><tr><td>500' Reel</td><td>H622500</td></tr><tr><td>1000' Reel</td><td>H6221000</td></tr></table> 		Description	Catalog #	50' Box	H622050	100' TruckPak*	H622100	250' Reel	H622250	500' Reel	H622500	1000' Reel	H6221000	•	•	•	•	•	•	—	—	•	•	—	•	•	•	•	•		—	• w H900	• w H900	• w H900	• w H900	• w H900	• w H900	• w H900	•	•	—					
Description	Catalog #																																													
50' Box	H622050																																													
100' TruckPak*	H622100																																													
250' Reel	H622250																																													
500' Reel	H622500																																													
1000' Reel	H6221000																																													
FROSTGUARD PREASSEMBLED <table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>6' Length</td><td>FG1-6P</td></tr><tr><td>12' Length</td><td>FG1-12P</td></tr><tr><td>18' Length</td><td>FG1-18P</td></tr><tr><td>24' Length</td><td>FG1-24P</td></tr><tr><td>36' Length</td><td>FG1-36P</td></tr><tr><td>50' Length</td><td>FG1-50P</td></tr><tr><td>75' Length</td><td>FG1-75P</td></tr><tr><td>100' Length</td><td>FG1-100P</td></tr></table> 		Description	Catalog #	6' Length	FG1-6P	12' Length	FG1-12P	18' Length	FG1-18P	24' Length	FG1-24P	36' Length	FG1-36P	50' Length	FG1-50P	75' Length	FG1-75P	100' Length	FG1-100P	•	•	•	•	—	•	—	—	—	—	•	—	—	•	•	•		•	—	—	—	—	—	—	—	—	—
Description	Catalog #																																													
6' Length	FG1-6P																																													
12' Length	FG1-12P																																													
18' Length	FG1-18P																																													
24' Length	FG1-24P																																													
36' Length	FG1-36P																																													
50' Length	FG1-50P																																													
75' Length	FG1-75P																																													
100' Length	FG1-100P																																													
<table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>6' Length</td><td>FG2-6L</td></tr><tr><td>12' Length</td><td>FG2-12L</td></tr><tr><td>18' Length</td><td>FG2-18L</td></tr><tr><td>24' Length</td><td>FG2-24L</td></tr></table> 		Description	Catalog #	6' Length	FG2-6L	12' Length	FG2-12L	18' Length	FG2-18L	24' Length	FG2-24L	•	•	•	•	—	—	—	—	—	—	•	—	—	—	—	—		—	•	•	•	—	—	—	—	—	—								
Description	Catalog #																																													
6' Length	FG2-6L																																													
12' Length	FG2-12L																																													
18' Length	FG2-18L																																													
24' Length	FG2-24L																																													
FROSTEX <table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>50' TruckPak</td><td>5050</td></tr><tr><td>100' Reel</td><td>2102</td></tr><tr><td>250' Reel</td><td>2250</td></tr><tr><td>500' Reel</td><td>2502</td></tr></table> 		Description	Catalog #	50' TruckPak	5050	100' Reel	2102	250' Reel	2250	500' Reel	2502	•	—	•	—	—	—	—	•	•	—	—	—	—	—	—	—		•	—	—	—	—	—	—	—	—	—								
Description	Catalog #																																													
50' TruckPak	5050																																													
100' Reel	2102																																													
250' Reel	2250																																													
500' Reel	2502																																													
IN-PIPE <table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>Mini 14' - 34'</td><td>see price list</td></tr><tr><td>Miser 14' - 240'</td><td>see price list</td></tr><tr><td>Retro 40' - 150'</td><td>see price list</td></tr></table> 		Description	Catalog #	Mini 14' - 34'	see price list	Miser 14' - 240'	see price list	Retro 40' - 150'	see price list	•	•	•	—	—	—	—	—	—	—	—	—	—	—	—	—		—	—	—	—	—	—	—	—	—	—										
Description	Catalog #																																													
Mini 14' - 34'	see price list																																													
Miser 14' - 240'	see price list																																													
Retro 40' - 150'	see price list																																													
<table><tr><th>Description</th><th>Catalog #</th></tr><tr><td>Retro 160' - 250'</td><td>see price list</td></tr></table> 		Description	Catalog #	Retro 160' - 250'	see price list	•	•	•	—	—	—	—	—	—	—	—	—	—	—	—	—		—	—	—	—	—	—	—	—	—	—														
Description	Catalog #																																													
Retro 160' - 250'	see price list																																													
ELECTROMELT See price list for the multitude of SKUs depending upon project needs 		—	•	—	—	—	—	•	—	—	—	—	—	—	—	—	•	—	—	—	•	•	•	•	•	—	•																			
MI See price list for the multitude of SKUs depending upon project needs 		—	•	—	—	—	—	•	—	—	—	—	—	—	—	—	—	—	—	—	•	•	•	•	•	—	•																			

*WinterGard TruckPaks contains 100 feet of heating cable, two H900 Hardwire Power Connection Kits, one H910 Splice or Tee Kit, and one H903 roll of Application Tape.
**Although these can work with Roof & Gutter applications, they are ambient-sensing only. The PD-Pro & GF-Pro are more ideal because they work with snow and gutter sensors.

Pipe - Pipe Freeze Protection; R&G = Roof & Gutter De-Icing; SM = Surface Snow Melting.

All nVent trademarks and logos are owned by nVent or its global affiliates. nVent reserves the right to change specifications without prior notice.
© 2020 nVent. RAYCHEM-AR-H59945-WSProductChartPlumbing-EN-2010
TEL: 1.800.545.6258