

EL1200MS

LED Enclosure light with socket and movement sensor



Operating voltage	100V-240V~, 50/60 Hz
Width	364
Socket type	Type F (Shucko)

Description: LED enclosure light specially designed for nVent HOFFMAN enclosures. Fast and tool-free assembly thanks to a latching hook system designed to fit the 25mm hole pattern on nVent HOFFMAN enclosures. May be fitted horizontally or vertically.

Lamp type: LED.

Luminosity: 1200 lm.

Light colour: 4000 K (neutral white).

Power consumption: 12 W

Operating voltage: 100 V - 240 V ~, 50/60 Hz

Connection: Infeed, 3-pole. Through wiring, 3-pole.

Operating temperature: -20 °C ... +55 °C

Protection: IP20

Follow-up time of the motion detector: 120 s

Dimensions: 364 × 76 × 48 mm.

LED light specially designed for nVent HOFFMAN enclosures. Equipped with a socket and a motion sensor. Tool-free assembly reduces the assembly time. Simple through wiring based on a plug and play system. Suitable for global use with a voltage range of 100-240V.

IP20