



SUBJECT: nVent LENTON Supplementary  
Installation Instructions

**IP8648      REV A**  
DATE: 20-DEC-2022  
PAGE 1 of 2  
PRODUCT: Taper-threaded  
couplers and  
Terminators

REFERENCE: CA-20247516

## 1. SCOPE

For the North America Region ONLY, the “*SNUG tight Installation Instruction Addendum 1*” (as defined in Section 2) may be applied to the product families listed in Table 1.

## 2. SNUG Tight Installation Instruction Addendum 1

Snug Tight installation (>5 ft-lb) may be used with ASTM A615 or A706 Grade 60 rebar (sizes #4 - #11) for commercial projects when splice performance requirements are limited to ACI 318 Type 1 (125% Specified Yield) or Type 2 (Specified Ultimate). Additional steps may be necessary to secure product for transportation and handling.

**Table 1**

<b>Product Family</b>	<b>Corresponding Installation Instructions</b>
Standard Couplers A2	PDF057
Position Couplers P9	PDF051
Terminators D6, D14	PDF097
Parallel Bolt Couplers S4, S5	PDF096
Weldable Couplers C2/C3J	PDF106
Form Saver Couplers SA	PDF084
Interlok Grout Filled Couplers LK	PDF008, IP8300, IP8419



SUBJECT: nVent LENTON Supplementary  
Installation Instructions

**IP8648    REV A**  
DATE: 20-DEC-2022  
PAGE 2 of 2  
PRODUCT: Taper-threaded  
couplers and  
Terminators

REFERENCE: CA-20247516

A	20/DEC/22	ALM	SPB	KMD	---	CA-20247516