

TLCL89005

Compact design LED light



This energy efficient LED enclosure light can be mounted in many different ways, as well as directly on 19" profiles, in any enclosure, and helps when maintenance is performed in the field.

CE EAC

IP 20

Finish	Black (RAL 9005)
Operating voltage	220-240 V AC, 50/60 Hz
Item no.	TLCL89005

Description: Lighting system with a compact design, suitable for all types of enclosures or racks. It has three possible fixing possibilities: magnetically, screw mounting with a variable distance between holes and/or snap-into 19" rack. This lamp has a very long service life (around 50000 h.) due to the use of LED technology. The body of the lighting system is made of PC-ABS. An integrated connector allows the activation of the lamp by a door switch by using the TLCS product without performing any additional wiring. The led-tube is made of PC and the colour of the light is white.

Lamp type: High Power LEDs.

Luminosity: 945 Lm.

Power consumption: 7.2 W.

Operating temperature: -20 °C to +50 °C.

Dimensions: 448 x 54.5 x 26 mm.

Connections: 2x0.75 mm² open end cable (1.5 m long), 2x0.75 mm² mini-connector for door switch use.

Approvals: CE, EAC.

Delivery: 1 light with fix mounted connection cable, integrated magnets and mounting screws.