
JBS-100-ECP-A



COMBINATION POWER CONNECTION BOX AND DIGITAL ELECTRONIC CONTROLLER FOR NONHAZARDOUS LOCATIONS



PRODUCT OVERVIEW

The nVent RAYCHEM JBS-100-ECP-A is a power connection/ electronic controller combination for nVent RAYCHEM polymeric and MI cables. Utilizing the features of the RAYCHEM JBS-100-A single-entry power connection with junction box, along with an indicating electronic controller, this assembly allows for local control of a heating circuit.

The assembly includes a window and a digital display that shows the monitored actual/set point temperatures and alarm conditions (RTD failure, high or low temperature) if detected. Alarm conditions can be remotely indicated via a form C dry contact. Status LEDs indicate whether the digital display is showing the set point or actual temperature.

Programming the set point temperature, deadband, and high and low alarm thresholds on the JBS-100-ECP-A is accomplished using the built-in digital display and push buttons.

The JBS-100-ECP-A is programmable to maintain temperatures of 425°F (218°C), can be used with voltages from 100 to 277 Vac, and is capable of switching current up to 30 Amps.

A 100-ohm platinum RTD provides feedback for either pipe maintenance or ambient sensing for freeze protection

The power connection/electronic controller combination significantly reduces installation cost. Eliminating wiring and devices to connect separate power connections and thermostats/controllers not only reduces material cost, but also leads to significant labor savings when combined with the cold-applied core sealer and spring clamp terminals characteristic of the JBS-100 line of power connection kits.

The kit contains all the necessary materials for a complete installation except one pipe strap, which must be ordered separately. For connection to a RAYCHEM MI cable, a grounding kit is required (ordered separately).

GENERAL

Heating cable compatibility

Approvals

Supply voltage

nVent RAYCHEM BTV-CR, XL-Trace, BTV-CT, QTVR-CT, XTV-CT, KTV and VPL-CT RAYCHEM Design A & D MI cables (requires MI cable grounding kit – ordered separately)

Nonhazardous locations



100-277 Vac ±10% 50-60 Hz Common supply for controller and heat-tracing circuit

Raychem-DS-H57462-JBS100ECPA-EN-1805 nVent.com | 1

ENCLOSURE

Protection TYPE 4X

Material Fiberglass reinforced polyester plastic

Entries 1 x 3/4 in (19 mm) conduit entries for power

1 x 1/2 in (13 mm) conduit entry (with plug) for MI cable entry or alarm wiring

Relative humidity 0% to 90%, noncondensing Ambient installation and usage temperature -40°F to 140°F (-40°C to 60°C)

Maximum pipe temperature Intermittent 482°F (250°C), continuous 425°F (218°C)

CONTROL

Relay type Double-pole, mechanical

Control range 32°F to 425°F (0°C to 218°C)

Deadband Adjustable 2°F to 10°F (2°C to 10°C)


Accuracy $\pm 3^{\circ}F$ (1.7°C) of set point

INPUT POWER

Voltage 277 Vac nominal, 50/60 Hz maximum

Current 30 A maximum
Circuit breaker rating 40 A maximum

ENCLOSURE



MONITORING AND ALARM OUTPUT

Temperature Low alarm range: 20°F–420°F (-6°C–216°C) from set point, or OFF

High alarm range: 38°F-482°F (3°C-250°C) from set point, or OFF

RTD failure Shorted or open RTD sensor

Alarm relay Form C: 2 A at 277 Vac, 2 A at 48 Vdc

Normally energized; changes state upon an alarm

Voltage Alarm relay changes state upon loss of voltage to the controller

RTD TEMPERATURE SENSOR

Sensor sheath 316 stainless-steel housing, 4 in (100 mm) length, 0.25 in (6 mm) outer diameter

Material Platinum 100 ohms at 0° C $\alpha = 0.00385$ ohms/ohm/ $^{\circ}$ C

Leads 24 AWG stranded, Teflon PFA insulated

Raychem-DS-H57462-JBS100ECPA-EN-1805 nVent.com | 2

RTD TEMPERATURE SENSOR

Lead length 10 ft (3 m)

Exposure temperature Minimum: -40°F (-40°C)

Maximum: Intermittent 482°F (250°C), continuous 425°F (218°C)

Accuracy $\pm 1^{\circ}F (0.5^{\circ}C)$ at $32^{\circ}F (0^{\circ}C)$

PROGRAMMING AND SETTING

Method Programmable at controller – Set/Up/Down push buttons on front panel

Units °F or °C

Digital display Four numeric display digits for parameter and error/alarm indication

LEDs Indicate actual and set point from display

Memory Nonvolatile, restored after power loss

Stored parameters Parameters can be programmed without power supply (external battery) and

parameters are stored in nonvolatile memory.

Alarm conditions Low/high temperature and RTD failure (open or shorted)

CONNECTION TERMINALS

Power supply input

Screw rising cage clamp, 18–6 AWG

Heating cable output

Screw rising cage clamp, 18–6 AWG

Ground

Screw rising cage clamp, 18–6 AWG

Screw rising cage clamp, 22–14 AWG

Alarm

Screw rising cage clamp, 22–14 AWG

ORDERING DETAILS

JBS-100-ECP-A

Description	Catalog number	Part number	Weight/lbs
Power connection kit with junction box and digital electronic controller	JBS-100-ECP-A	P000000180	5.0
Spare Parts and Accessories			
MI cable grounding kit (required if installing MI heating cable)	MI-GROUND-KIT	P000000279	0.2
Replacement controller unit	JBS-100-EC	P000000217	1.0
Replacement RTD and stand assembly	JBS-RTD-Replace	P000000341	0.8

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

hem-DS-H57462-JBS100ECPA-EN-1805