
MIJB-1086-A



MI POWER JUNCTION BOX JUNCTION BOX WITH PRE-DRILLED EARTHING PLATE FOR USE WITH MI HEATING UNITS



PRODUCT OVERVIEW

The efficient design and simple construction of these enclosures make them durable in corrosive environments, yet aesthetically pleasing.

Corner latches provide unobstructed access.

The continuous hinge pin provides a secure seal and double latching creates added security.

Typical uses include power, splice and end box for 3-phase system. It accommodates up to three power cables:

- · One power cable in and up to three MI cables out
- One power cable in, one power cable out and two MI cables out
- Two D or E design MI cables in and two D or E design MI cables out (splice box)
- Three B design MI cables in and three B design MI cables out (splice box)

THOIT VII

CONSTRUCTION

- Compression molded fibreglass has outstanding chemical and temperature resistance qualities and exhibits excellent weatherability and physical properties
- · Light gray finish inside and out. Gasket assures water-tight and dust-tight seal
- Polyester mounting tabs and stainless steel attachment screws are provided with each enclosure
- Two corrosion resistant polyester quick release latches are located in corners to provide unobstructed access to enclosure
- · Removable hinged cover attached to body with stainless steel hinge pin
- $\bullet \ \ \text{Hinge pin and bail are corrosion resistant Type 316 stainless steel. Padlock provisions included in each latch}$
- Inside dimensions: 10" high x 8" wide x 6" deep (250 x 200 x 150 mm)
- Box includes earthing plate on three sides and back of box and is pre-punched for eleven ½" and eight ¾" hubs
- Entries: Up to 11 x ½" and 8 x ¾" Use a step bit to drill out or enlarge any holes in fibreglass required for hubs/connectors

CSA approved Type 4X enclosure and certified electrical assembly

Area classification - Hazardous locations CL I Division 2 (Zone 2), Groups A,B,C,D T5


Enclosure type: Type 4X

Ambient temperature rating: -50°C to +40°C

Enclosure flammability evaluated per UL 508A



ELECTRICAL SPECIFICATIONS



Maximum operating voltage 600Vac

Maximum 65A per terminal, rated 18AWG to 6AWG


Order a separate MIJB-LPWR-KIT for #2 or #4AWG power cable to downsize to #6AWG

Consider MI cold lead cable gland size, hub size and power cable size in selecting appropriate box


Power cable gland and hubs for MI cold lead glands not included

TYPICAL ELECTRICAL CONNECTION OPTIONS

MIJB-1086-A-PARALLEL




- USE WITH A, E OR D DESIGN MI CABLES. POWER WIRES TO BE FIELD ROUTED FROM
- MARSHALLING BOX TO INDIVIDUAL EHT POWER BOXES (I.E. MIJB-864-A-PWR,JBS, ETC...).




- USE WITH A, E OR D DESIGN MI CABLES.

MIJB-1086-A-SERIES




- FIELD TO REMOVE ONE 2-POLE JUMPER AS SHOWN. USE WITH A, E OR D DESIGN MI CABLES.



-FIELD TO REMOVE TWO 2-POLE JUMPERS AS SHOWN. -USE WITH A, E OR D DESIGN MI CABLES.


POWER CABLE DOWNSIZING OPTION:

MIJB-1086-A-3PWR




- FIELD TO REMOVE TWO 2-POLE JUMPERS AS SHOWN.
- USE WITH B DESIGN MI CABLES.
- USE A MIJB-864-A-STAR TO TERMINATE OR AN MIJB-864-A-SPLC TO CONTINUE THE 3-PHASE HEATER CABLE.

MIJB-LPWR-KIT



- USED TO DOWNSIZE #2 OR #4 AWG POWER CABLES.
- ORDER MIJB-LPWR-KIT SEPARATELY IF REQUIRED.
 CONSISTS OF 3 POWER TERMINAL BLOCKS, 1 GROUND
- TERMINAL BLOCK, AND #6 AWG JUMPER WIRES.

ENCLOSURE DETAIL



- Junction boxes can be mounted using holes in back and screws provided, or using four mounting tabs supplied
- Hinge can be moved to other side of box by rotating earthing plate 180°
- Earthing plate is fabricated from galvanized steel and is bonded to internal PE terminal block for bonding of hubs and connectors
- No bonding wires are required between the hubs, connectors and PE terminal blocks.


GENERAL

Lamacoids are not included.


Two mounting brackets (MBRP-B) and two pipe straps or alternate mounting method must be ordered separately for installation.

ENCLOSURE MOUNTING BRACKET

○ %" HOLE FOR ½" CONDUIT HUB/CONNECTOR




BOTTOM MOUNT



MBRP-B Product Overview

- Mounting bracket for MIJB series fiberglass enclosures which enables enclosure installation and connection prior to application of insulation and cladding
- Installation time reduction as electrician does not need to return after cladding is installed
- 304SS Stainless steel pipe support bracket for MIJB-864-A, nVent RAYCHEM MIJB-1086-A and MIJB-1086-B fiberglass enclosures
- Two brackets are required to support each enclosure. Each bracket requires one pipe strap
- Suitable for pipe temperatures up to 900°F (480°C)
- Stainless steel is a poor conductor of heat so the bracket is not hot or a heat sink



ORDERING DETAILS

Description	Catalog number	Part number	Weight/lbs
Enclosure	MIJB-1086-A	T0002053	8.00lbs
Spare Parts and Accessories			
Mounting Bracket for MIJB series fiberglass enclosures	MBRP-B	T0002003	1.1lbs
Terminal kit for MIJB-1086 model	MIJB-LPWR-KIT	T1005000	0.5lbs

Raychem-DS-H59615-MIJB1086A-EN-1809 nVent.com | 3

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

nVent.com