

# Ultimate Position Splice MT02 and PM09



**LENTON**

**CONNECT AND PROTECT**



## MT02 MALE TAPER STUD



Material: Steel | Finish: Plain

## FEATURES

- Installs quickly and easily
- Utilizes the standard nVent LENTON taper profile
- Designed to splice two curved, bent or straight bars, when neither bar can be rotated and where the ongoing bar is free to move in its axial direction
- No special tools or skills required
- Generous axial adjustability

## PM09 FEMALE POSITION ASSEMBLY





Material: Steel | Finish: Plain

Part Number	Hex Width W	Dia-meter Ø	Length L	Bar Depth BD	Unit Weight	Rebar Size Metric	Part Number	Hex Width W	Hex Dia-meter 1 Ø1	Hex Dia-meter 2 Ø2	Coupler Body CB	Length L	Bar Depth BD	Unit Weight
LU16MT02	27 mm	-	58 mm	39 mm	0.16 kg	16 mm	LU16PM09	27 mm	-	35 mm	95 mm	156 mm Max	39 mm	0.82 kg
LU20MT02	30 mm	-	67 mm	44 mm	0.28 kg	20 mm	LU20PM09	30 mm	-	40 mm	109 mm	180 mm Max	44 mm	1.12 kg
LU25MT02	-	35 mm	78 mm	49 mm	0.49 kg	25 mm	LU25PM09	-	35 mm	50 mm	116 mm	187 mm Max	49 mm	1.89 kg
LU32MT02	-	45 mm	95 mm	61 mm	0.93 kg	32 mm	LU32PM09	-	45 mm	60 mm	136 mm	223 mm Max	61 mm	3.93 kg
LU40TMT02	-	60 mm	118 mm	77 mm	1.89 kg	40 mm	LU40TPM09	-	60 mm	75 mm	162 mm	263 mm Max	77 mm	6.24 kg

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

PM09 Female Position Assembly is comprised of MS09 Male Parallel Stud, PT09 Parallel to Taper Coupler and NS09 Locking Nut.

**Designed to Meet:** AASHTO; ABNT NBR 8548:1984; ACI 318 Type 1 (125% Specified Yield); ACI 318 Type 2 (Specified Tensile); ACI 349; ACI 359; AS3600; BS EN 1992-1-1; BS EN 1992-2; CAN/CSA - N287.2/.3/.4; DIN EN 1992-1-1; Eurocode 2; IBC Type 1 (125% Specified Yield); IBC Type 2 (Specified Tensile); ISO 15835; NEN EN 1992-1-1; NF A 35-020-1; NF EN 1992-1-1; ÖNORM EN 1992-1-1; Sellafield Ltd. Std. ES\_0\_3110; US Army Corps of Engineers; CAN/CSA - A23.3



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**