

# EL900DS

LED Enclosure light with socket



An LED light specially designed for nVent HOFFMAN enclosures. Equipped with a socket. Tool-free assembly reduces the assembly time. Simple through wiring based on a plug and play system. Suitable for global use with a voltage range of 100-240V.



IP20

Socket type	Type F (Shucko)
Operating voltage	100 V - 240 V ~, 50/60 Hz
Width	364

**Description:** LED enclosure light specially designed for nVent HOFFMAN enclosures. Fast and tool-free assembly thanks to a latching hook system designed to fit the 25mm hole pattern on nVent HOFFMAN enclosures. May be fitted horizontally or vertically.

**Lamp type:** LED.

**Luminosity:** 900 lm.

**Light colour:** 4000 K (neutral white).

**Power consumption:** 9 W

**Operating voltage:** 100 V - 240 V ~, 50/60 Hz

**Connection:** Infeed, 3-pole. Through wiring, 3-pole.

**Operating temperature:** -20 °C ... +55 °C

**Protection:** IP20

**Dimensions:** 364 × 76 × 48