

Ultimate Position Splice MT12 and PM15



LENTON

CONNECT AND PROTECT



MT12 MALE TAPER STUD



Material: Steel | Finish: Plain

Part Number	Hex Width W	Diameter Ø	Length L	Bar Depth BD	Unit Weight	Rebar Size, US
LU25MT12D	1.19"	—	2.80"	1.73"	0.6 lb	#8
LU28MT12D	—	1.38"	2.88"	1.82"	0.8 lb	#9
LU32MT12D	—	1.50"	3.21"	1.95"	1.2 lb	#10
LU36MT12D	—	1.75"	3.47"	2.21"	1.6 lb	#11
LU43TMT12D	—	2.00"	4.48"	2.90"	2.8 lb	#14
LU57TMT12D	—	2.50"	5.40"	3.57"	5.8 lb	#18

FEATURES

- Slim design maintains concrete cover
- Installs quickly and easily
- Utilizes the standard nVent LENTON taper profile
- Telescoping feature allows for gaps between mating bars
- Sight groove incorporated in the design to ensure proper installation
- No special tools or skills required
- Designed to splice two curved, bent or straight bars, when neither bar can be rotated and where the ongoing bar is NOT free to move in its axial direction

PM15 FEMALE POSITION ASSEMBLY





Material: Steel | Finish: Plain

Part Number	Hex Width W	Diameter Ø1	Diameter Ø2	Coupler Body CB	Length L	Bar Depth BD	Unit Weight
LU25PM15D	1.19"	—	1.75"	4.78"	7.70" Max	1.63"	1.3 lb
LU28PM15D	—	1.38"	1.88"	5.14"	8.24" Max	1.71"	2.0 lb
LU32PM15D	—	1.50"	2.00"	5.52"	8.76" Max	1.84"	2.8 lb
LU36PM15D	—	1.75"	2.25"	6.18"	9.68" Max	2.10"	4.0 lb
LU43TPM15D	—	2.00"	2.75"	8.07"	12.73" Max	2.71"	8.0 lb
LU57TPM15D	—	2.75"	4.00"	10.31"	16.00" Max	3.39"	24.1 lb

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Designed to Meet: AASHTO, ABNT NBR 8548:1984, ACI 318 Type 1 (125% Specified Yield), ACI 318 Type 2 (Specified Tensile), ACI 349, ACI 359, AS3600, BS EN 1992-1-1, BS EN 1992-2, CAN/CSA - N287.2/.3/.4, DIN EN 1992-1-1, Eurocode 2, IBC Type 1 (125% Specified Yield), IBC Type 2 (Specified Tensile), ISO 15835, NEN EN 1992-1-1, NF A 35-020-1, NF EN 1992-1-1, ÖNORM EN 1992-1-1, Sellafeld Ltd. Std. ES_0_3110, US Army Corps of Engineers, CAN/CSA - A23.3



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER