



Description: Thermostat with NC/NO contacts to manage temperature in panels. ETR202 with a normally closed contact for regulating heaters. ETR201 with a normally open contact for regulating cooling devices or signal devices. Sensor element thermostatic bimetal. Mounting clip for 35 mm DIN rail (EN 60715).

Material: Plastic according to UL94 V-0.

Setting range: 0 °C to +60 °C. Switching temperature difference less than 7 °K, and switching point tolerance ± 4 °K.

Switch capacity: 240 V AC, 10(2) A. 120 V AC, 15(2) A. 24 V DC, 30 W. Value in brackets for inductive load.

Operating temperature: -20 °C to +80 °C.

Service life: > 100,000 cycles.

Connection: Screw terminal for cable (0.5 to 2.5 mm²).

Protection: IP 20.

Approvals: CE, EAC, cULus_UL Listed.

Finish: RAL 7035.

Pack quantity: 1 piece.

Description	Item no.
Normally opened contact	ETR201
Normally closed contact	ETR202