

TT5001-HUV




RAYCHEM

CONNECT AND PROTECT

Solvent sensing cable for aboveground leak detection

PRODUCT OVERVIEW



Cable construction

nVent RAYCHEM TraceTek TT5001-HUV sensing cable detects the presence of liquid organic solvents at any point along its length, yet it does not react to the presence of water. Installed with an nVent RAYCHEM TraceTek Sensor Interface Module and Alarm Panel, the cable senses the solvent liquid, triggers an alarm and pinpoints the location of the leak within one meter.

Designed for aboveground leak detection

TT5001-HUV sensing cable is designed for use on aboveground pipe, around pump pads or valves where the cable will be exposed to sunlight and weather during its service life. The sensor cable core is standard TT5001 with well documented response times, and years of successful applications. The cable can be purchased in bulk form, cut to length in the field and joined using connector kits, or it can be obtained in standard or custom cut lengths with connectors attached in the factory. The cable is designed to be attached to the bottom of horizontal piping, spiraled around vertical pipe, or placed on flat surfaces below or around pumps and valves and other applications where surface level fuel leaks and spills can be anticipated.

Distinctive appearance and ready for chemical facility, tank farm and terminal applications


TT5001-HUV sensing cable has a matte black rope outer layer with a purple or blue tracer stripe. The rope outer layer is fabricated with thousands of individual filaments that add strength and excellent protection from the damaging effects of direct sunlight exposure. Additionally, this rope layer makes the sensor cable resistant to kinks and pliable, yet rugged enough for installation and long service life in pipe applications.

The sensor cable can have connectors wherever necessary; can be branched as needed and in general can be tailored to match the piping network. Circuits up to 1000 meters can be constructed by connecting individual segments. Multiple circuits can be monitored from a single control room location.

Advanced technology

nVent RAYCHEM radiation cross-linking and conductive-polymer technology is used to make TT5001-HUV cables. The combination of water and chemically resistant cable core coupled with the enhanced UV protection provided by the rope outer layer yield a product well suited for aboveground leak detection. The cable is able to withstand the rigors of installation and long years of service with exposure to rain, snow, sunlight and similar weather stresses.

ORDERING INFORMATION



TT5001-HUV modular sensing cable with factory-installed connectors

Catalog number	Part number	Description
TT5001-HUV-1M-MC	P000000836	1 m (3 ft) sensing cable
TT5001-HUV-3M-MC	P000000835	3 m (10 ft) sensing cable
TT5001-HUV-7.5M-MC	P000000834	7.5 m (25 ft) sensing cable
TT5001-HUV-15M-MC	P000000833	15 m (50 ft) sensing cable
TT5001-HUV-30M-MC	P000000832	30 m (100 ft) sensing cable
TT5001-HUV-50M-MC	P000000831	50 m (164 ft) sensing cable
TT5001-HUV-100M-MC	P000000830	100 m (328 ft) sensing cable

TT5001-HUV bulk sensing cable (connector kits required)

Catalog number	Part number	Description
TT5001-HUV-SC	P000000829	Bulk sensing cable on reel Minimum length: 30 m (100 ft) Maximum length: 240 m (800 ft)

Connector kits (not shown)

Catalog number	Part number	Description
TT5000-HUV-CK-MC-M/F (includes test tools)	P000001207	Components for five mated pairs of connectors

Installation materials

Catalog number	Part number	Description
TT-PU-FOAM-2x0.5	P000001136	2-inch wide foam with adhesive backing
TT-VSTRAP-1.5x75ft	P000001135	Fastening strap

PRODUCT CHARACTERISTICS

Cable diameter	7 mm (0.28 in) nominal
Cable diameter with connector	13 mm (0.52 in) nominal
Cable diameter with fiber jacket	10.2 mm (0.40 in) nominal
Fluoropolymer braid	Color—white and black
Braided fiber jacket	Color—black with purple or blue tracer
Cable weight	8.8 kg/100 m nominal (5.9 lb/100 ft nominal)
Operating temperature range	-20°C to 60°C (-4°F to 140°F)
Pull force limit	Not to exceed 100 kg (220 lb)
Bend radius	50 mm (2 in) minimum
Pressure	Loads greater than 9 kg (20 lb) per linear inch at 20°C (68°F) may immediately trigger an alarm
Nonresettable	Must be replaced after exposure to most solvents

CHEMICAL RESISTANCE

Cable functions normally after exposure in accordance with ASTM D 543 at 23°C (73°F) for seven days	Sulfuric acid	(10%)
	Hydrochloric acid	(10%)
	Nitric acid	(10%)
	Sodium hydroxide	(10%)

WATER RESISTANCE

Sensing cable	Less than 10 µA leakage when immersed in salt water for 90 days
Connector system	Less than 10 µA leakage when immersed in water at 10 psig for 24 hours

RESPONSE TIME

Represented materials detected	Typical response time at 68°F (20°C)
Toluene	10 min
Dichloromethane (methylene chloride)	5 min
1, 1, 1-trichloroethylene (TCE)	8 min
Trichloroethane (TCA)	20 min
Methyl ethyl ketone (MEK) [†]	10 min [†]
Acetone [†]	10 min [†]
n-methyl pyrrolidone (NMP) [†]	60 min [†]
Isopropyl alcohol (anhydrous)	90 min

[†] Prolonged immersion in ketones will inhibit sensing-cable performance.

Notes:

- Response times are based on 2 in (50 mm) of cable immersed in liquid.
- Response times are affected by operating temperature. Consult factory for specific response times at other temperatures and in other liquids.

APPROVALS AND CERTIFICATIONS

TT5001-HUV sensing cables are approved for installation in ordinary and hazardous areas when used in conjunction with approved nVent RAYCHEM TraceTek monitoring equipment and zener safety barriers when appropriate.

All nVent RAYCHEM TraceTek sensing cables are designated as "simple apparatus" and included in the approval certification for nVent RAYCHEM TraceTek monitoring instruments.

Consult the specific data sheets and approval certificates for the nVent RAYCHEM TraceTek TT-TS12, TTDM-128, TTSIM-1, TTSIM-1A, TTSIM-2, TTC-1 and TT-FLASHER-BE for application limitations and specific area approvals and certifications.



General Signaling Equipment
76LJ



The TT5001 HUV sensing cable is FM approved in the TraceTek Leak Detection System that detects the presence of liquid organic solutions when installed with a TraceTek Alarm and Locator Module.

North America

Tel +1.800.545.6258
Fax +1.800.527.5703
thermal.info@nVent.com

Europe, Middle East, Africa

Tel +32.16.213.511
Fax +32.16.213.603
thermal.info@nVent.com

Asia Pacific

Tel +86.21.2412.1688
Fax +86.21.5426.3167
cn.thermal.info@nVent.com

Latin America

Tel +1.713.868.4800
Fax +1.713.868.2333
thermal.info@nVent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER