

# **Surge Protection Solutions**

nVent ERICO Product Selection Guide





### Table of Content

The Need for Coordinated Protection	4	DT2 DIN Rail Surge Protection IEC Class II, 1+0 Mode	62
Total Facility Electrical Protection	6	DT2 DIN Rail Surge Protection IEC Class II, 2+0 Mode	63
nVent ERICO Expertise	8	DT2 DIN Rail Surge Protection IEC Class II, 3+0 Mode	64
Certified Surge Protection Devices	9	DT2 DIN Rail Surge Protection IEC Class II, 4+0 Mode	65
Transient Discriminating Technology	10	DT2 DIN Rail Surge Protection Class II, 1+0 Mode, 100 kA	66
The Core of TD Technology	11	EDT2 Enhanced DIN Rail Surge Protection	
Selection and Application of AC Power System SPDs		IEC Class II, 1+0 Mode	67
(UL System)	12	EDT2 Enhanced DIN Rail Surge Protection	
A Guide to Common Power Distribution Systems	13	IEC Class II, 2+0 Mode	68
Selection and Application of AC Power System SPDs	14	EDT2 Enhanced DIN Rail Surge Protection	60
Data and Signal Line Protection	18	IEC Class II, 3+0 Mode	69
Products	21	EDT2 Enhanced DIN Rail Surge Protection IEC Class II, 4+0 Mode	70
Surge Protection Product Selection	23	EDT2 Enhanced DIN Rail Surge Protection Class II,	/ 0
SES40	26	1+0 Mode, 100kA	71
SES80P	27	PVT1 Photovoltaic Surge Protection Class I	
SES40P	28	PVT2 Photovoltaic Surge Protection Class II	
SES 160/320/360/480 Series	29	Transient Discriminating Surge Diverter,	/ 0
Service Entrance Suppressor(B), 160 kA	30	20 kA Three Mode	74
Service Entrance Suppressor(F), 160 kA	31	Surge Diverter, 24/48 DC	
Service Entrance Suppressor(B), 320 kA	32	Transient Surge Filter	76
Service Entrance Suppressor(F), 320 kA		Surge Reduction Filter N-Series, Single Phase	77
Service Entrance Suppressor(BC), 320 kA	34	Surge Reduction Filter N-Series, Three Phase	
Service Entrance Suppressor(FC), 320 kA	35	High Speed Data Line Protector	
Service Entrance Suppressor(DB), 360 kA	36	Subscriber Line Protector, Single Stage	
Service Entrance Suppressor(DF), 360 kA	37	Telephone Line Protector	
Service Entrance Suppressor(DB), 480 kA	38	Coaxial Surge Protector	82
Service Entrance Suppressor(DF), 480 kA	39	Closed Circuit Television Protector	
SES Accessories		LAN Surge Protector	84
SES200	41	Data Equipment Protector	85
DT Panel Protector (B), 120 kA	43	Universal Transient Barrier, Single Pair	
DT Panel Protector (F), 120 kA	44	Universal Transient Barrier, Dual Pair	87
DT Panel Protector (B), 240 kA	45	Universal Transient Barrier, Dual Pair Single Power	88
DT Panel Protector (F), 240 kA	46	Universal Transient Barrier, Single Pair Isolated Ground	89
TDXM Modular Series	47	Universal Transient Barrier, Modem/Telephone	
Rail Primary Power Surge Protector	53	nVent ERICO Protection Device, F-Series	
Rail Primary Power Surge Protector with Flying Lead	54	Electronic Track Signal Protector	
Rail Secondary Power Surge Protector, AC Circuits	55	RTBN Rail Transient Barrier	93
Rail Secondary Power Surge Protector, DC Circuits	56	Remote Transmitter Protector	94
DT and EDT SPD Features	57	Load Cell Protector	95
DT1 DIN Rail Surge Protection IEC Class I+II, 1+0 Mode	58	Surge Counter, Digital Display	
DT1 DIN Rail Surge Protection IEC Class I+II, 2+0 Mode		Potential Equalization Clamp	
DT1 DIN Rail Surge Protection IEC Class I+II, 3+0 Mode	60	MOV/GDT/SAD Tester MGATESTER1	
DT1 DIN Rail Surge Protection IEC Class I+II, 4+0 Mode	61	Glossary of Terminology	

**NOTE:** Product application information given in this document is of a general nature. Installers of the product are cautioned to ensure product is always installed in accordance with any applicable National Standards, Codes, and Practices.

### The Need for Coordinated Protection



#### **CRITICAL FACTORS**

Critical factors need to be considered when determining the need for facility protection. Many factors can be determined by answering the following questions:

- · What is the risk to personnel?
- What is the risk of equipment damage?
- · What are the consequences of equipment failure?
- · Is the equipment associated with an essential service?
- · How will equipment failure affect overall facility operation and revenue generation?
- What are the legal implications of providing inadequate protection?

The statistical nature of lightning and the broad spectrum of energy delivered by a lightning flash, the problems created by

various power generation and distribution systems, and the continued trend to more sensitive and specialized electronics, requires careful selection of available technologies if adequate protection is to be provided.

#### WHAT ARE THE COSTS OF **INADEQUATE PROTECTION?**

The costs that can result from inadequate protection are many and varied. The type of equipment within a facility will have a direct impact on the damage that can occur. Robust equipment, such as lighting and air-conditioning systems, are often able to withstand impulses as high as 1500 volts and are not as sensitive to the rapid rate-of-rise exhibited by the pre-clamped surge waveform as are electronics.

These systems are often not critical to the continuing operation of the site and therefore usually do not require the

premium level of protection that is essential for more sensitive equipment. However, significant damage can occur, even to the more robust systems, as a result of lightning induced surges

resulting within a radius of several kilometers, or from switching induced surges. Costs can range from degradation of electrical or electronic systems to data loss, equipment destruction or injury to personnel. Some of these costs can appear relatively minor but the loss of an essential service or revenues associated with a facility or plant shut down can be enormous.

#### **SOURCES OF TRANSIENTS AND SURGES**

Although lightning is the most spectacular form of externally generated surges, it is only one source of over-voltage. Other sources include the switching of power circuits, the operation of electrical equipment by neighboring industries, the operation of power factor correction devices, and the switching and clearing

> of faults on transmission lines. It is important to note that lightning does not need to directly strike a power line for such damage to occur; a strike several hundred meters away can induce large damaging transients, even to underground cables.

> It is estimated that 70 to 85% of all transients are generated internally within one's own facility by the switching of electrical loads such as lights, heating systems, motors and the operation of office equipment.

> Modern industry is highly reliant on electronic equipment and automation to increase productivity and safety. The economic benefits of such devices are well accepted. Computers

are commonplace and microprocessor-based controllers are used in most manufacturing facilities. Microprocessors can also be found embedded in many industrial machines, security & fire alarms, time clocks and inventory tracking tools. Given the wide range of transient sources and the potential cost of disruption, the initial installed cost of surge protection can readily be justified for any facility. As a guide, the cost of protection should be approximately 10%





Damage to vital equipment caused by destructive surges and transients.


of the cost of the facility's economic risk.

### The Need for Coordinated Protection

Reliable protection of structures, industrial and commercial operations and personnel, demands a systematic and comprehensive approach to minimize the threats caused by transient over-voltages. Grounding, bonding, lightning protection and surge protection all need to be considered for comprehensive facility electrical protection. Each of these are interdependent disciplines that need a holistic design approach to ensure the facility is not left with a vulnerable "blind spot". The investment in surge protection can be wasted if "blind spots" exist. For example, installing a surge protection device on the power supply to a programmable logic controller is of little value if the I/O lines are not also protected. In addition, an air terminal on the facility may capture the lightning energy but without a dependable ground system, this energy


cannot be safely dissipated. Equally, even the most expensive Surge Protection Devices (SPDs) are poor performers if a low impedance equipotential ground is not provided. These interdependent disciplines are best applied when looking at a total facility rather than at an individual piece of equipment or portion of the facility.


It is for these reasons that nVent ERICO developed the Six Point Plan of Protection. The plan prompts the consideration of a coordinated approach to lightning protection, surge and transient protection and grounding, an approach that embraces all aspects of potential damage, from the more obvious direct strike to the more subtle mechanisms of differential earth potential rises and voltage induction at service entry points.



The Six Point Plan applied to a manufacturing facility. Surge and transient protection principles applied to a total facility rather than individual pieces of equipment.

### Total Facility Electrical Protection







#### **TOTAL FACILITY PROTECTION**

The consequences of an unexpected lightning strike or power surge can be catastrophic for a facility:

- · Personnel are at risk
- · Critical equipment may be damaged or destroyed
- Data can be corrupted
- The costs of operational downtime and lost revenue can be very substantial

As industries become more dependent on increasingly sensitive equipment, proper protection from lightning and dangerous over-voltage transients is necessary.

With more than a century of research, testing and product development, nVent ERICO has acknowledged that no single technology can totally eliminate vulnerability to lightning and surges.

The nVent ERICO Six Point Plan of Protection is designed to provide total facility protection by integrating several concepts.

The Six Point Plan of Protection will minimize the risk of damage to facilities through:


- · Direct lightning strike protection
- · Grounding and bonding
- Surge and over-voltage transient protection

#### **ABOUT NVENT ERICO**

For more than a century, nVent ERICO has been the global leader in precision-engineered electrical products for protecting structures, equipment and people. We serve the rail, commercial, telecom, utility, and industrial markets with application-specific facility electrical protection solutions. Our offices are headquartered in Solon, Ohio, USA, with a network of sales locations, manufacturing and distribution facilities serving more than 30 countries worldwide.

### nVent ERICO Expertise





The nVent ERICO advantage is our approach to the complete Facility Electrical Protection Solution. Well designed and high quality Surge Protection is critical to a facility equipment's reliable operation, however it is only part of the solution.

nVent ERICO therefore offers the complete range and expertise in grounding, bonding, surge and lightning protection, providing the complete solution worldwide and across applications including Commercial, Industrial, Telecom, Utility and Railway. Our service and expertise encompasses more than just the product.

#### **PRODUCT TESTING**

To effectively meet market requirements and ensure our products are designed and tested to the highest of performance standards. nVent ERICO has invested in state of the art testing equipment that is able to:

- Support application testing for clients to ensure your equipment is adequately protected.
- Participate in the UL Client Test Data Program.
- · Support competitive product testing.
- Test and evaluate to a range of mechanical, electrical and environmental requirements.

#### **HISTORY**

nVent ERICO continues to be a pioneer in the low voltage Surge Protection industry, having been involved in grounding and bonding applications for over 100 years, and as a manufacturer of SPDs for over thirty years.

Our involvement in the industry predates the creation of the initial IEC and UL low voltage surge protection standards. We've been on the journey since the early days of Low Voltage AC surge protection, with the issuing of the IEEE587 standard in 1980, and we have been active on all major worldwide SPD standards committees and industry bodies (including IEEE, IEC, and UL) since.



#### **SEMINARS AND SITE AUDITS**

Each year nVent ERICO conducts hundreds of seminars in numerous countries around the world, educating specifiers, engineers, and installers on Facility Electrical Protection, of which surge protection plays a key role.

### Certified Surge Protection Devices





nVent ERICO surge protective devices (SPDs) provide the option for traditional construction or TD technology. For example, the DT product line features traditional construction, while the EDT product line features with TD technology. These product lines have been designed and independently tested and certified to the latest editions of both IEC 61643-11 and UL 1449

This provides the user of the product peace of mind that the products will perform safely in application, and also perform to the claimed ratings provided. Both these standards have stringent tests that are not easy to pass, but essential to ensure the product is designed well for safe behavior, and for effective protection performance to the product ratings.

Compliance to these standards are required by code in many countries, however still many countries around the world do not require compliance, leaving those countries vulnerable to poorly performing products.

An informed buyer will avoid noncompliant product, instead demanding compliance to one or both of these standards, factually verified by an independent third party test laboratory certificate. Compliance to these standards alone however should be considered a



benchmark or minimum requirement, as there are certain enhanced performance requirements that may be advantageous for some applications.

One example of this is how the SPD performs during an AC overvoltage event.


In both standards referenced above, the requirement is for the SPD to safely disconnect from service during these events, however a better solution is for the SPD to survive such an event, thereby continuing to provide protection to your valuable equipment being protected.


nVent ERICO's TD technology delivers just that, a true step-up in performance for SPDs. Our SPDs with TD technology have been designed to be unaffected by the AC overvoltages applied during testing, while not compromising the clamping performance. This provides them with the ability to survive extreme overvoltage conditions and still be operational afterwards to protect your valuable equipment from subsequent surges and transients.

This extends greatly the life expectancy of the SPD within the most extreme environments, saving maintenance work and reducing operational downtime.

### Transient Discriminating Technology







To meet the fundamental requirements of performance, longer service life and greater safety under real world conditions, nVent ERICO has developed Transient Discriminating (TD) Technology.

This quantum leap in technology adds a level of "intelligence" to the Surge Protection Device enabling it to discriminate between sustained abnormal overvoltage conditions (Temporary Over Voltages – TOVs) and true transient or surge events. Not only does this help ensure safe operation under practical application, but it also prolongs the life of the protector since permanent disconnects are not required as a means of achieving internal over-voltage protection.

#### TRADITIONAL TECHNOLOGIES


Conventional SPD technologies utilizing metal oxide varistors and/or silicon avalanche diodes to clamp or limit transient events are susceptible to sustained 50/60 Hz mains overvoltage conditions (TOVs) which often occur during faults to the utility system. Such occurrences present a significant safety hazard when the suppression device attempts to clamp the peak of each half cycle on the mains overvoltage.

This condition can cause the device to rapidly accumulate heat and in turn fail with the possibility of inducing a fire hazard. The diagram shows how a traditional SPD is chosen to have a nominal clamping voltage that is above the peak of the nominal AC mains voltage. However, in the lower diagram, it can be seen that when the AC mains experiences a Temporary Over-Voltage (TOV), the SPD attempts to clamp the over-voltage, and rapidly heats up, resulting in failure, potentially accompanied by fire or explosion.

### The Core of TD Technology



The secret to nVent ERICO's Transient Discriminating Technology is its active frequency discrimination circuit. This patented device can discriminate between a temporary over-voltage (TOV) condition and a very fast transient, which is associated with lightning or switching-induced surges. When the transient frequencies are detected, the patented Quick-Switch within TD activates to allow the robust protection to limit the incoming transient. The frequency discriminating circuit that controls the Quick-Switch helps ensure that the SPD device is immune to the effects of a sustained 50 or 60 Hz TOV. This allows the device to keep operating, in order to help provide safe and reliable transient protection, even after anabnormal over-voltage condition has occurred.




Effectively, TD Technology allows the SPD to have two clamping levels – one well above the peak of a TOV (up to twice its nominal AC voltage!), and the other much lower, to effectively and swiftly clamp lightning transients.

As the explanatory illustration shows, this allows the TD circuit to still remain operational after TOV events, thus continuing to clamp transients and providing a much longer operational life. For example, the IEC 61643-11 standard applies a test of 442 Vac for two hours from Line to Neutral for SPDs intended to operate at 230 Vac. While most SPDs fail safely during this test, nVent ERICO's EDT2 Series SPDs are unaffected by this stringent test, and remain completely operational. The IEC 61643-11 standard calls this Withstand mode, as opposed to Safe Failure mode.

nVent ERICO SPDs that incorporate TD Technology are especially recommended for any site where sustained over-voltages are known to occur, and where failure of traditional SPD technologies cannot be tolerated.

# Selection and Application of AC Power System SPDs (UL System)

#### RECOMMENDED SURGE RATINGS (8/20µs)



Ng = strikes/km<sup>2</sup>/year.

Recommended Pro	ducts				
			SRF N SERIES		
	DTX 120, 240; TDX 300, 400				
LS S	SES40, SES80, SES160, SES320, SES360, SES480				
PRODUC	DT1 SERIES				
P.R.	DT2/EDT2 SERIES				
	TSF Series				Series
					TDS1301 Series

#### "TYPE" OF SPD

In the UL system, SPDs are tested to various Types, intended to assess and assure their suitability for use in different locations and circumstances. The Type of SPD indicates its suitability for use in certain areas of a facility (service entrance, Branch Panel, etc.). Because of this, the battery of tests that the SPD are subject to will be more or less severe, in descending order of Type.

#### The SPD Types are as follows:

**Type 1** – Permanently connected SPDs, intended for installation between the secondary of the service transformer and the line side of the service equipment overcurrent device, as well as the load side, including Molded Case SPDs intended to be installed without an external overcurrent protective device.

**Type 2** – Permanently connected SPDs intended for installation on the load side of the service equipment overcurrent device; including SPDs located at the branch panel and Molded Case SPDs.

**Type 3** – Point of utilization SPDs, installed at a minimum conductor length of 30 feet (10 meters) from the electrical service panel to the point of utilization, for example cord connected, direct plug-in, receptacle type and SPDs installed at the utilization equipment being protected.

**Type 4 Component Assemblies** – Component assembly consisting of one or more Type 5 components together with a disconnect (integral or external) or a means of complying with the limited current tests.

**Type 1, 2, 3 Component Assemblies** – Consists of a Type 4 component assembly with internal or external short circuit protection.

**Type 5** – Discrete component surge suppressors, such as MOVs that may be mounted on a PWB, connected by its leads or provided within an enclosure with mounting means and wiring terminations.

Fitting SPDs at all three locations may not be necessary, depending on the building size, and wiring length. Generally, SPDs are always fitted at the point of entry (Service Entrance), and in smaller equipment rooms may just be, additionally, at the equipment. In larger buildings, spread over multiple floors or large areas, SPDs should also be provided at the Branch Panels, and additionally at sensitive or critical equipment.

SPDs are primarily rated according to how large a surge current magnitude they can handle, and how well they limit the voltage while conducting that surge current. These parameters are

# A Guide to Common Power Distribution Systems


Throughout the world a number of different power distribution systems are used. This guide identifies the more common of these systems. The individual product specification tables detail system suitability.

Description	Source Configuration	Typical Supp	oly Voltages
Single Phase 1Ph, 2W+G	L N S G S G	110V 120V 220V 240V	(L-N)
Single Phase 1Ph, 3W+G Also known as Split phase or Edison system	L1 N L2 G G	120/240V	(L-N/L-L)
Three Phase WYE without neutral 3Ph Y, 3W+G	L1  L2  L3  G	480V	(L-L)
Three Phase WYE with neutral 3Ph Y, 4W+G	L1  N  L2  L3  G	120/208V 220/380V 230/400V 240/415V 277/480V 347/600V	(L-N/L-L)
Delta High leg 3Ph Δ, 4W+G	L1 L2 L3 N G	120/240V	(L-N/L-L)
Delta Ungrounded 3Ph $\Delta$ , 3W+G	L1  L2  L3  G	240V 480V	(L-L)
Delta Grounded corner 3Ph Δ, 3W+G	L1 L2 L3 G	240V 480V	(L-L)

Having determined the Class of SPD required, the correct voltage and configuration needs to be determined. The standard IEC 60364-1 details the following system configurations. In the descriptions that follow, Uo is used for the nominal systems voltage, and Uc is used for the maximum continuous operating voltage (this is a parameter of an SPD).

#### **TN-C System**

In this system, the neutral and protective earth conductor are combined in a single conductor throughout the system. This conductor is referred to as a PEN, a "Protective Earth & Neutral". All exposed conductive equipment parts are connected to the PEN.




SPDs Installed	Description	Example Product
Phase to PEN ("3+0")	At least 1.1 x Uo	DT230030R

For example, on a 230 V Ph-N system, Ph-PEN protection should have a Uc rating of at least 255 V. Generally an SPD with a Uc rating of at least 275 V would be selected for 220 to 240 V systems. Often, to allow for power supply voltage fluctuations, a Uc of at least 1.3 x Uo is recommended, such as a Uc of 300 V for a 230 V system, or nVent ERICO's TD technology would be chosen.

#### **TN-S System**

In this system, a separate neutral and protective earth conductor are run throughout. The Protective Earth (PE) conductor is normally a separate conductor, but can also be the metallic sheath of the power cable. All exposed conductive equipment parts are connected to the PE conductor.




SPDs Installed	Description	Example Product
Phase to PE ("4+0"), or	At least 1.1 x Uoc	DT230040R
Phase-N, and N-PE ("3+1")		DT230031R

For example, on a 230 V Ph-N system, Ph-PE (or Ph-N) protection should have a Uc rating of at least 255 V. Generally an SPD with a Uc rating of at least 275 V would be selected for 220 to 240 V systems. Often, to allow for power supply voltage fluctuations, a Uc of at least 1.3 x Uo is recommended, such as a Uc of 300 V for a 230 V system, or nVent ERICO's TD technology would be chosen.

#### **TN-C-S System**

In this system, the supply is configured as per TN-C, while the downstream installation is configured as per TN-S. The combined PEN conductor typically occurs between the substation and the entry point into the building, and earth and neutral are separated in the Main Distribution Board. This system is also known as Protective Multiple Earthing (PME) or Multiple Earthed Neutral (MEN). The supply PEN conductor is earthed at a number of points throughout the network and generally as close to the consumer's pointof-entry as possible.




SPDs Installed	Description	Example Product	
MDB: Phase to PEN ("3+0")			
DB: Phase to PEN ("4+0"), or	At least 1.1 x Uo	DT130030R, DT230040R, DT230031R	
Phase-N, and N-PE ("3+1")			

For example, on a 230 V Ph-N system, Ph-PE (or Ph-N) protection should have a Uc rating of at least 255 V. Generally an SPD with a Uc rating of at least 275 V would be selected for 220 to 240 V systems. Often, to allow for power supply voltage fluctuations, a Uc of at least 1.3 x Uo is recommended, such as a Uc of 300 V for a 230 V system, or nVent ERICO's TD technology would be chosen.

#### **TT SYSTEM**

A system having one point of the source of energy earthed and the exposed conductive parts of the installation connected to independent earthed electrodes. The incoming supply neutral is not earthed at the main distribution board.




SPDs Installed	Description	Example Product
Phase to N, N-PE ("3+1")	At least 1.1 x Uoc	DT130031R, DT230031R

For example, on a 230 V Ph-N system, Ph-N protection should have a Uc rating of at least 255 V. Generally an SPD with a Uc rating of at least 275 V would be selected for 220 to 240 V systems. Often, to allow for power supply voltage fluctuations, a Uc of at least 1.3 x Uo is recommended, such as a Uc of 300 V for a 230V system, or nVent ERICO's TD technology would be chosen.


In the TT system, in order for overcurrent protective devices (fuses and circuit breakers) to operate in the intended manner, it is important that SPDs must not connect directly from phase to protective ground, but from phase to neutral and neutral to ground. Therefore, the Neutral-to-PE SPD carries both the PE to neutral impulse current and the PE to phase impulse currents. This SPD is recommended to be a GDT (Gas Discharge Tube) due to their generally superior energy handling characteristics.

#### **IT SYSTEM**

A system having no direct connection between live parts and earth, but all exposed conductive parts of the installation being connected to independent earthed electrodes. The source is either floating or earthed through a high impedance (to limit fault currents). This means that during a Phase to Earth fault, the systems continues to operate. This is detected, and maintenance efforts commenced to rectify the fault. However, during this time, the Phase to Earth voltage rises to the usual Line to Line voltage, and installed SPDs must withstand this during this time. Most installed IT systems do not utilise a neutral conductor - equipment is powered from line to line. The IT system is typically used in older installations in countries such as Norway and France. It is also used in special applications, such as intensive care wards of hospitals and special industrial applications.



SPDs Installed	Description	Example Product
Phase to PEN ("3+0")	At least 1.73 x Uo	DT230030R



SPDs Installed	Description	Example Product
Phase to PEN ("4+0")	At least 1.73 x Uo	DT130040R, DT230040R

For example, on a 230 V Ph-N system, Ph-PE and N-PE protection should have a Uc rating of 440 V (allowing for the L-L voltage and a 10% tolerance). Often an additional safety margin is applied, to allow for instabilities that can occur in the ungrounded IT system, such as a Uc of 480 V.

## Data and Signal Line Protection

### HOW TO SELECT SURGE PROTECTION FOR DATA, SIGNALLING AND CONTROL CIRCUITS

Knowing where to install surge protection can be difficult. To ensure cost-effective protection is provided for data, signalling

and control circuits, two issues need to be considered:

- · Where should the SPDs be installed?
- What type of SPD is appropriate for each circuit type and location?


#### WHERE SHOULD THE SPD(S) BE INSTALLED?

Communications devices are at risk from transients being induced onto the interconnecting signal lines. The use of surge protection barriers, installed at either end of the lines, provides cost effective protection. Communication or signal lines that enter or exit the building pose the highest risk. In such circumstances, protection devices should be installed at the point-of-entry or at the equipment termination itself. Internal wiring which extends more than 10 to 15 m should also be protected. Twisting or shielding of cables provides a level of protection, however this should not be regarded as sufficient for the sensitive interfaces that characterize today's communication devices.

#### **HOW TO SELECT AN SPD FOR A GIVEN LOCATION**

Five parameters must be considered to ensure that surge protection devices for use on data, signalling or control circuits are effective and do not adversely affect operation of the circuit.


- SPDs are designed to clamp the excess transient voltage to safe levels sustainable by the equipment, yet should not interfere with the normal signalling voltages. As a guide, the SPD clamping voltage should be selected to be approximately 20% higher than peak working voltage of the circuit.
- 2. The line current rating of the SPD should be sufficient to handle the maximum expected signalling current.
- 3. The SPD bandwidth should be sufficient to allow correct operation of the system without adverse attenuation. This ensures that the attenuation of the SPD at the nominal operating frequency of the system does not exceed the stated limit. For most SPDs, frequency attenuation data or a maximum recommended baud rate is generally specified.
- 4. The connection termination, mounting method, number of lines to be protected and other physical aspects must be considered.
- 5. The SPD surge rating should be appropriate for the intended location. For circuits internal to the building, surge ratings of 1-5 kA are generally sufficient. For the protection of circuits that connect to exposed lines entering or exiting the facility, 10-20 kA is recommended. Alternatively a protocol or standard may be specified that defines the above parameters. All UTB products are rated 20 kA for higher exposure areas.




# Data and Signal Line Protection

#### **SAMPLE APPLICATIONS**


#### 2-Wire Isolated Ground Transducers/Sensors




#### 2-Wire Sensors




#### **Powered Sensor Protection**



#### Multiple Sensor or up to 4-Wire Sensor



#### **Protecting Sensors in Hazardous Locations**



### Data and Signal Line Protection

#### **GUIDE TO DATA AND SIGNALING CIRCUITS**

The selection of an SPD for communication and signalling circuits requires knowledge of the:

- 1. Maximum Continuous Operating Voltage (Uc)
- 2. Maximum line current (IL)
- 3. Frequency
- 4. Termination (connector type and/or impedence)

Where a protocol is known, this often eliminates the need to verify product selection criteria 1-3, and occasionally 4.

A number of different SPDs often meet the requirements as defined by the protocol, so the final choice of which SPD to use is often determined by its type of physical connection, number of lines to be protected, or its surge rating. Some protocols do not define the actual connector or pin configuration, and in some cases, not all lines defined by the protocol will be used. Please refer to the documentation provided with the equipment requiring protection to ensure the proposed protection modes are adequate and that the SPD's characteristics will not interfere with normal system operation.

Protocol/Standard	Description	Applicable SPD Series
	Unbalanced, bi-directional communication circuit.	UTB 15 SP <sup>(1)</sup> , UTB 15DP <sup>(2)</sup>
RS-232 (V.24)	Although standard allows +/- $25\mathrm{V}$ signaling, use of more than +/- $12\mathrm{V}$ is uncommon	UTB 5 <sup>(1)</sup>
RS-422 (V.11)	Industrial version of RS-232. 0-5 V balanced signaling	UTB 5 <sup>(1)</sup>
RS-423	Similar to RS-232 but +/- 5 V signaling used	UTB 5 <sup>(1)</sup>
RS-485	Similar to RS-422 but allows multiple devices to communicate. DB-9 connector is common	UTB 15
Ethernet	Ethernet is the term used to describe a family of communication protocols.	
Cat 4	* 10BaseT is a 10 MHz system using twisted pair of coax cables	
Cat 5	* 100BaseT is a 100 MHz system using twisted pair cables	
Cat 6	* 10GBaseT is a 250 MHz system using twisted pair cables	LANRJ45C6P
10BaseT	Cat 4 is a cable specification that allows operation up to 10BaseT,	
100BaseT	while Cat 5 allows operation up to 100BaseT frequencies.	
PoE	Power Over Ethernet	
Telephone Lines		UTB SA <sup>(2)</sup> , UTB TA <sup>(2)</sup>
4-20 mA current loop (with HART)	Common industrial communications protocol used to interface with transducers etc	UTB xDP, UTB 30DPS, UTB xSP
Binary Signals		UTB xSP <sup>(1)</sup> , UTB xDP <sup>(1)</sup>
Bitbus (IEEE 1118)	Digital communications network based on RS-485 and SDLC allowing communication between PLCs and controllers	
CAN-Bus (data signal line)	Differential serial communications protocol defined in ISO 11898 standard	UTB 5 <sup>(1)</sup>
DeviceNet (data signal line)	Communication protocol used to connect industrial devices such as limit switches, motor starters to PLCs and controllers	
M-Bus	Communication protocol for networking and remote reading of heat, gas, water, and energy meters	UTB 60 <sup>(1)</sup>
Ex (I) - HART, 4-20 mA circuit, measurement circuits	Hazardous locations	UTB15 Ex, UTB30 Ex
Profibus - PA	Process field bus - process automation. Ideal for explosion - hazardous areas	UTB30 Ex
Strain gauge / Load cells	As used in weigh bridges etc.	LCP01A
ASDL	Asymmetric Digital Subscriber Line. Protocol for data communication over copper telephone lines. Uses single copper wire pair.	UTB TA <sup>(2)</sup> , UTIntegrated Service
HDSL	High bit rate Digital Subscriber Line. Protocol for data communication over copper telephone lines. Uses two copper wire pairs.	Digital Network. Protocol for voice and data over copper telephone
ISDN	Integrated Service Digital Network. Protocol for voice and data over copper telephone lines	linesB SA <sup>(2)</sup>

- The number of UTB's required is dependent on the number of wires being used in the signalling circuit. UTBs are designed for balanced circuits and each UTB will protect one pair of wires. The UTB can also be used to protect two unbalanced circuits.
- The UBT TA is rated to 500 A 8/20 us and intended to meet US NEC requirements. The UTB SA are rated to 20 kA 8/20 μs and specifically designed and approved for use on the Australian telecommunication network.

### **Products**

#### **AC POWER SURGE PROTECTION**

#### DT1

The DIN Rail mounted DT1 family of SPDs provide reliable and efficient protection against voltage transients within the IEC Class I & II environments and is certified to UL Type 1 CA. Tested and independently certified to the IEC (via VDE) and UL standards, the DT1 Series provides a range of safety and performance features for the harshest environments and suitable for protection within a wide range of applications.

#### DT2

The DIN Rail mounted DT2 family provides many of the same benefits as the DT1 Series but is specifically designed to fit within the parameters of IEC Class II environments and is certified to UL Type 1 CA. Targeting the Class II / Type 1 CA classification allows the system designer to effectively select the correct coordinated protection while keeping total project costs in check.

#### EDT2

The DIN Rail mounted EDT2 family of SPDs provide reliable protection against voltage transients within the IEC Class II environments and is certified to UL Type 1 CA. In addition, nVent ERICO's Transient Discriminating (TD) technology ensures continued operation during and after sustained and abnormal over-voltage events. Tested and independently certified to the IEC (via VDE) and UL standards, the EDT2 Series provides a range of safety and performance features for the harshest environments and suitable for protection within a wide range of applications. The EDT2 Series provides extended service life in the harshest of environments, ensuring your equipment and systems are kept safe and operational through extreme abnormal voltage conditions.

#### **DTX Panel Protector**

The nVent ERICO DTX120 and DTX240 Series of Surge Protective Devices (SPD) features a cUL 1449 listing and provides premium protection against damaging transients and surge currents, particularly in Type 1 and Type 2 locations. The innovative design is Field Serviceable and also includes RS-485 Connectivity for integration into Building Automation Systems. With a 120 - 240 kA per phase surge rating, nVent ERICO DTX120 and DTX240 are well suited for category C locations and is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX120 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

#### SES40P

The nVent ERICO SES40P Series of Surge Protective Devices (SPD) provide economical protection against damaging transients and surge events. These Type 1 devices are UL® Listed to UL 1449 Edition 5 and CSA C22.2 No. 291.1-17. This allows installations on the line or load side (Type 1 or Type 2) of the service panel in accordance with the NEC® CSA C22.2 No. 291.1-17 without the requirement for additional circuit breakers or fuses. Primary applications are service entrance, branch, commercial, industrial, and residential. Other applications include OEM panels, solar combiner boxes, UL 96A lightning protection installations and light pole applications. The housing is constructed of UV-stabilized thermoplastic and meets the UL 50 Type 4X rating, making it ideal for both indoor and outdoor applications. All of the models have a 20kA nominal discharge current rating, the highest level recognized under the UL 1449 Edition 5 standard.









### **Products**

#### **AC POWER SURGE PROTECTION**

#### SES360/480

The nVent ERICO SES360 and SES480 Series of Surge Protective Devices (SPD) provides economical protection against damaging transients and surge currents. The SES360 and SES480 Series is a cUL 1449 listed SPD for Type 1 or Type 2 locations, allowing for installation either on the line or load of service panels without requiring circuit breakers (DB models only). With a 360 - 480 kA per phase surge rating, the SES360 and SES480 are well suited for category C locations. Typical applications for the nVent ERICO SES360 and SES480 Series include service entrances, distribution, branch panels, MCC, lighting panels, HVAC and more. Featuring a NEMA 4 enclosure rating, the DB and DF series are also appropriate for use in outdoor applications.

#### SES160 / SES320

The nVent ERICO SES 160 and SES320 Series is a compact and robust design, with many features being standard. The standard features for this 160 kA or 320 kA per phase SPD include an audible alarm, pre-wired relay contacts, LED indicators and a NEMA 4X enclosure. The SES160 and SES320 F models include a UL 1283 listed filter, tested to Mil-Std 220 A; an additional Status LED; and, Ground Ref. Monitoring (GRM.) The SES320 C models include a surge counter. The SES160 and SES320 Series is well suited for service entrance, distribution, branch panels, MCC, lighting panels, HVAC, A/V systems, IT equipment and more.



#### **SURGE FILTERS**

#### **SRF**

The SRF (Surge Reduction Filters) product family combines high-energy surge diversion with surge filtering, making them ideal for primary service protection applications. Their efficient low pass filtering stage dramatically reduces the rate-of-voltage rise and the let-through voltage thereby substantially reducing the risk of physical equipment damage. They incorporate TD technology making them robust against AC power system temporary overvoltages, and their standards compliance to IEC 61643-11 Class I & Class II ensure maximum product performance with maximum product safety.

#### **TSF**

The Transient Surge Filter (TSF) product family combines nVent ERICO's Transient Discriminating (TD) technology with a low pass filter to protect against transient events and attenuate small signal RFI/EMI noise problems. Perfect for PLC controllers, SCADA systems, motor control centers, and other similar applications, the TSF also features serviceable surge modules and a compact form factor. The TSF range of products are certified to UL 1449 5th Edition, UL 1283 5th Edition (EMI Filtering), and IEC 61643-11 Class II.



#### **DATA / SIGNAL PROTECTION**

Lightning or induced surges can destroy or compromise signal communications systems and data. nVent ERICO offers multiple series of data and signal surge protection devices designed to provide transient protection for equipment from induced surges. These are also well-suited to the protection of industrial equipment and are compact in size, while offering high surge carrying capacity. nVent ERICO data and signal surge protection offers a complete solution to eliminate damage, downtime, and power disruption.



# Surge Protection Product Selection

The various product solutions available are listed below. The basic division is into power protection and signal protection. Power protectors are further divided into shunt protection and series (filtering) protection. Signal protectors are genberally divided by connectors types and application.

Power Protection - Non-DIN Rail					
Shunt protection for Power Circuits					
TDX YYY V ZZZ	TDX = PRODUCT FAMILY		YYY = SURGE RATING 50 KA 100 KA 200 KA 300 KA 400 KA	V = PRODUCT VERSION M = MODULAR S = MODULAR WITH SURGE COUNTER & FILTER (100KA & 200KA) C = COMPACT	ZZZ = VOLTAGE CONFIGURATION 120 120/208 120/240 120/240D 240 240D 277/480 277/480TT 347/600 480D
SES40P XXX YY	SES = PRODUCT FAMILY		XXXX = VOLTAGE CONFIGURATION 120 120/240 208 240 480 300	YY = CONFIGURATION 1P = SINGLE PHASE SP = SPLIT PHASE 3P = THREE PHASE DC = DIRECT CURRENT	
SES160 / SES320	SES = PRODUCT FAMILY	XXXX = IMAX AND TYPE 160B = 160 KA, BASIC 160F = 160 KA, FILTER 320B = 320 KA, BASIC 320F = 320 KA, FILTER 320BC = 320 kA, Counter, Basic 320FC = 320 kA, Counter, Filter	YYYY = VOLTAGE CONFIGURATION 120 120240 208 240 480 600	ZZ = CONFIGURATI V = SINGLE PHASE S OR SP = SPLIT PH Y = WYE D = DELTA	
SES360 / SES480  Power Protection - DI	SES = PRODUCT FAMILY	XXXX = IMAX AND TYPE  360DB = 360 kA,	YYYY = VOLTAGE CONFIGURATION 120240 480 600 240480 208	ZZ = CONFIGURATI S = SPLIT PHASE D = DELTA Y = WYE	ON

Shunt protection	for	power	circuits
------------------	-----	-------	----------

(E)DTX YYY ZZ (R)	(E)DTX =	YYY = VOLTAGE	ZZ = MODE /	R = REMOTE CONTACTS
	PRODUCT	75 = 75 V	VARIANT	
	FAMILY	150 = 150 V	10 = 1 + 0	
	DT1 = Dinrail IEC	300 = 300 V	20 = 2 + 0	
THE E	Test Class 1	350 = 350 V	30 = 3 + 0	
	DT2 = Dinrail IEC	480 = 480 V	40 = 4 + 0	
	Test Class 2	550 = 550 V	11 = 1 + 1	
	EDT2 = Enhanced	750 = 750 V	31 = 3 + 1	
	Dinrail IEC		100 = 100 kA	
	Test Class 2			

### Surge Protection Product Selection

#### Power Protection - Transient Surge Filters

Series protection for power circuits (6 A to 20 A)

**TSF XXA YYYV** 



TSF = PRODUCT FAMILY

**XX = LINE CURRENT** 6 = 6 A 20 = 20 A **YYY = VOLTAGE** 24 = 24 V (6 A only) 120 =120 V 240 =240 V

#### Power Protection - Surge Reduction Filters

Series protection for power circuits (63 A to 800 A)

**SRF XXXA N** 



SRF = PRODUCT FAMILY

CURRENT
63 = 63 A
125 = 125 A
250 = 250 A
500 = 500 A
800 = 800 A

XXX = LINE

N = N SERIES

#### Signal Protection - Universal Transient Barriers

General purpose signal protection

**UTB XXX SP** 



UTB = PRODUCT FAMILY

**XXX = VOLTAGE** 5 = 5 V 15 = 15 V 30 = 30 V 60 = 60V 110 = 110V

SP = SINGLE PAIR DP = DUAL PAIR

#### Telephone line protection

**UTBSA** 



UTB = PRODUCT FAMILY SA = TELEPHONE TA = TELELPHONE, UL LISTED

#### Signal Protection - Coaxial Surge Protection

General purpose coaxial cable protection

**CSP1 XXX YYY** 



**CSP1 = PRODUCT FAMILY** 

XXX = CONNECTOR

NB =N type, F-F bulkhead

NMF =N type, male-female

BNC = BNC type, male-female

SMA = SMA type, male-female

F = F Type male-female


**YYY = MODE** 90 = 90 V 600 = 600 V


# Surge Protection Product Selection

Signal Protection - High	n Speed & Subscriber Line Protecti	ion										
High Speed twisted pai	r Krone block protection											
HSP 10 K XXX	HSP = PRODUCT FAMILY	10 = 10 PAIR	K = KRONE BLOCK	XXX = VOLTAGE 12 = 12 V 36 = 36 V 72 = 72 V 230 = 230 V								
General twisted pair Krone block protection												
SLP 1 RJ11	SLP = PRODUCT FAMILY	1 = 1 PAIR	RJ11A = RJ11 CONNEC RJ11 = RJ11 CONNECT									
SLP 10 K1F	SLP = product family	10 = 10 pair	K = Krone block									
Signal Protection - Clos	sed Circuit & Cable TV											
Coaxial Cable CCTV												
CCTV 12	CCTV = PRODUCT FAMILY	12 = voltage										
Signal Protection - Loc	al Area Network											
General Purpose RJ45	protection											
LAN RJ45 C6P	LAN = PRODUCT FAMILY	RJ45 = connector	C6P = Category 6 Protec	etion								
The state of the s												

### SES40

### Service Entrance Suppressor, 40 kA, Metal






#### **Features**

- Compact NEMA®-4 enclosure design can be flush mounted or installed in a small space
- LED status indication flag for status monitoring
- 120/240 VAC operating voltage suits the most common power distribution system for residential or small commercial buildings
- 40 kA 8/20 µs maximum surge rating (per mode) provides protection suitable for service entrance and distribution panels
- 5-Year Warranty

Part Number	SES40120/240
Nominal System Voltage (Un)	120/240 V
Distribution System	1Ph 3W+G
Max Continuous Operating Voltage (Uc)	170/276 VAC
Frequency	50 - 60 Hz
Short Circuit Current Rating (SCCR)	200 kA
Nominal Discharge Current (In)	20 kA 8/20 μs
Max Discharge Current (Imax)	40 kA 8/20 us per mode
Voltage Protection Rating (VPR)	800 V @ 3 kA; 1,200 V @ 20 kA
Protection Modes	L-L; L-N; L-PE
Status Indication	LED
Technology	MOV with thermal disconnect
_ead Length	30"
_ead Size	#10
Ground Lead Length	36"
Temperature	-40 to 176°F
Enclosure Material	Metal
Enclosure Rating	IP 65 NEMA®-4
Mounting	¾" straight nipple
Depth (D)	2.87"
Height (H)	3.27"
Width (W)	3.27"
Unit Weight	1.54 lb
Certification Details	UL® 1449 Edition 5 Type 1/2, 20 kA Mode
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 2, 20 kA 8/20 μs, 2 kA 10/350 μs IEC® 61643-1 Class II
Certifications	UL
Standard Packaging Quantity	1 pc

### SES80P

### Service Entrance Suppressor(P), 80 kA



#### **Features**


- Compact design can be directly mounted to the secondary side of the transformer
- · Front-facing design eases installation and performance monitoring
- 80 kA 8/20 µs maximum surge rating per mode
- Cable entrance features water-resistant heatshrink seal
- Includes mounting bracket for secondary side of distribution transformers

The nVent ERICO SES80P Surge Protective Device (SPD) provides economical protection against damaging transients and surge events. Primary applications are the secondary windings of distribution transformers. The housing is constructed of UV-stabilized thermoplastic and is tested to the UL50 Type 4X rating, making it ideal for both indoor and outdoor applications. The product features a 20 kA nominal discharge current rating.

Part Number	SES80P1202SC
Nominal System Voltage (Un)	120 VAC
Distribution System	1Ph 2W+G
Max Continuous Operating Voltage (Uc)	150 VAC
Frequency	0 – 100 Hz
Short Circuit Current Rating (SCCR)	200 kA
Nominal Discharge Current (In)	20 kA 8/20 μs
Max Discharge Current (Imax)	80 kA 8/20 μs
Voltage Protection Rating (VPR), L-PE	700 V
Technology	MOV with thermal disconnect
Status Indication	Blue LED
Lead Size	#12
Lead Length	36"
Temperature	-40 to 176°F
Mounting	½" straight nipple
Enclosure Rating	NEMA®-4X
-	IP 65
Enclosure Material	UL® 94V-0 Thermoplastic
Unit Weight	0.065 lb
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C
Depth (D)	3"
Width (W)	4 3/4"
Length (L)	4 3/4"
Height 1 (H1)	2 3/4"
Height 2 (H2)	1½"
Hole Size (HS)	0.185"

### SES40P

### Service Entrance Suppressor



#### **Features**

- Compact NEMA®-4X enclosure design can be flush mounted or installed in a small space
- · LED status indication flag for status monitoring
- 40 kA 8/20 µs maximum surge rating per mode protection suitable for service entrance and distribution panels
- CE, UL® 1449 Edition 5 Listed, CSA-22.2
- Optional Flush Plate and L-Bracket available
- 5-Year Warranty



SES40P shown with optional Flush Plate (SES40PFP)


The nVent ERICO SES40P Series of Surge Protective Devices (SPD) provide economical protection against damaging transients and surge events. These Type 1 devices are UL® Listed to UL 1449 Edition 5 and CSA C22.2 No. 291.1-17. This allows installations on the line or load side (Type 1 or Type 2) of the service panel in accordance with the NEC® CSA C22.2 No. 291.1-17 without the requirement for additional circuit breakers or fuses. Primary applications are service entrance, branch,

commercial, industrial, and residential. Other applications include OEM panels, solar combiner boxes, UL 96A lightning protection installations and light pole applications. The housing is constructed of UV-stabilized thermoplastic and meets the UL 50 Type 4X rating, making it ideal for both indoor and outdoor applications. All of the models have a 20kA nominal discharge current rating, the highest level recognized under the UL 1449 Edition 5 standard.

Part Number	SES40P120/240SP	SES40P1201P	SES40P2083P	SES40P2401P	SES40P4801P	SES40P4803P	SES40P300DC				
Nominal System Voltage (U <sub>n</sub> )	120/240 VAC	120 VAC	120/208 VAC	240 VAC	277/480 VAC	277/480 VAC	300 VDC				
Distribution System	1Ph 2W+G		3Ph 4W+G 3Ph∆ 3W+G	1Ph 2W+G		3Ph 4W+G 3Ph∆ 3W+G	DC 2W+G				
Max Continuous Operating Voltage (U <sub>c</sub> )	150/300 VAC	150 VAC	150/300 VAC	300 VAC	340/590 VAC	340/590 VAC	360 VDC				
Frequency	0 – 100 Hz						-				
Short Circuit Current Rating (SCCR)	200 kA						100 kA				
Nominal Discharge Current (I <sub>n</sub> ), Per Mode	20 kA 8/20 μs				10 kA 8/20 μs	20 kA 8/20 μs					
Max Discharge Current (I <sub>max</sub> ), Per Mode	40 kA 8/20 μs	0 kA 8/20 μs									
Voltage Protection Rating (VPR),	L-L 1,800 V L-N 900 V	L-N 1,800 V L-PE 900 V N-PE 900 V	L-L 1,800 V L-N 800 V L-PE 1,800 V N-PE 800 V	L-N 2,500 V L-PE 1,500 V N-PE 1,200 V	L-L 4000 V L-G 2000 V	L-L 2,500 V L-N 1,500 V L-PE 2,500 V N-PE 1,500 V	DC+-DC-2,500 V PE-DC-1,500 V PE-DC+1,500 V				
Status Indication	Blue LED										
Technology	MOV with thermal dis	connect									
Lead Length	36"						30"				
Lead Size	#12										
Temperature	-40 to 176°F										
Enclosure Material	UL® 94V-0 Thermopla	astic, UL 50 Type 4	X								
Enclosure Rating	UL 50E Type 4X, NEW	1A 4X, IP65					NEMA®-4X				
Mounting	½" straight nipple						34" straight nipple				
Unit Weight	0.55 lb		0.85 lb	0.55 lb 0.85 lb			0.55 lb				
Certification Details	UL® 1449 Edition 5 Ty CSA C22.2 No. 269.1-	UL® 1449 Edition 5 for DC General Use, Solar PV									
Complies With	ANSI®/IEEE® C62.41.2	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C									
Dimensions H x D x W	2 ¾" x 3" x 4 ¾"										

### SES 160/320/360/480 Series






In this test (MIL-STD 220A), the filter is effective at reducing the amplitude of AC voltage signals, especially as a frequency of 500 kHz is approached. Attenuation across a range of frequencies appears to be consistent within the voltage range tested. Frequencies greater than 15 MHz resulted in the sinusoidal signal becoming distorted beyond recognition and the Vpp unable to be measured.

nVent ERICO has a range of specialized devices that are unmatched in capabilities and performance, including surge diversion, surge filtering and TD technology.

nVent ERICO product development creates innovative products backed with 100 years of industry experience. Our products go through rigorous testing and research to validate they are ready to protect your facility.

## Service Entrance Suppressor(B), 160 kA







The nVent ERICO SES160B Series of Surge Protective Devices (SPD) provide economical protection against damaging transients and surge currents. cUL® 1449 Listed SPD for Type 1 or Type 2 locations. Allows for installation on the line or load of the service panels, circuit breakers not required. With a 160 kA

#### **Features**


- 160 kA 8/20 µs maximum surge rating per phase
- Excellent clamping, low UL voltage protection
- Relay alarming for power/phase loss and surge protection device health
- Compact design can be directly mounted to panel or installed in a small space
- Optional Flush Plate and L-Bracket available
- 10 year limited warranty

per phase surge rating, the SES160B is well suited for category C locations. Applications include service entrance, distribution, branch panels, MMC, lighting panels, HVAC, and more. With a NEMA® 4X enclosure rating this product series is also well suited for outdoor applications.

Part Number	SES160 B120240SP	SES160 B120V	SES160 B208Y	SES160 B240D	SES160 B240V	SES160 B480D	SES160 B480Y	SES160B 120240D	SES160B 600Y			
Nominal System Voltage (Un)	120/240 V	120 V	120/208 V	240 V	240 V	480 V	277/480 V	120/240 V	347/600 V			
Distribution System	1Ph 3W+G	1Ph 2W+G	3Ph Y 4W+G	3Ph∆ 3W+G	1Ph 2W+G	3Ph∆ 3W+G	3Ph Y 4W+G	3Ph∆ 4W+G	3Ph Y 4W+G			
Max Continuous Operating Voltage (Uc)	180/360 V	180 V	150/300 V	275 V	350 V	550 V	350/700 V	180/275 V	440/880 V			
Frequency	0 - 600 Hz											
Short Circuit Current Rating (SCCR)	200 kA											
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μ	20 kA 8/20 μs										
Max Discharge Current (Imax), Per Phase	160 kA 8/20	μs										
Voltage Protection Rating (VPR), L-L	1,200 V	_	1,000 V	1,200 V	-	1,800 V	2,000 V	1,200 V 1,500 V	2,500 V			
Voltage Protection Rating (VPR), L-N	700 V	700 V	600 V	_	1,200 V	_	1,200 V	700 V 900 V	1,500 V			
Voltage Protection Rating (VPR), L-PE	700 V	700 V	700 V	1,000 V	1,000 V	1,800 V	1,000 V	700 V 1,000 V	1,500 V			
Voltage Protection Rating (VPR), N-PE	600 V	600 V	500 V	_	1,000 V	_	1,000 V	700 V 1,000 V	1,500 V			
Protection Modes	All modes pro	otected										
Status Indication	1 green LED p	per line; Audib	le alarm; Chan	ge-over conta	ct (Form C dry	y), 240 VAC/2A	4					
Remote Contact Switching Capacity	2.0 A @ 240	V										
Remote Contacts	Yes											
Lead Length	18"											
Lead Size	#12											
Temperature	-40 to 185°F											
Enclosure Material	Polycarbonat	te										
Enclosure Rating	NEMA®-4X; L	JL® 50E Type 4	1									
Mounting	¾" straight ni	pple										
Unit Weight	1.16 lb	1.16 lb										
Certification Details	CSA C22.2 N	o. 269.1; UL® 1	1449 Edition 5	Type 1/2, 20 k	A Mode							
Complies With			2 Cat A, Cat B, Cat A, Cat B, (		'IEEE® C62.41.	1-2002 Cat A,	Cat B, Cat C;					
Dimensions H x D x W	4.2" x 2.93" x	3 1/4"										

## Service Entrance Suppressor(F), 160 kA





The nVent ERICO SES160F Series is an enhanced version of the SES160B Series. The SES160F Surge-Filter is robust, with a 160 kA per phase surge rating. The high surge rating increases both survivability and life cycle. With the addition of a filter nuisance high frequency transients on the power distribution

#### **Features**


- Compact design can be directly mounted to panel or installed in a small space
- · Front-facing design eases installation and performance monitoring
- 160 kA 8/20  $\mu$ s maximum surge rating per phase
- Up to 57 dB attenuation (10 kHz to 100 MHz)
- Optional Flush Mounting Plate
- Ground reference monitoring triggers an alarm when N-PE mode exceeds 20 volts
- 10 year limited warranty

system are attenuated, protecting sensitive equipment. cUL® 1449 Listed SPD for Type 2 locations. Applications include service entrance, distribution, branch panels, MMC, lighting panels, HVAC, A/V systems, IT equipment, and more.

Part Number	SES160 F120240SP	SES160 F120V	SES160 F208Y	SES160 F240D	SES160 F240V	SES160 F480D	SES160 F480Y	SES160F 120240D	SES160F 600Y				
Nominal System Voltage (Un)	120/240 V	120 V	120/208 V	240 V	240 V	480 V	277/480 V	120/240 V	347/600 V				
Distribution System	1Ph 3W+G	1Ph 2W+G	3Ph Y 4W+G	3Ph∆ 3W+G	1Ph 2W+G	3Ph∆ 3W+G	3Ph Y 4W+G	3Ph∆ 4W+G	3Ph Y 4W+G				
Max Continuous Operating Voltage (Uc)	180/360 V	180 V	150/300 V	275 V	350 V	550 V	350/700 V	180/275 V	440/880 V				
Filtering	-40 dB @ 10	0 kHz											
Frequency	0 – 600 Hz												
Short Circuit Current Rating (SCCR)	200 kA	200 kA											
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μ	20 kA 8/20 μs											
Max Discharge Current (Imax), Per Phase	160 kA 8/20	μs											
Voltage Protection Rating (VPR), L-L	1,200 V	_	1,200 V	1,200 V	_	1,800 V	2,500 V	1,500 V 1,500 V	2500 V				
Voltage Protection Rating (VPR), L-N	700 V	700 V	700 V	_	1,200 V	_	1,200 V	8,00 V 1,000 V	1,500 V				
Voltage Protection Rating (VPR), L-PE	700 V	700 V	700 V	1,000 V	1,200 V	1,800 V	1,200 V	700 V 1,000 V	1,500 V				
Voltage Protection Rating (VPR), N-PE	600 V	700 V	600 V	_	1,000 V	_	1,000 V	700 V 1,000 V	1,500 V				
Protection Modes	All modes pro	otected											
Status Indication	1 green LED	per line; Audib	le alarm; Chan	ge-over conta	ct (Form C dr	y), 240 VAC/2A	4						
Remote Contact Switching Capacity	2.0 A @ 240	V											
Remote Contacts	Yes												
Lead Length	18"												
Lead Size	#12												
Temperature	-40 to 185°F												
Enclosure Material	Polycarbonat	te											
Enclosure Rating	NEMA®-4X; L	JL® 50E Type 4	4										
Mounting	¾" straight ni	pple											
Unit Weight	1.38 lb												
Certification Details	CSA C22.2 N	o. 269.2; UL®	1283 Edition 7	; UL® 1449 Edi	tion 5 Type 2,	20 kA Mode"							
Complies With	ANSI®/IEEE® Cat A, Cat B,		2 Cat A, Cat B,	Cat C; ANSI®,	/IEEE® C62.41	.1-2002 Cat A,	Cat B, Cat C; A	ANSI®/IEEE® C	62.45-2002				
Dimensions H x D x W	7.95" x 3.06"	x 2 ¾"											

## Service Entrance Suppressor(B), 320 kA







The nVent ERICO SES320 B Series of Surge Protective Devices (SPD) provides economical protection against damaging transients and surge currents. The B Series is a cUL 1449 listed SPD for Type 1 and Type 2 locations allowing for installation either on the line or load of service panels without requiring circuit breakers. With a 320 kA per phase surge rating, the

#### **Features**


- 320 kA 8/20 µs maximum surge rating per phase
- Excellent clamping, low UL voltage protection ratings
- Relay alarming for power/phase loss and surge protection device health
- Compact design can be directly mounted to panel or installed in a small space
- Ground reference monitoring triggers an alarm when N-PE mode exceeds 20 volts
- Optional Flush Mounting Plate
- 10-year limited warranty

SES320 B is well suited for category C locations. Typical applications for the nVent ERICO SES320 B Series include service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. Featuring a NEMA 4X enclosure rating, the B series is also appropriate for use in outdoor applications.

Part Number	SES320B 120240D	SES320B 120240SP	SES320B 120V	SES320B 208Y	SES320B 240D	SES320B 240V	SES320B 480D	SES320B 480Y	SES320B 600Y		
Nominal System Voltage (Un)	120/240 V		120 V	120/208 V	240 V		480 V	277/480 V	347/600 V		
Max Continuous Operating Voltage (Uc)	180/275 V	180/360 V	180 V	150/300 V	275 V	350 V	550 V	350/700 V	440/880 V		
Distribution System	3Ph∆ 4W+G	1Ph 3W+G	1Ph 2W+G	3Ph Y 4W+G	3Ph∆ 3W+G	1Ph 2W+G	3Ph∆ 3W+G	3Ph Y 4W+G	3Ph Y 4W+G		
Frequency	0 - 600 Hz										
Short Circuit Current Rating (SCCR)	200 kA										
Voltage Protection Rating (VPR), L-G	800/ 900 V	800 V		700 V	900 V	1,200 V	1,800 V	1,200 V	1500 V		
Voltage Protection Rating (VPR), L-L	1,200 V 1,500 V	1,200 V	_	1,000 V	1,200 V	_	1,800 V	2,000 V	2500 V		
Voltage Protection Rating (VPR), L-N	800 V 1,000 V	700 V		600 V	_	1,200 V	_	1,200 V	1500 V		
Voltage Protection Rating (VPR), N-G	700 V	600 V		700 V	_	1,000 V	_	1,000 V	1500 V		
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μ	20 kA 8/20 μs									
Max Discharge Current (Imax), Per Phase	320 kA 8/20	μs									
Protection Modes	All modes pro	otected									
Status Indication	1 green LED	per line; Dual c	color status LE	D, flashing red	d for faults; Au	dible alarm					
Remote Contact Switching Capacity	2.0 A @ 240	V									
Remote Contacts	Yes										
Lead Length	36"										
Lead Size	#10										
Temperature	-40 to 185°F	:									
Enclosure Material	Polycarbona	te									
Enclosure Rating	NEMA®-4X; L	JL® 50E Type 4	4								
Mounting	¾" straight ni	<sup>3</sup> / <sub>4</sub> " straight nipple									
Unit Weight	1.38 lb	1.38 lb									
Certification Details	CSA C22.2 N	o. 269.1; UL® 1	1449 Edition 5	Type 1/2, 20 k	:A Mode						
Complies With			2 Cat A, Cat B, Cat A, Cat B, C		/IEEE® C62.41.	1-2002 Cat A,	Cat B, Cat C				
Dimensions H x D x W	6.89" x 2.99"	x 8.38"									

# Service Entrance Suppressor(F), 320 kA







The nVent ERICO SES320 F Series of Surge Protective Devices (SPD) is an enhanced version of our nVent ERICO SES320B Series. The SES320 F Surge-Filter is robust and features a 320 kA per phase surge rating, increasing both survivability and overall life cycle. With the addition of a filter, bothersome high frequency transients on the power distribution system

#### **Features**


- · Compact design can be directly mounted to panel or installed in a small space
- · Front-facing design eases installation and performance monitoring
- 320 kA 8/20  $\mu$ s maximum surge rating per phase
- Up to 60 dB attenuation (10 kHz to 100 MHz)
- Ground reference monitoring triggers an alarm when N-PE mode exceeds 20 volts
- Optional Flush Mounting Plate
- 10-year limited warranty

are attenuated, therefore protecting sensitive equipment. The F Series is a cUL 1449 Listed SPD for Type 2 locations. Typical applications for the nVent ERICO SES320 F Series service entrances, distribution, branch panels, MCC, lighting panels, HVAC, A/V systems, IT equipment, and more.

Part Number	SES320F 120240D	SES320F 120240SP	SES320F 120V	SES320F 208Y	SES320F 240D	SES320F 240V	SES320F 480D	SES320F 480Y	SES320F 600Y		
Nominal System Voltage (Un)	120/240 V		120 V	120/208 V	240 V		480 V	277/480 V	347/600 V		
Max Continuous Operating Voltage (Uc)	180/275 V	180/360 V	180 V	150/300 V	275 V	350 V	550 V	350/700 V	440/880 V		
Distribution System	3Ph∆ 4W+G	1Ph 3W+G	1Ph 2W+G	3Ph Y 4W+G	3Ph∆ 3W+G	1Ph 2W+G	3Ph∆ 3W+G	3Ph Y 4W+G	3Ph Y 4W+G		
Filtering	-40 dB @ 10	00 kHz									
Frequency	0 – 600 Hz										
Short Circuit Current Rating (SCCR)	200 kA	200 kA									
Voltage Protection Rating (VPR), L-G	800 V 900 V	800 V		700 V	900 V	1,200 V	1,800 V	1,200 V	1500 V		
Voltage Protection Rating (VPR), L-L	1,200 V 1,500 V	1,200 V	_	1,000 V	1,200 V	_	1,800 V	2,000 V	2500 V		
Voltage Protection Rating (VPR), L-N	800 V 1,000 V	700 V		600 V	_	1,200 V	_	1,200 V	1500 V		
Voltage Protection Rating (VPR), N-G	700 V	600 V		700 V	_	1,000 V	_	1,000 V	1500 V		
Nominal Discharge Current (In), Per Mode	20 kA 8/20 µ	20 kA 8/20 μs									
Max Discharge Current (Imax), Per Phase	320 kA 8/20	μs									
Protection Modes	All modes pr	otected									
Status Indication	1 green LED	per line; Dual o	color status LE	D, flashing red	l for faults; Au	dible alarm					
Remote Contact Switching Capacity	2.0 A @ 240	V									
Remote Contacts	Yes										
Lead Length	36"										
Lead Size	#10										
Temperature	-40 to 185°F	-									
Enclosure Material	Polycarbona	te									
Enclosure Rating	NEMA®-4X; L	JL® 50E Type 4	4								
Mounting	34" straight ni	ipple									
Unit Weight	1.38 lb										
Certification Details	CSA C22.2 N	lo. 269.2; UL®	1283 Edition 7	; UL® 1449 Edi	tion 5 Type 2,	20 kA Mode					
Complies With				, Cat C; ANSI®, Cat C; Mil-Std 2		1-2002 Cat A,	Cat B, Cat C				
Dimensions H x D x W	6.89" x 2.99"	x 8.38"									

# Service Entrance Suppressor(BC), 320 kA









The nVent ERICO SES320 BC Series of Surge Protective Devices (SPD) provides economical protection against damaging transients and surge currents. The BC Series is a cUL 1449 listed SPD for Type 1 and Type 2 locations, allowing for installation either on the line or load of service panels without requiring circuit breakers. With a 320 kA per phase surge rating,

#### **Features**

- 320 kA 8/20 µs maximum surge rating per phase
- Excellent clamping and low UL voltage protection ratings
- Features relay alarming for power/phase loss and status of SPD health
- Compact design can be directly mounted to panel or installed in a small space
- Ground reference monitoring triggers an alarm when N-PE mode exceeds 20 volts
- Optional Flush Mounting Plate
- 10-year limited warranty
- Digital Surge Counter Utilizing Non-volatile Memory

the SES320 BC is well suited for category C locations. Typical applications for the nVent ERICO SES320 BC Series include service entrances, distribution, branch panels, MCC, lighting panels, HVAC and more. Featuring a NEMA 4X enclosure rating, the B series is also appropriate for use in outdoor applications.


Part Number	SES320 BC208Y	SES320 BC120V	SES320 BC120240S	SES320 BC120240D	SES320 BC240D	SES320 BC240V	SES320 BC480Y	SES320 BC480D				
Nominal System Voltage (Un)	120/208 V	120 V	120/240 V	120/240 V	240 V	240 V	277/480 V	480 V				
Max Continuous Operating Voltage (Uc)	150/300 V	180 V	180/360 V	180/275 V	275 V	350 V	350/700 V	550 V				
Distribution System Frequency	3Ph 4W+G 0 - 600 Hz	1Ph 2W+G	1Ph 3W+G	3Ph∆ 4W+G	3Ph∆ 3W+G	1Ph 2W+G	3Ph Y 4W+G	3Ph∆ 3W+G				
Short Circuit Current Rating (SCCR)	200 kA	200 kA										
Voltage Protection Rating (VPR), L-G	700 V	800 V	800 V	800 V, 900 V	900 V	1200 V	1200 V	1800 V				
Voltage Protection Rating (VPR), L-L	1000 V		1200 V	1200 V, 1500 V	1200 V		2000 V	1800 V				
Voltage Protection Rating (VPR), L-N	600 V	700 V	700 V	800 V, 1000 V		1200 V	1200 V					
Voltage Protection Rating (VPR), N-G	600 V	600 V	600 V	700 V		1000 V	1000 V					
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μs	20 kA 8/20 μs										
Max Discharge Current (Imax), Per Phase	320											
Status Indication	1 green LED pe	r line, Dual colo	r status LED, fla	shing red for fau	ults, Audible ala	rm, Surge count	er					
Remote Contacts	Yes											
Remote Contact Switching Capacity	2.0 A @ 240 V	A										
Lead Size	10											
Lead Length	36 in											
Temperature	-40 to 185°F											
Mounting	34" straight nipp	ole										
Enclosure Rating	NEMA®-4X, UL	<sup>®</sup> 50E Type 4										
Enclosure Material	Polycarbonate											
Unit Weight	1.38 lb	1.38 lb	1.38 lb	1.38 lb	1.38 lb min	1.38 lb	1.38 lb	1.38 lb				
Certification Details	CSA C22.2 No.	269.1, UL® 1449	Edition 5 Type	1/2, 20 kA Mod	e							
Complies With		ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C										
Dimensions H x D x W	6.89" x 2.99" x	8.38"										

# Service Entrance Suppressor(FC), 320 kA









The nVent ERICO SES320 FC Series of Surge Protective Devices (SPD) is an enhanced version of our nVent ERICO SES320BC Series. The robust SES320 FC Surge-Filter features a 320 kA per phase surge rating, increasing both survivability and overall life cycle. With the addition of a filter, bothersome high frequency transients on the power distribution system are attenuated,

#### **Features**

- · Compact design can be directly mounted to panel or installed in a small space
- · Front-facing design simplifies installation and performance monitoring
- 320 kA 8/20 µs maximum surge rating per phase
- Up to 60 dB attenuation (10 kHz to 100 MHz)
- Ground reference monitoring triggers an alarm when N-PE mode exceeds 20 volts
- Optional Flush Mounting Plate
- 10-year limited warranty
- Digital Surge Counter Utilizing Non-volatile Memory

ultimately protecting sensitive equipment. The FC Series is a cUL 1449 Listed SPD for Type 2 locations. Typical applications for the nVent ERICO SES320 FC Series service entrances, distribution, branch panels, MCC, lighting panels, HVAC, A/V systems, IT equipment and more.

Part Number	SES320 FC208Y	SES320 FC120V	SES320 FC120240S	SES320 FC120240D	SES320 FC240D	SES320 FC240V	SES320 FC480Y	SES320 FC480D		
Nominal System Voltage (Un)	120/208 V	120 V	120/240 V	120/240 V	240 V	240 V	277/480 V	480 V		
Max Continuous Operating Voltage (Uc)	150/300 V	180 V	180/360 V	180/275 V	275 V	350 V	350/700 V	550 V		
Distribution System	3Ph Y 4W+G	1Ph 2W+G	1Ph 3W+G	3Ph∆ 4W+G	3Ph∆ 3W+G	1Ph 2W+G	3Ph Y 4W+G	3Ph∆ 3W+G		
Frequency	0 – 600 Hz									
Filtering	-40 dB @ 100 kHz dB	-40 dB @ 100 kHz dB	-40 dB @ 100 kHz dB	-40 dB @ 100 kHz dB	-40 dB @ 100 kHz dB	-40 dB @ 100 kHz dB	-40 dB @ 100 kHz dB	-40 dB @ 100 kHz dB		
Short Circuit Current Rating (SCCR)	200 kA									
Voltage Protection Rating (VPR), L-G	700 V	800 V	800 V	800 V, 900 V	900 V	1200 V	1200 V	1800 V		
Voltage Protection Rating (VPR), L-L	1000 V		1200 V	1200 V, 1500 V	1200 V		2000 V	1800 V		
Voltage Protection Rating (VPR), L-N	600 V	700 V	700 V	800 V, 1000 V		1200 V	1200 V			
Voltage Protection Rating (VPR), N-G	600 V	600 V	600 V	700 V		1000 V	1000 V			
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μs									
Max Discharge Current (Imax), Per Phase	320									
Status Indication	1 green LED pe	r line, Dual colo	r status LED, fla	shing red for fau	ults, Audible alar	m, Surge count	er			
Remote Contacts	Yes									
Remote Contact Switching Capacity	2.0 A @ 240 V	A								
Lead Size	10									
Lead Length	36 in									
Temperature	-40 to 185°F									
Mounting	34" straight nipp	ole								
Enclosure Rating	NEMA®-4X, UL®	<sup>®</sup> 50E Type 4								
Enclosure Material	Polycarbonate									
Certification Details	CSA C22.2 No.	269.1, UL® 1449	Edition 5 Type	2, 20 kA Mode	JL® 1283 Edition	n 7				
Complies With	ANSI®/IEEE® C Cat A, Cat B, Ca		at A, Cat B, Cat (	C, ANSI®/IEEE® (	C62.41.1-2002 C	at A, Cat B, Cat	C, ANSI®/IEEE®	C62.45-2002		
Dimensions H x D x W	6.89" x 2.99" x	8.38"								
Unit Weight	1.38 lb	1.38 lb								

## Service Entrance Suppressor(DB), 360 kA







The nVent ERICO SES360 DB Series of Surge Protective Devices (SPD) provides economical protection against damaging transients and surge currents. The DB Series is a cUL 1449 listed SPD for Type 1 and Type 2 locations, allowing for installation either on the line or load of service panels without requiring circuit breakers. With a 360 kA per phase surge rating,

#### **Features**

- · Front-facing design simplifies installation and performance monitoring
- 360 kA 8/20 µs maximum surge rating per phase
- Advanced monitoring includes Surge and TOV Counters with time and date stamping
- Rotatable, full color graphics-based LCD utilizing a PIC Micro Controller
- Repetitive impulse tested to 10,000 strikes per mode
- · Rotary Disconnect included, standard for safe servicing
- 10-year limited warranty

the SES360 DB is well suited for category C locations. Typical applications for the nVent ERICO SES360 DB Series include service entrances, distribution, branch panels, MCC, lighting panels, HVAC and more. Featuring a NEMA 4 enclosure rating, the DB series is also appropriate for use in outdoor applications.

Part Number	SES360 DB208Y	SES360 DB120240S	SES360 DB120240D	SES360 DB240480S	SES360 DB240480D	SES360 DB480Y	SES360 DB600Y	SES360 DB480D				
Nominal System Voltage (Un)	120/208 V	120/240 V	120/240 V	240/480 V	240/480 V	277/480 V	347/600 V	480 V				
Max Continuous Operating Voltage (Uc)	150/300 V	175/350 V	175/275 V	320/550 V	350/550 V	320/700 V	420/880 V	550 V				
Distribution System	3Ph Y 4W+G	1Ph 3W+G	3Ph∆ 4W+G	1Ph 3W+G	3Ph∆ 4W+G	3Ph Y 4W+G	3Ph Y 4W+G	3Ph∆ 3W+G				
Frequency	0 - 600 Hz	– 600 Hz										
Short Circuit Current Rating (SCCR)	200 kA	200 kA										
Voltage Protection Rating (VPR), L-G	800 V	800 V	1000 V, 1000 V	1200 V	1800 V, 1800 V	1200 V	1500 V	1800 V				
Voltage Protection Rating (VPR), L-L	1000 V	1800 V	1200 V, 1500 V	2500 V	2000 V, 2500 V	2000 V	2500 V	1800 V				
Voltage Protection Rating (VPR), L-N	800 V	800 V	800 V, 1000 V	1200 V	1200 V, 1800 V	1200 V	1500 V	_				
Voltage Protection Rating (VPR), N-G	800 V	800 V	800 V	1200 V	1200 V	1200 V	1500 V	_				
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μs											
Max Discharge Current (Imax), Per Phase	360 kA 8/20 μs	3										
Status Indication	2 Tri Color LED with Time / Da		dible alarm with	n silence switch	, Graphics-based	d LCD with Rese	ettable Surge an	d TOV Counter				
Remote Contacts	Yes											
Remote Contact Switching Capacity	5.0 A @ 240 V	А										
Lead Size	#10 - #4											
Temperature	-31 to 167°F											
Mounting	Flange Mount											
Enclosure Rating	NEMA®-4, UL®	50E Type 4										
Enclosure Material	Metal											
Complies With			at A, Cat B, Cat on the NEC® Article		C62.41.1-2002 C	Cat A, Cat B, Cat	C, ANSI®/IEEE®	C62.45-2002				
Unit Weight	18.2 lb											
Certification Details	CSA C22.2 No.	269.1, UL® 1449	9 Edition 5 Type	1/2, 20 kA Mod	e							
Impulse Life	10,000 Impulse	10,000 Impulses at 10 kA 8/20 μs										
Dimensions H x D x W	16.79" x 13.19"	x 7.23"										

### Service Entrance Suppressor(DF), 360 kA







The nVent ERICO SES360 DF Series of Surge Protective Devices (SPD) is an enhanced version of our nVent ERICO SES360 DB Series. The robust SES360 DF Surge-Filter features a 360 kA per phase surge rating, increasing both survivability and overall life cycle. With the addition of a filter, bothersome high frequency transients on the power distribution system are attenuated,

#### **Features**

- Front-facing design simplifies installation and performance monitoring
- 360 kA 8/20 µs maximum surge rating per phase
- Up to 64 dB attenuation (10 kHz to 100 MHz)
- Advanced monitoring includes Surge and TOV Counters with time and date stamping
- Rotatable, full color graphics-based LCD utilizing a PIC Micro Controller
- Repetitive impulse tested to 10,000 strikes per mode
- · Rotary Disconnect included, standard for safe servicing
- 10-year limited warranty

ultimately protecting sensitive equipment. The DF Series is a cUL 1449 Listed SPD for Type 2 locations. Typical applications for the nVent ERICO SES360 DF Series service entrances, distribution, branch panels, MCC, lighting panels, HVAC, A/V systems, IT equipment and more.

Part Number	SES360 DF208Y	SES360 DF120240S	SES360 DF120240D	SES360 DF240480S	SES360 DF240480D	SES360 DF480Y	SES360 DF600Y	SES360 DF480D
Nominal System Voltage (Un)	120/208 V	120/240 V	120/240 V	240/480 V	240/480 V	277/480 V	347/600 V	480 V
Max Continuous Operating Voltage (Uc)	150/300 V	175/350 V	175/275 V	320/550 V	350/550 V	320/700 V	420/880 V	550 V
Distribution System	3Ph Y 4W+G	3Ph∆ 3W+G	3Ph∆ 4W+G	1Ph 3W+G	3Ph∆ 4W+G	3Ph Y 4W+G	3Ph Y 4W+G	3Ph∆ 3W+G
Frequency	0 - 600 Hz							
Filtering	-64 dB from 1	0 kHz to 100 MI	Ηz					
Short Circuit Current Rating (SCCR)	200 kA							
Voltage Protection Rating (VPR), L-G	800 V	800 V	1000 V, 1000 V	1200 V	1800 V, 1800 V	1200 V	1500 V	1800 V
Voltage Protection Rating (VPR), L-L	1000 V	1800 V	1200 V, 1500 V	2000 V	2000 V, 2500 V	2000 V	2500 V	1800 V
Voltage Protection Rating (VPR), L-N	800 V	800 V	800 V, 1000 V	1200 V	1200 V, 1800 V	1200 V	1500 V	_
Voltage Protection Rating (VPR), N-G	800 V	800 V	800 V, 800 V	1200 V	1200 V	1200 V	1500 V	_
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μs							
Max Discharge Current (Imax), Per Phase	360 kA 8/20 μ	S						
Status Indication	2 Tri Color LED with Time / Da		ıdible alarm witl	h silence switch	ı, Graphics-base	d LCD with Rese	ettable Surge ar	d TOV Counter
Remote Contacts	Yes							
Remote Contact Switching Capacity	5.0 A @ 240 V							
Lead Size	#10 - #6							
Temperature	-31 to 167°F							
Mounting	Flange Mount							
Enclosure Rating	NEMA ® -4; UL	50E Type 4						
Enclosure Material	Metal							
Unit Weight	8.255 kg min							
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C, UL® 96A and NEC® Article 285							
Certification Details	CSA C22.2 No.	. 269.1, UL® 144	9 Edition 5 Type	2, 20 kA Mode	, UL® 1283 Editio	on 7		
Impulse Life	10,000 Impulses at 10 kA 8/20 μs							
Dimensions H x D x W	16.79" x 13.19"	x 7.23"						

# Service Entrance Suppressor(DB), 480 kA







The nVent ERICO SES480 DB Series of Surge Protective Devices (SPD) provides economical protection against damaging transients and surge currents. The DB Series is a cUL 1449 listed SPD for Type 1 and Type 2 locations allowing for installation either on the line or load of service panels without requiring circuit breakers. With a 480 kA per phase surge rating,

#### **Features**

- Front-facing design simplifies installation and performance monitoring
- 480 kA 8/20 µs maximum surge rating per phase
- Advanced monitoring includes Surge and TOV Counters with time and date stamping
- Rotatable, full color graphics-based LCD utilizing a PIC Micro Controller
- Repetitive impulse tested to 10,000 strikes per mode
- Rotary Disconnect included, standard for safe servicing
- 10-year limited warranty

the SES480 DB is well suited for category C locations. Typical applications for the nVent ERICO SES480 DB Series include service entrances, distribution, branch panels, MCC, lighting panels, HVAC and more. Featuring a NEMA 4 enclosure rating, the DB series is also appropriate for use in outdoor applications.

Part Number	SES480 DB208Y	SES480 DB240480S	SES480 DB480Y	SES480 DB240480D	SES480 DB600Y	SES480 DB480D	SES480 DB600D		
Nominal System Voltage (Un)	120/208 V	240/480 V	277/480 V	240/480 V	347/600 V	480 V	600 V		
Max Continuous Operating Voltage (Uc)	150/300 V	320/550 V	320/700 V	320/550 V	420/880 V	550 V	680 V		
Distribution System	3Ph Y 4W+G	1Ph 3W+G	3Ph Y 4W+G	3Ph∆ 4W+G	3Ph Y 4W+G	3Ph∆ 3W+G	3Ph∆ 3W+G		
Frequency	0 - 600 Hz	0 – 600 Hz							
Short Circuit Current Rating (SCCR)	200 kA								
Voltage Protection Rating (VPR), L-G	800 V	1200 V	1200 V	1800 V, 1800 V	1500 V	1800 V	2000 V		
Voltage Protection Rating (VPR), L-L	1000 V	2500 V	2000 V	2000 V, 2500 V	2500 V	1800 V	1800 V		
Voltage Protection Rating (VPR), L-N	800 V	1200 V	1200 V	1200 V, 1800 V	1500 V	-	-		
Voltage Protection Rating (VPR), N-G	800 V	1200 V	1200 V	1200 V	1500 V	_	_		
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μs								
Max Discharge Current (Imax), Per Phase	480 kA 8/20 μs								
Status Indication		s per phase, Au ter with Time / I		n silence switch	, Graphics-base	d LCD with Rese	ettable Surge		
Remote Contacts	Yes								
Remote Contact Switching Capacity	5.0 A @ 240 V								
Lead Size	#10 - #4								
Temperature	-31 to 167°F								
Mounting	Flange Mount								
Enclosure Rating	NEMA®-4, UL®	50E Type 4							
Enclosure Material	Metal								
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C								
Unit Weight	18.2 lb								
Certification Details	CSA C22.2 No. 269.1, UL® 1449 Edition 5 Type 1/2, 20 kA Mode								
Impulse Life	10,000 Impulses at 10 kA 8/20 μs								
Dimensions H x D x W	16.79" x 13.19"	x 7.23"							

## Service Entrance Suppressor(DF), 480 kA







The nVent ERICO SES480 DF Series of Surge Protective Devices (SPD) is an enhanced version of our nVent ERICO SES480 DB Series. The robust SES480 DF Surge-Filter features a 480 kA per phase surge rating, increasing both survivability and overall life cycle. With the addition of a filter, bothersome high frequency transients on the power distribution system are

#### **Features**

- Front-facing design eases installation and performance monitoring
- 480 kA 8/20 µs maximum surge rating per phase
- Up to 64 dB attenuation (10 kHz to 100 MHz)
- Advanced monitoring includes Surge and TOV Counters with time and date stamping
- Rotatable, full color graphics-based LCD utilizing a PIC Micro Controller
- Repetitive impulse tested to 10,000 strikes per mode
- · Rotary Disconnect included, standard for safe servicing
- 10-year limited warranty

attenuated, ultimately protecting sensitive equipment. The DF Series is a cUL 1449 Listed SPD for Type 2 locations. Typical applications for the nVent ERICO SES480 DF Series service entrances, distribution, branch panels, MCC, lighting panels, HVAC, A/V systems, IT equipment and more.

Part Number	SES480 DF600D	SES480 DF240480S	SES480 DF240480D	SES480 DF208Y	SES480 DF480Y	SES480 DF600Y	SES480 DF480D			
Nominal System Voltage (Un)	600 V	240/480 V	240/480 V	120/208 V	277/480 V	347/600 V	480 V			
Distribution System	3Ph∆ 3W+G	1Ph 3W+G	3Ph∆ 4W+G	3Ph Y 4W+G	3Ph Y 4W+G	3Ph Y 4W+G	3Ph∆ 3W+G			
Frequency	0 - 600 Hz	•	•							
Filtering	-64 dB from 10	-64 dB from 10 kHz to 100 MHz								
Short Circuit Current Rating (SCCR)	200 kA									
Voltage Protection Rating (VPR), L-G	2000 V	1200 V	1800 V, 1800 V	800 V	1200 V	1500 V	1800 V			
Voltage Protection Rating (VPR), L-L	2000 V	2000 V	2000 V, 2500 V	1000 V	2000 V	2500 V	1800 V			
Voltage Protection Rating (VPR), L-N	_	1200 V	1200 V, 1800 V	800 V	1200 V	1500 V	-			
Voltage Protection Rating (VPR), N-G	_	1200 V	1800 V, 1800 V	800 V	1200 V	1500 V	_			
Nominal Discharge Current (In), Per Mode	20 kA 8/20 μs									
Max Discharge Current (Imax), Per Phase	480 kA 8/20 μs	480 kA 8/20 μs								
Status Indication	2 Tri Color LED and TOV Coun		udible alarm with Date Stamp	silence switch,	Graphics-based	LCD with Reset	ttable Surge			
Remote Contacts	Yes									
Remote Contact Switching Capacity	5.0 A @ 240 V									
Lead Size	#10 - #4									
Temperature	-31 to 167°F									
Mounting	Flange Mount									
Enclosure Rating	NEMA®-4, UL®	50E Type 4								
Enclosure Material	Metal									
Certification Details	CSA C22.2 No.	269.1, UL® 144	9 Edition 5 Type	2, 20 kA Mode,	UL® 1283 Edition	า 7				
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C, ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C									
Unit Weight	18.2 lb									
Impulse Life	10,000 Impulses at 10 kA 8/20 μs									
Dimensions H x D x W	16.79" x 13.19"	16.79" x 13.19" x 7.23"								

### **SES Accessories**



### **SES40 Accessories**



### SES40BRK

Mounting L-Bracket for SES40 Series



### SES40FP

SES40 flush plate kit for mounting behind drywall

### **SES40P Accessories**



### SES40PBRK

Mounting L-Bracket for SES40P Series



### SES40PFP

SES40P flush plate kit for mounting behind drywall

### **SES160 Accessories**



### SES160BFP

SES160B flush plate kit for mounting behind drywall



### SES160FFP

SES160F flush plate kit for mounting behind drywall



### SES160LBRACKET

Mounting L-Bracket for SES160 B & F Series

### **SES320 Accessories**




### SES320FP

SES320 Series flush plate kit for mounting behind drywall

### **SES200**

### Transient Discriminating Service Entrance Suppressor





The SES200 series of Transient Voltage Surge Suppressors deliver specification grade performance and features at an affordable price. The versatile and compact design provides high quality protection for a wide variety of commercial and industrial applications where sensitive electronic equipment is to be protected.

Internal electronics continuously monitor SPD protection, and the status is displayed on 5 segment LED bar graphs. Alarm contacts for remote monitoring are a standard feature.

The SES200 provides up to 200 kA 8/20 µs per mode of surge material, making it ideal for the protection of service entrance panels and helping to ensure a long operational life under severe lightning conditions.

#### **Features**

- 200 kA 8/20 µs primary protection rated for service entrance applications
- NEMA®-4X enclosure for harsh environments
- Internal high interrupt capacity fusing for added safety
- Modular design allows easy replacement of surge modules
- · Built in disconnect and fusing eliminates need for external fusina
- Transient Discriminating (TD) Technology provides increased service life
- Optional Filter and Surge Counter for enhanced protection
- UL® 1449 5th Edition
- 10-Year Warranty

The replaceable surge modules provide protection to L-N and N-G modes, delivering effective protection from both common mode and differential transients in single phase and three phase WYE systems. Models for grounded delta power systems provide L-L protection.

Transient Discriminating (TD) Technology, which meets the safety standards of UL 1449 Edition 5, provides a superior life by eliminating the common temporary over-voltage failure mode of most SPDs.

The SES is designed to mount adjacent to the service entrance panel with the connection being made via a small length of conduit.



SES200 metal enclosure option



SES200 without filter or surge counter options


Note: Ensure that installation of this model of the SES200 is not exposed to direct sunlight as solar radiation may cause internal temperatures to exceed the maximum specified and damage will result to the surge protective modules. A sun shield should be fitted if this unit is to be installed outdoors and exposed to sunlight.


### **SES200**

### Transient Discriminating Service Entrance Suppressor

Model	SES200 120/208	SES200 120/240	SES200 240D	SES200 277/480	SES200 120/208CM	SES200 120/240CM	SES200 240DCM	SES200 277/480CM		
Nominal Voltage, Un	120/208 V	120/240 V	220/240 V	277/480 V	120/208 V	120/240 V	220/240 V	277/480 V		
Distribution System	3Ph Y 4W+G	1Ph 3W+G	3Ph ∆ 3W+G	3Ph Y 4W+G		1Ph 3W+G	3Ph ∆ 3W+G	3Ph Y 4W+G		
System Compatibility(1)	TN-C, TN-S, TN	TN-C, TN-S, TN-C-S								
Max Cont. Operating Voltage, Uc	170/295 VAC	170/340 VAC	400 VAC	400/692 VAC	170/295 VAC	170/340 VAC	400 VAC	400/692 VAC		
Stand-off Voltage	240/415 V	240/480 V	275 V	480/831 V	240/415 V	240/480 V	275 V	480/831 V		
Frequency	50/60 Hz									
Operating Current @ Un	25 mA									
Aggregate Surge Rating	200kA (8/20µs	per line)								
Impulse Current, limp	20 kA 10/350 µ	IS								
Max Discharge Current, Imax	100 kA 8/20 μs	per line								
Nominal Discharge Current, In (UL)	20 kA 8/20 μs									
Protection Modes	All modes prote	ected	L-L	All modes prote	cted		L-L	All modes protected		
Technology	MOV/Silicon w	ith over-curren	t fusing; TD Tech	nology						
Short Circuit Current Rating	200 kAIC									
Voltage Protection Rating (VPR)	L-N 600 V @ 3 kA 800 V @ 20 kA		L-L 900 V @ 3 kA 1.0 kV @ 20 kA	L-N 900 V @ 3 kA 1.0 kV @ 20 kA	L-N 600 V @ 3 kA 800 V @ 20 k		L-L 900 V @ 3 kA 1.0 kV @ 20 kA	L-N 900 V @ 3 kA 1.0 kV @ 20 kA		
Filtering			'		-40 dB @ 100 kHz					
Status(2)	5 segment LED	bar graph per	phase		5 segment LE	D bar graph pe	er phase, surge co	ounter		
Dimensions H x D x W: mm (in)	406 x 190 x 30	5 (16 x 7.5 x 12)	)		406 x 190 x 3	55 (16 x 7.5 x 1	4)			
Weight: kg (lbs)	8 (17.64)				13 (28.66)					
Enclosure	IP66 (NEMA®-4	IX), Polycarbor	ate		IP66 (NEMA-4	4), Metal (Steel	)			
Connection	3 mm² to 35 m	m² (#12 AWG t	:o #2 AWG)		•					
Mounting	Wall mount									
Back-up Overcurrent Protection	Fused disconnect included in enclosure									
Temperature	-10°C to 60°C	-10°C to 60°C (14°F to 140°F)								
Approvals	NOM, UL® 1449	Edition 5 Liste	ed Type 1/2							
Surge Rated to Meet		62.41.2-2002 S		) ure 3, 100 kA 8/20	) μs, 10 kA 10/3	50 μs				

(2) Normally open contact, 250V~10A, ≤1.5 mm² (#16AWG) connecting wire.





ANSI is a registered trademark of the American National Standards Institute. IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers, Incorporated. NEMA is a registered trademark of the National Electrical Manufacturers Association. UL is a registered certification mark of UL LLC.

### DT Panel Protector (B), 120 kA





The nVent ERICO DTX120 Series of Surge Protective Devices (SPD) features a cUL 1449 listing and provides premium protection against damaging transients and surge currents, particularly in Type 1 and Type 2 locations. The innovative design allows for installation either on the line or load of the service panels and removes the need for circuit breakers (B

#### **Features**

- Excellent clamping and low UL voltage protection ratings
- Features relay alarming for power/phase loss and status of SPD health
- Design allows for easy removal and replacement of surge modules via lever assist
- RS-485 Interface Standard
- 10 Year Warranty

Version Only). With a 120 kA per phase surge rating, nVent ERICO DTX120 is well suited for category C locations and is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX120 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

Part Number	DTX120 B120240SP	DTX120 B120240HD	DTX120 B208Y	DTX120 B240D	DTX120 B480D	DTX120 B480Y		
Nominal System Voltage (Un)	120/240 V	120/240 V	120/208 V	240 VAC	480 V	277/480 V		
Max Continuous Operating Voltage (Uc)	150/300 VAC	150/275 VAC	150/300 VAC	275 VAC	510 VAC	350/700 VAC		
Distribution System	1Ph 3W+G	3Ph∆ 4W+G	3Ph 4W+G	3Ph∆ 3W+G	3Ph∆ 3W+G	3Ph 4W+G		
Protection Modes	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-PE	L-PE	L-N, L-PE, N-PE		
Frequency	50 - 60 Hz		1	1				
Short Circuit Current Rating (SCCR)	200 kA							
Nominal Discharge Current (In), UL	20 kA 8/20 μs							
Max Discharge Current (Imax), Per Phase	120 kA 8/20 μs							
Impulse Current (limp), Per Mode	12.5 kA 10/350 μ	S						
Voltage Protection Rating (VPR), L-G	700 V	1,200 V	700 V	1,000 V	1,800 V	1,200 V		
Voltage Protection Rating (VPR), L-L	1,000 V	1,500 V	1,200 V	1,000 V	1,800 V	2,000 V		
Voltage Protection Rating (VPR), L-N	700 V	800 V	700 V	-	-	1,200 V		
Voltage Protection Rating (VPR), N-G	700 V	1,500 V	600 V	_	_	1,200 V		
Status Indication	Audible alarm wi Surge/TOV Coun		Dual color status	LED, Mechanical fl	lag, OLED Display,	Resettable		
Technology	Hybrid technolog	y utilizing therma	l disconnects					
Remote Contacts	Yes (Form C)							
Temperature	-40 to 176°F							
Mounting	4 Screw Location	ns						
Enclosure Rating	NEMA 4X; UL 50	Е Туре 4						
Enclosure Material	Metal with PC Lie	d						
Certification Details	CSA C22.2 No. 2	69.2;UL® 1449 Edi	tion 5 Type 1/2, 20	) kA Mode				
Complies With		2.41.2-2002 Cat A, 02 Cat A, Cat B, C	Cat B, Cat C;ANSI at C	®/IEEE® C62.41.1-2	2002 Cat A, Cat B,	Cat C;ANSI®/		
Unit Weight	5.95 lb	6.4 lb	6.3 lb	6.15 lb	6.35 lb	6.78 lb		
Dimensions H x D x W	13.02" x 3.87" x 4				•			
Lead Size	#14 - #6							
Replacement Module	DT2180DTXM	DT2180DTXM DT2275DTXM	DT2150DTXM	DT2275DTXM	DT2510DTXM	DT2350M		

# DT Panel Protector (F), 120 kA





The nVent ERICO DTX120 Series of Surge Protective Devices (SPD) features a cUL 1449 listing and provides premium protection against damaging transients and surge currents, particularly in Type 1 and Type 2 locations. The innovative design allows for installation either on the line or load of the service panels and removes the need for circuit breakers (B

#### **Features**

- Excellent clamping and low UL voltage protection ratings
- Features relay alarming for power/phase loss and status of SPD health
- Design allows for easy removal and replacement of surge modules via lever assist
- · RS-485 Interface Standard
- Up to 53 dB attenuation (10 kHz to 100 MHz)
- 10 Year Warranty

Version Only). With a 120 kA per phase surge rating, nVent ERICO DTX120 is well suited for category C locations and is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX120 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

Part Number	DTX120 F120240SP	DTX120 F120240HD	DTX120 F208Y	DTX120 F240D	DTX120 F480D	DTX120 F480Y
Nominal System Voltage (Un)	120/240 V	120/240 V	120/208 V	240 VAC	480 V	277/480 V
Max Continuous Operating Voltage (Uc)	150/300 VAC	150/275 VAC	150/300 VAC	275 VAC	510 VAC	350/700 VAC
Distribution System	1Ph 3W+G	3Ph∆ 4W+G	3Ph 4W+G	3Ph∆ 3W+G	3Ph∆ 3W+G	3Ph 4W+G
Protection Modes	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-PE	L-PE	L-N, L-PE, N-PE
Frequency	50 - 60 Hz	•		•		
Short Circuit Current Rating (SCCR)	200 kA					
Nominal Discharge Current (In), UL	20 kA 8/20 μs					
Max Discharge Current (Imax), Per Phase	120 kA 8/20 μs					
Impulse Current (Iimp), Per Mode	12.5 kA 10/350 µ	S				
Filtering	-29 dB @ 100 kH	Hz				
Voltage Protection Rating (VPR), L-G	700 V	1,200 V	700 V	1,000 V	1,800 V	1,200 V
Voltage Protection Rating (VPR), L-L	1,000 V	1,500 V	1,200 V	1,000 V	1,800 V	2,000 V
Voltage Protection Rating (VPR), L-N	700 V	800 V	700 V	-	_	1,200 V
Voltage Protection Rating (VPR), N-G	700 V	1,500 V	600 V	-	_	1,200 V
Status Indication	Audible alarm wi Surge/TOV Cour		Dual color status	LED, Mechanical f	lag, OLED Display,	Resettable
Technology	Hybrid technolog	gy utilizing therma	l disconnects			
Remote Contacts	Yes (Form C)					
Temperature	-40 to 176°F					
Mounting	4 Screw Location	าร				
Enclosure Rating	NEMA 4X; UL 50	E Type 4				
Enclosure Material	Metal with PC Lie	d				
Certification Details	CSA C22.2 No. 2	69.2;UL® 1283 Ed	ition 7;UL® 1449 Ed	lition 5 Type 2, 20	kA Mode	
Complies With			Cat B, Cat C;ANSI at C;Mil-Std 220A	®/IEEE® C62.41.1-2	2002 Cat A, Cat B,	Cat C;ANSI®/
Unit Weight	6.4 lb	5.95 lb	6.3 lb	6.15 lb	6.35 lb	6.78 lb
Dimensions H x D x W	13.02" x 3.87" x 4					
Lead Size	#14 - #6					
Replacement Module	DT2180DTXM	DT2180DTXM DT2275DTXM	DT2150DTXM	DT2275DTXM	DT2510DTXM	DT2350M

### DT Panel Protector (B), 240 kA





The nVent ERICO DTX240 Series of Surge Protective Devices (SPD) features a cUL 1449 listing and provides premium protection against damaging transients and surge currents, particularly in Type 1 and Type 2 locations. The innovative design allows for installation either on the line or load of the service panels and removes the need for circuit breakers (B

#### **Features**

- Excellent clamping and low UL voltage protection ratings
- Features relay alarming for power/phase loss and status of SPD health
- Design allows for easy removal and replacement of surge modules via lever assist
- · RS-485 Interface Standard
- 10 Year Warranty

Version Only). With a 240 kA per phase surge rating, nVent ERICO DTX240 is well suited for category C locations and is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX240 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

	DTX240	DTX240	DTX240	DTX240	DTX240	DTX240	
Part Number	B120240SP	B120240HD	B208Y	B240D	B480D	B480Y	
Nominal System Voltage (Un)	120/240 V	120/240 V	120/208 V	240 VAC	480 V	277/480 V	
Max Continuous Operating Voltage (Uc)	150/300 VAC	150/275 VAC	150/300 VAC	275 VAC	510 VAC	350/700 VAC	
Distribution System	1Ph 3W+G	3Ph∆ 4W+G	3Ph 4W+G	3Ph∆ 3W+G	3Ph∆ 3W+G	3Ph 4W+G	
Protection Modes	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-PE	L-PE	L-N, L-PE, N-PE	
Frequency	50 – 60 Hz						
Short Circuit Current Rating (SCCR)	200 kA						
Nominal Discharge Current (In), UL	20 kA 8/20 μs						
Max Discharge Current (Imax), Per Phase	240 kA 8/20 μs						
Impulse Current (limp), Per Mode	12.5 kA 10/350 μ	S					
Voltage Protection Rating (VPR), L-G	700 V	1,200 V	700 V	1,000 V	1,800 V	1,200 V	
Voltage Protection Rating (VPR), L-L	1000 V	1,500 V	1,200 V	1,000 V	1,800 V	1,800 V	
Voltage Protection Rating (VPR), L-N	600 V	800 V	700 V	-	-	1,200 V	
Voltage Protection Rating (VPR), N-G	600 V	1,500 V	700 V	_	_	1,200 V	
Status Indication	Audible alarm wi Surge/TOV Coun		Dual color status	LED, Mechanical fl	lag, OLED Display,	Resettable	
Technology	Hybrid technolog	y utilizing therma	l disconnects				
Remote Contacts	Yes (Form C)						
Temperature	-40 to 176°F						
Mounting	8 Screw Location	ıs					
Enclosure Rating	NEMA 4X; UL 50	E Type 4					
Enclosure Material	Metal with PC Lic	t					
Certification Details	CSA C22.2 No. 2	69.2;UL® 1449 Edi	tion 5 Type 1/2, 20	) kA Mode			
Complies With		2.41.2-2002 Cat A, 02 Cat A, Cat B, C	Cat B, Cat C;ANSI at C	®/IEEE® C62.41.1-2	2002 Cat A, Cat B,	Cat C;ANSI®/	
Unit Weight	10.98 lb	11.86 lb	11.86 lb	11.42 lb	11.68 lb	12.02 lb	
Dimensions H x D x W	13.02" x 3.87" x 8	.76"			·	·	
Lead Size	#14 - #6						
Replacement Module	DT2180DTXM	DT2180DTXM DT2275DTXM	DT2150DTXM	DT2275DTXM	DT2510DTXM	DT2350M	

### DT Panel Protector (F), 240 kA





The nVent ERICO DTX240 Series of Surge Protective Devices (SPD) features a cUL 1449 listing and provides premium protection against damaging transients and surge currents, particularly in Type 1 and Type 2 locations. The innovative design allows for installation either on the line or load of the service panels and removes the need for circuit breakers (B

#### **Features**


- Excellent clamping and low UL voltage protection ratings
- Features relay alarming for power/phase loss and status of
- Design allows for easy removal and replacement of surge modules via lever assist
- RS-485 Interface Standard
- Up to 53 dB attenuation (10 kHz to 100 MHz)
- 10 Year Warranty

Version Only). With a 240 kA per phase surge rating, nVent ERICO DTX240 is well suited for category C locations and is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX240 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

Part Number	DTX240 F120240SP	DTX240 F120240HD	DTX240 F208Y	DTX240 F240D	DTX240 F480D	DTX240 F480Y
Nominal System Voltage (Un)	120/240 V	120/240 V	120/208 V	240 VAC	480 V	277/480 V
Max Continuous Operating Voltage (Uc)	150/300 VAC	150/275 VAC	150/300 VAC	275 VAC	510 VAC	350/700 VAC
Distribution System	1Ph 3W+G	3Ph∆ 4W+G	3Ph 4W+G	3Ph∆ 3W+G	3Ph∆ 3W+G	3Ph 4W+G
Protection Modes	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-N, L-PE, N-PE	L-PE	L-PE	L-N, L-PE, N-PE
Frequency	50 - 60 Hz				•	•
Short Circuit Current Rating (SCCR)	200 kA					
Nominal Discharge Current (In), UL	20 kA 8/20 μs					
Max Discharge Current (Imax), Per Phase	240 kA 8/20 µs					
Impulse Current (limp), Per Mode	12.5 kA 10/350 µ	S				
Filtering	-29 dB @ 100 kH	Hz				
Voltage Protection Rating (VPR), L-G	700 V	1,200 V	700 V	1,000 V	1,800 V	1,200 V
Voltage Protection Rating (VPR), L-L	1,200 V	1,500 V	1,200 V	1,000 V	1,800 V	1,800 V
Voltage Protection Rating (VPR), L-N	600 V	800 V	700 V	_	_	1,200 V
Voltage Protection Rating (VPR), N-G	600 V	1,500 V	700 V	-	_	1,200 V
Status Indication	Audible alarm wi Surge/TOV Cour		Dual color status	LED, Mechanical f	lag, OLED Display,	Resettable
Technology	Hybrid technolog	y utilizing therma	l disconnects			
Remote Contacts	Yes (Form C)					
Temperature	-40 to 176°F					
Mounting	8 Screw Location	าร				
Enclosure Rating	NEMA 4X; UL 50	E Type 4				
Enclosure Material	Metal with PC Lie	b				
Certification Details	CSA C22.2 No. 2	69.2;UL® 1283 Edi	tion 7;UL® 1449 Ec	lition 5 Type 2, 20	kA Mode	
Complies With		2.41.2-2002 Cat A, 02 Cat A, Cat B, C	Cat B, Cat C;ANSI at C;Mil-Std 220A	®/IEEE® C62.41.1-2	2002 Cat A, Cat B,	Cat C;ANSI®/
Unit Weight	10.98 lb	11.86 lb	11.86 lb	11.42 lb	11.68 lb	12.02 lb
Dimensions H x D x W	13.02" x 3.87" x 8	.76"				
Lead Size	#14 - #6					
Replacement Module	DT2180DTXM	DT2180DTXM DT2275DTXM	DT2150DTXM	DT2275DTXM	DT2510DTXM	DT2350M

### **TDX200 Transient Discriminating Panel Protection**





#### **Features**

- Transient Discriminating (TD) Technology provides increased service life
- · Modular design allows individual modes to be field replaceable, built-in disconnect and fusing eliminates need for external fusing
- Built-in features include TD Technology, thermal protection and short circuit current cartridge fusing
- · Compact NEMA®-4 enclosure design can be flush mounted or installed in a small space
- Status indication flag per mode, voltage presence LED's, audible alarm and voltage-free contacts providing remote status monitoring
- 200 kA 8/20 µs maximum surge rating provides protection suitable for service entrance, main-distribution panels and highly exposed applications
- · Available in various operating voltages to suit most common power distribution systems
- CE, UL® 1449 Edition 5 Listed, CSA-22.2 (347/600v model)
- 'S' Versions of the TDX200 include a surge counter and a surge filter

The TDX200 Series of Transient Voltage Surge Suppressors is designed for critical protection applications. The 200 kA 8/20 µs of surge protection exceeds the IEEE® C62.41.2 Scenario II single shot surge rating requirements for exposed service entrance locations - Exposure 3.

The NEMA-4 weather-tight housing allows the TDX to be installed on indoor or outdoor service panels. The preconfigured connecting leads simplify installation. The unique narrow

construction allows the SPD to fit between adjacent panel boards and connect via a 90-degree elbow. A flush mounting kit (p/n TDXM200FP) is also available for installing the SPD in drywall applications. A side mount kit (p/n TDXSM) is also available.

Listed as a Type 1 SPD to UL 1449 Edition 5, the TDX200 Series can be installed within a Type 1 or 2 location in accordance with the NEC® 2017



Typical installation



TDX200M Enclosure



TDX Replaceable Modules




TDX Replaceable Module backplane fully removed

### **TDX200 Transient Discriminating Panel Protection**

Part Number	TDX200M 120/208	TDX200M 120/240	TDX200M 277/480	TDX200M 347/600	TDX200M 120/240D	TDX200M 240D	TDX200M 480D	
Nominal System Voltage (Un)	120/208 V	120/240 V	277/480 V	347/600 V	120/240 V	240 VAC	480 V	
Distribution System	3Ph 4W+G	1Ph 3W+G	3Ph 4W+G		3Ph∆ 4W+G	3Ph∆ 3W+G	'	
Max Continuous Operating Voltage (Uc)	170/276 VAC	'	320/550 VAC	550/1100 VAC	170/276 VAC	276 VAC	550 VAC	
Stand-off Voltage	240/415 VAC	240/480 VAC	480/831 VAC	790/1370 VAC	240/415 VAC	415 VAC	790 VAC	
Frequency	50 - 60 Hz	'	'	•		'		
Short Circuit Current Rating (SCCR)	200 kA							
Nominal Discharge Current (In), IEC	40 kA 8/20 μs							
Nominal Discharge Current (In), UL	20 kA 8/20 μs							
Max Discharge Current (Imax), Per Phase	200 kA 8/20 μs							
Impulse Current (limp), Per Mode	25 kA 10/350 µs							
Voltage Protection Rating (VPR)	600 V @ 3 kA L-N 1,200 V @ 20 kA L	1,000 V 1,800 V				1,000 V @ 3 kA L-L 1,800 V @ 20 kA L-L	1,800 V @ 3 kA L-L 2,600 V @ 20 kA L-L	
Filtering (S Option)	-40dB @ 100 kHz	-40dB @ 100 kHz						
Protection Modes	L-N L-PE N-PE	L-N L-PE N-PE						
Status Indication	LED Mechanical f	LED Mechanical flag Audible alarm						
Surge Counter	Yes, S version	Yes, S version						
Technology	TD technology wi	th thermal disco	onnect Over-currer	nt replaceable cai	rtridge fusing			
Remote Contacts	Yes							
Lead Length	30"							
Lead Size	#10							
Ground Lead Length	36"							
Temperature	-40 to 176°F							
Enclosure Material	Metal							
Enclosure Rating	IP 65 NEMA®-4							
Mounting	3/4" straight nippl	le						
Dimensions H x D x W	9.45" x 3.07" x 5.1	2"						
Unit Weight	4.4 lb							
Certification Details	UL® 1449 Edition	5 Type 1/2, 20 k	A Mode		UL® 1449 Editio	on 5 Type 1/2, 20	) kA Mode	
Complies With		ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 µs, 10 kA 10/350 µs IEC® 61643-1 Class I, Class II						
Replacement Module	TDS150M150		TDS150M277	TDS150M560	TDS150M150 TDS150M240	TDS150M240	TDS150M560	
Certifications	CE; C-Tick UL			CE; C-Tick; cULus	CE; C-Tick			
Accessories	Flush Plate (TDXM	200FP), Side Mo	unt Kit (TDXSM), Fu	ise Replacement (	TDXFUSE)			


Delta and "S" models are Type 2 devices.



ANSI is a registered trademark of the American National Standards Institute. IEC is a registered trademark of the International Electrotechnical Commission. IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers, Incorporated. NEMA is a registered trademark of the National Electrical Manufacturers Association. UL is a registered certification mark of UL LLC.

### **TDX100 Transient Discriminating Panel Protection**





- Transient Discriminating (TD) Technology provides increased service life
- · Modular design allows individual modes to be field replaceable, built-in disconnect and fusing eliminates need for external fusing
- · Built-in features include TD Technology, thermal protection and short circuit current cartridge fusing
- Compact NEMA®-4 enclosure design can be flush mounted or installed in a small space
- · Status indication flag per mode, voltage presence LEDs, audible alarm and voltage-free contacts providing remote status monitoring
- 100 kA 8/20 µs maximum surge rating provides protection suitable for smaller main-distribution panels and an extended operational life
- Available in various operating voltages to suit most common power distribution systems
- CE, UL® 1449 Edition 5 Listed, CSA-22.2 (347/600v model)
- 'S' Versions of the TDX100 include a surge counter and a surge filter

The TDX100 Series of Transient Voltage Surge Suppressors is designed for critical protection applications. The 100 kA 8/20 µs of surge protection meets the IEEE® C62.41.2 Scenario II single shot surge rating requirements for exposed service entrance locations - Exposure 3.

The NEMA-4 weather tight housing allows the TDX to be installed on indoor or outdoor service panels. The preconfigured connecting leads simplify installation. The unique narrow

construction allows the SPD to fit between adjacent panel boards and connect via a 90-degree elbow. A flush mounting kit (p/n TDXM100FP) is also available for installing the SPD in drywall applications. A side mount kit (p/n TDXSM) is also available.

Listed as a Type 1 SPD to UL 1449 Edition 5, the TDX100 Series can be installed within a Type 1 or 2 location in accordance with the NEC® 2017.



Typical Installation



Output contacts



TDX Replaceable Cartridge overcurrent fuse protection




TDX Replaceable Modules

### **TDX100 Transient Discriminating Panel Protection**

Part Number	TDX100M120/208	TDX100M120/240	TDX100M277/480	TDX100M347/600	TDX100M120/240D	TDX100M240D	TDX100M480D
Nominal System Voltage (Un)	120/208 V	120/240 V	277/480 V	347/600 V	120/240 V	240 VAC	480 V
Distribution System	3Ph 4W+G	1Ph 3W+G	3Ph 4W+G	3Ph 4W+G	3Ph∆ 4W+G	3Ph∆ 3W+G	3Ph 3W+G
Max Continuous Operating Voltage (U <sub>c</sub> )	170/276 VAC		320/550 VAC	550/1100 VAC	170/276 VAC	276 VAC	550 VAC
Stand-off Voltage	240/415 VAC	240/480 VAC	480/831 VAC	790/1370 VAC	240/415 VAC	415 VAC	790 VAC
Frequency	50 - 60 Hz						
Short Circuit Current Rating (SCCR)	200 kA						
Nominal Discharge Current (In), IEC	40 kA 8/20 µs						
Nominal Discharge Current (In), UL	20 kA 8/20 μs						
Max Discharge Current (I <sub>max</sub> ), Per Phase	100 kA 8/20 μs						
Impulse Current (I <sub>imp</sub> ), Per Mode	12.5 kA 10/350 µs						
Voltage Protection Rating (VPR), L-L	1000V	1000V	1800V	4000V	1800V	1,000 V @ 3 kA 1,800 V @ 20 kA	1,800 V @ 3 kA 2,600 V @ 20 kA
Voltage Protection Rating (VPR), L-N	600 V @ 3 kA 1,200 V @ 20 kA		1,200 V @ 3 kA 1,800 V @ 20 kA	1,800 V @ 3 kA 2,600 V @ 20 kA	600 V @ 3 kA 1,200 V @ 20 kA	_	
Filtering (S Option)	-40dB @ 100 kHz						
Protection Modes	L-N L-PE N-PE						
Status Indication	LED, Mechanical fla	g, Audible alarm					
Surge Counter	Yes, S version						
Technology	TD technology with	thermal disconnect	Over-current replacea	ble cartridge fusing E	MI/RFI filter (S versions	3)	
Remote Contacts	Yes						
Lead Length	30"						
Lead Size	#10						
Ground Lead Length	36"						
Temperature	−40 to 176°F						
Enclosure Material	Metal						
Enclosure Rating	IP 65 NEMA®-4						
Mounting	3/4" straight nipple						
Dimensions H x D x W	9.45" x 3.07" x 3.31"						
Unit Weight	3.1 lb						
Certification Details	UL® 1449 Edition 5 7	Гуре 2, 20 kA Mode					
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μs, 10 kA 10/350 μs IEC® 61643-1 Class I, Class II						
Replacement Module	TDS150M150		TDS150M277	TDS150M560	TDS150M150 TDS150M240	TDS150M240	TDS150M560
Accessories	Flush Plate (TDXM1	00FP), Side Mount K	it (TDXSM), Fuse Rep	lacement (TDXFUSE)			


Delta and "S" models are Type 2 devices.



ANSI is a registered trademark of the American National Standards Institute. IEC is a registered trademark of the International Electrotechnical Commission. IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers, Incorporated. NEMA is a registered trademark of the National Electrical Manufacturers Association. UL is a registered certification mark of UL LLC.

### **TDX400S Transient Discriminating Panel Protection**







The TDX400 Series of Transient Voltage Surge Suppressors is designed for critical protection applications. The 400kA 8/20µs of surge protection exceeds the IEEE® C62.41.2 Scenario II single shot surge rating requirements for exposed service entrance locations - Exposure 3.

The NEMA®-12/3R weather-tight housing.

#### **Features**

- Transient Discriminating (TD) Technology provides increased service life
- · Modular design allows individual modes to be field replaceable, built-in disconnect and fusing eliminates need for external fusing
- Built-in features include TD Technology, thermal protection, short circuit current cartridge fusing and a surge counter
- Status indication flag per mode, voltage presence LED's, audible alarm, surge counter, and voltage-free contacts providing remote status monitoring
- · Available in various operating voltages to suit most common power distribution systems
- 400 kA 8/20 µs maximum surge rating provides protection suitable for service entrance, main-distribution panels and highly exposed applications
- CE, UL® 1449 Edition 5 Listed

The preconfigured connecting leads simplify installation. The unique narrow construction allows the SPD to fit between adjacent panel boards and connect via a 90-degree elbow.


Listed as a Type 1 SPD to UL 1449 Edition 5, the TDX400 Series can be installed within a Type 1 or 2 location in accordance with the NEC® 2017, Article 285.

Part Number	TDX400S120/208	TDX400S120/240	TDX400S277/480				
Nominal System Voltage (U <sub>n</sub> )	120/208 V	120/240 V	277/480 V				
Distribution System	3Ph 4W+G	1Ph 3W+G	3Ph 4W+G				
Max Continuous Operating Voltage (Uc)	170/276 VAC		320/550 VAC				
Stand-off Voltage	240/415 VAC	240/480 VAC	480/831 VAC				
Frequency	50 - 60 Hz						
Short Circuit Current Rating (SCCR)	200 kA						
Nominal Discharge Current (In), IEC	40 kA 8/20 μs						
Nominal Discharge Current (In), UL	20 kA 8/20 μs						
Max Discharge Current (I <sub>max</sub> ), Per Phase	400 kA 8/20 μs						
Impulse Current (I <sub>imp</sub> ), Per Mode	25 kA 10/350 μs						
Voltage Protection Rating (VPR), L-N	800 V @ 3 kA		1,200 V @ 3 kA				
Protection Modes	L-N L-PE N-PE						
Status Indication	LED, Mechanical flag Audible alarm						
Surge Counter	Yes						
Technology	TD technology with thermal disc	connect Over-current replaceable	cartridge fusing				
Remote Contacts	Yes						
Lead Length	30"						
Lead Size	#10						
Ground Lead Length	36"						
Temperature	-40 to 176°F						
Enclosure Material	Metal						
Enclosure Rating	IP 20 NEMA®-12/3R						
Mounting	¾" straight nipple						
Dimensions H x D x W	10.40" x 3.25" x 10.32"						
Unit Weight	14 lb						
Certification Details	UL® 1449 Edition 5 Type 1/2, 20	kA Mode					
Complies With	ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μs, 10 kA 10/350 μs IEC® 61643-1 Class I, Class II						
Replacement Module	TDS150M150		TDS150M277				

ANSI is a registered trademark of the American National Standards Institute. IEC is a registered trademark of the International Electrotechnical Commission IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers, Incorporated. NEMA is a registered trademark of the National Electrical Manufacturers Association UL is a registered certification mark of UL LLC

### **TDX300S Transient Discriminating Panel Protection**







The TDX300 Series of Transient Voltage Surge Suppressors is designed for critical protection applications. The 300kA 8/20µs of surge protection exceeds the IEEE® C62.41.2 Scenario II single shot surge rating requirements for exposed service entrance locations – Exposure 3.

The NEMA®-12/3R weather-tight housing.

#### **Features**

- Transient Discriminating (TD) Technology provides increased service life
- Modular design allows individual modes to be field replaceable, built-in disconnect and fusing eliminates need for external fusing
- Built-in features include TD Technology, thermal protection, short circuit current cartridge fusing and surge counter
- Status indication flag per mode, voltage presence LED's, audible alarm surge counter and voltage-free contacts providing remote status monitoring
- Available in various operating voltages to suit most common power distribution systems
- 300 kA 8/20 µs maximum surge rating provides protection suitable for service entrance, main-distribution panels and highly exposed applications
- CE, UL® 1449 Edition 5 Listed

The preconfigured connecting leads simplify installation. The unique narrow construction allows the SPD to fit between adjacent panel boards and connect via a 90-degree elbow.


Listed as a Type 1 SPD to UL 1449 Edition 5, the TDX300 Series can be installed within a Type 1 or 2 location in accordance with the NEC® 2017.

Part Number	TDX300S120/208	TDX300S120/240	TDX300S277/480			
Nominal System Voltage (Un)	120/208 V	120/240 V	277/480 V			
Distribution System	3Ph 4W+G	1Ph 3W+G	3Ph 4W+G			
Max Continuous Operating Voltage (Uc)	170/276 VAC		320/550 VAC			
Stand-off Voltage	240/415 V	240/480 V	480/831 V			
Frequency	50 - 60 Hz					
Short Circuit Current Rating (SCCR)	200 kA					
Nominal Discharge Current (In), IEC	40 kA 8/20 μs					
Nominal Discharge Current (In), UL	20 kA 8/20 μs					
Max Discharge Current (I <sub>max</sub> ), Per Phase	300 kA 8/20 μs					
Impulse Current (I <sub>imp</sub> ), Per Mode	23 kA 10/350 μs					
Voltage Protection Rating (VPR), L-N	800 V @ 3 kA		1,200 V @ 3 kA			
Protection Modes	L-N L-PE N-PE					
Status Indication	LED, Mechanical flag Aud	ible alarm				
Surge Counter	Yes					
Technology	TD technology with therm	nal disconnect Over-current repla	ceable cartridge fusing			
Remote Contacts	Yes					
Lead Length	30"					
Lead Size	#10					
Ground Lead Length	36"					
Temperature	-40 to 176°F					
Enclosure Material	Metal					
Enclosure Rating	IP 20 NEMA®-12/3R					
Mounting	34" straight nipple					
Dimensions H x D x W	10.40" x 3.25" x 10.32"					
Unit Weight	13 lb					
Certification Details	UL® 1449 Edition 5 Type 1	/2, 20 kA Mode				
Complies With	ANSI®/IEEE® C62.41.2-20 IEC® 61643-1 Class I, Clas	ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μs, 10 kA 10/350 μs IEC® 61643-1 Class I, Class II				
Replacement Module	TDS150M150		TDS150M277			


ANSI is a registered trademark of the American National Standards Institute. IEC is a registered trademark of the International Electrotechnical Commission. IEEE is a registered trademark of the Institute of Electrical and Electronics Engineers, Incorporated. NEMA is a registered trademark of the National Electrical Manufacturers Association.

UL is a registered certification mark of UL LLC.

# Rail Primary Power Surge Protector





- Modular design allows easy replacement of surge modules
- Terminals provided within panel
- Viewing window for safe inspection
- Internal high interrupt capacity fusing for added safety




Part Number	EPD100HZ120240V	EPD100HZ120S	EPD100HZ120V				
Nominal System Voltage (Un)	120/240 V	120 VAC					
Max Continuous Operating Voltage (Uc)	150/300 VAC	0 VAC 150 VAC					
Max Discharge Current (Imax), Per Mode	15 kA 8/20 μs	15 kA 8/20 µs					
Nominal Discharge Current (In), Per Mode	40 kA 8/20 μs	40 kA 8/20 μs					
Frequency	0 – 100 Hz						
Voltage Protection Level (Up)	1,400 V @ 15 kA	1,400 V @ 15 kA 1,200 V @ 15 kA					
Short Circuit Current Rating (SCCR)	25 kA	·					
Connection, Stranded	#16 - #4	#14 - 2/0	#16 - #4				
Protection Modes	Differential Common						
Status Indication	Mechanical flag	Mechanical flag					
Technology	MOV with thermal discor	MOV with thermal disconnect					
Humidity	0 - 90 % RH	0 - 90 % RH					
Temperature	-40 to 176°F	-40 to 176°F					
Enclosure Material	Metal						
Enclosure Rating	NEMA®-4						
Depth (D)	4.6"						
Height (H)	8"						
Width (W)	11 ½"						
Unit Weight	12 lb						
Complies With	ANSI®/IEEE® C62.41.2-20	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C; AREMA® requirements					

# Rail Primary Power Surge Protector with Flying Lead






- Uses a hybrid Transient Voltage Surge Suppression (TVSS) filter device that incorporates TD technology
- Capacitive filtering and voltage dependent metal oxide varistors provide high-energy surge suppression
- Active parallel filter removes common disturbances in electrical environment
- Flying lead monitors status of surge suppression components in each phase




Part Number	EPD120/240TDFL
Nominal System Voltage (Un)	120/240 V
Max Continuous Operating Voltage (Uc)	150/300 VAC
Stand-off Voltage	240/480 VAC
Frequency	50 – 60 Hz
Aggregate Surge Rating	206 kA 8/20 μs
Voltage Protection Level (Up)	600 V @ 10 kA L-N; 870 V @ 20 kA L-N; 450 V @ 3 kA L-N; 400 V @ 500 A
Short Circuit Current Rating (SCCR)	200 kA
Filtering	-40 dB @ 100 kHz
Lead Length	24"
Lead Size	#12
Distribution System	1Ph 3W+G
Protection Modes	L-N; L-PE
Status Indication	LED
Technology	TD technology with EMI/RFI filter
Mounting	½" straight nipple
Humidity	0 – 90 % RH
Temperature	-40 to 158°F
Enclosure Material	Metal
Enclosure Rating	NEMA®-1
Depth (D)	4.3"
Height (H)	6.3"
Width (W)	6.3"
Unit Weight	6 lb
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C; ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 2, 50 kA 8/20 µs; AREMA® requirements

# Rail Secondary Power Surge Protector, AC Circuits




- Transient Discriminating (TD) technology helps ensure safe operation during abnormal over-voltage events
- Hybrid TVSS technology
- Low let-through voltage
- Sine wave filter for RFI/EMI attenuation





Part Number	EPD120TDAARB
Nominal System Voltage (Un)	120 V
Max Continuous Operating Voltage (Uc)	150 VAC
Rated Load Current (IL)	30 A
Frequency	50 – 60 Hz
Filtering	−65 dB @ 100 kHz
Aggregate Surge Rating	20 kA 8/20 μs
Distribution System	1Ph 2W+G
Protection Modes	L-N
Technology	TD technology with thermal disconnect; EMI/RFI filter
Connection Type	AAR Terminals
Status Indication	LED
Humidity	0 – 90 % RH
Temperature	-40 to 158°F
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20; NEMA®-1
Depth (D)	4 34"
Height (H)	2 %"
Width (W)	5 34"
Unit Weight	2.5 lb
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C
Standard Packaging Quantity	1 pc

# Rail Secondary Power Surge Protector, DC Circuits











- Hybrid TVSS technology
- High surge rating provides a high level of protection and long operational life
- Internal patented thermal disconnect system designed specifically for operation of DC systems to assist safe disconnect at end of life
- Low let-through voltage
- Sine wave filter for RFI/EMI attenuation




Part Number	EPD1224ATAAR1
Nominal System Voltage (Un)	12 VDC; 24 VDC
Max Continuous Operating Voltage (Uc), 12 VDC	18 VDC
Max Continuous Operating Voltage (Uc), 24 VDC	36 VDC
Voltage Protection Level, 12 VDC (Up)	34 V @ 20 kA
Voltage Protection Level, 24 VDC (Up)	41 V @ 20 kA
Rated Load Current (IL)	30 A; 60 A
Filtering	-65 dB @ 100 kHz
Distribution System	Two wire
Aggregate Surge Rating	20 kA 8/20 μs
Status Indication	LED
Technology	Metal Oxide Varistor (MOV); Silicon Avalanche Diode (SAD); In-line series filter
Connection Type	AAR Terminals
Protection Modes	-ve to +ve
Humidity	0 – 90 % RH
Temperature	−40 to 158°F
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20; NEMA®-1
Depth (D)	4.73"
Height (H)	2.37"
Width (W)	4.73"
Unit Weight	1.92 lb
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C; AREMA® requirements

### DT and EDT SPD Features



## DT1 DIN Rail Surge Protection IEC Class I+II, 1+0 Mode





#### **Features**

- · Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

**Certification Details:** IEC 61643-11 Class I+II,

EN 61643-11 Type 1+2

UL 1449, 5th Edition Type 1CA

IEC 61643-11:2011 Complies with:

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4

**Protection Modes:** L-PE, N-PE (only TN-S),


L-PE/N, L-N, L-L



Part Number	DT17510R	DT115010R	DT130010R	DT135010R	DT148010R	DT175010R	
UL Electrical	60)/	1001/	0.40)/	077) /	400)/	6001/	
UL Nominal Voltage Maximum Continuous Operating Voltage (AC)	60V	120V	240V	277V	400V	600V	
MCOV	75V	150V	300V	350V	480V	750V	
Voltage Protection Rating VPR	330V	500V	900V	1200V	1500V	2500V	
Nominal Discharge Current (8/20 µs) In	20 kA	20 kA	20 kA	20 kA	20 kA	20 kA	
Short-Circuit Current Rating (AC) SCCR	100 kA	200 kA	150 kA	150 kA	200 kA	150 kA	
IEC Electrical							
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	60V	120V	240V	277V	400V	600V	
Maximum Continuous Operating Voltage (AC) Uc	75V	150V	300V	350V	480V	750V	
Nominal Discharge Current (8/20 µs) In	20 kA						
Maximum Discharge Current (8/20 μs) I <sub>max</sub>	100 kA	100 kA	100 kA	100 kA	100 kA	60 kA	
Impulse Discharge Current (10/350 μs) I <sub>imp</sub>	12.5 kA	12.5 kA	12.5 kA	12.5 kA	10 kA	5 kA	
Specific Energy W/R	39 kJ/Ω	39 kJ/Ω	39 kJ/Ω	39 kJ/Ω	25 kJ/Ω	6.25 kJ/Ω	
Charge Q	6.25 As	6.25 As	6.25 As	6.25 As	5 As	2.5 As	
Voltage Protection Level Up	700V	1000V	1400V	1500V	2000V	2700V	
Response Time t <sub>A</sub>	< 25 ns						
Back-Up Fuse (max)	315A / 250A go	G				250A gG	
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA					50 kA	
TOV Withstand 5s U <sub>T</sub>	114V	175V	337V	403V	581V	871V	
TOV 120 min U <sub>T/mode</sub>	114V/withstand	229V/safe fail	442V/safe fail	529V/safe fail	762V/safe fail	1143/safe fa	
Number of Ports	1					'	
Mechanical							
Operating Temperature Range T <sub>a</sub>	-31°F to 185°F	(-35°C to 85°C	)				
Permissible Operating Humidity RH	5%95%	•	,				
Altitude	6562 ft [2000 r	m]					
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5	Nm]					
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid)	) / 25 mm² (Strai	nded) , 2 AWG (S	solid) / 4 AWG (S	tranded)		
Mounting	35 mm DIN Ra	il, EN 60715		·	·		
Degree of Protection	IP 20						
Housing Material	Thermoplastic: Extinguishing Degree UL 94 V-0						
Thermal Protection	Yes						
Operating State / Fault Indication	Green Flag / N	ot Green Flag					
Remote Contacts (RC)	Yes	-					
RC Switching Capacity	AC: 250V/ 1A,	125V/ 1A; DC: 48	V/0.5A, 24V/0.5	A, 12V/0.5A			
RC Conductor Cross Section (max)		) / 16 AWG (Solid					
Single Unit Weight pounds	0.371	0.371	0.402	0.437	0.446	0.452	
Single Unit Weight grams	168	168	182	198	202	205	

## DT1 DIN Rail Surge Protection IEC Class I+II, 2+0 Mode





### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

**Certification Details:** IEC 61643-11 Class I+II

EN 61643-11 Type 1+2

UL 1449, 5th Edition Type 1CA

Complies with: IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4


**Protection Modes:** L-PE, N-PE, L-L

<b>C</b> € ♠	c FNI US
--------------	----------

Part Number	DT115020R	DT130020R	DT135020R	DT175020R
UL Electrical				
UL Nominal Voltage	240/120V 1S 208/120V 3Y	415/240V 3Y 240V 3D	480/277V 3Y 240V 3D	347/600V 3Y
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	750V/1500V
Voltage Protection Rating VPR	500V/1000V	900V/1800V	1200V/2000V	2500V/5000V
Nominal Discharge Current (8/20 µs) I <sub>n</sub>	20 kA	20 kA	20 kA	20 kA
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	150 kA	150 kA
IEC Electrical				
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	120V	240V	277V	600V
Maximum Continuous Operating Voltage (AC) U <sub>c</sub>	150V	300V	350V	750V
Nominal Discharge Current (8/20 µs) In	20 kA			
Maximum Discharge Current (8/20 μs) I <sub>max</sub>	100 kA	100 kA	100 kA	60 kA
Impulse Discharge Current (10/350 µs) I <sub>imp</sub>	12.5 kA	12.5 kA	12.5 kA	5 kA
Specific Energy W/R	39 kJ/Ω	39 kJ/Ω	39 kJ/Ω	6.25 kJ/Ω
Charge Q	6.25 As	6.25 As	6.25 As	2.5 As
Voltage Protection Level Up	1000V	1400V	1500V	2700V
Response Time t <sub>A</sub>	< 25 ns		'	
Back-Up Fuse (max)	315A / 250A gG		250A gG	
Short-Circuit Current Rating (AC) ISCCR	25 kA / 50 kA			50 kA
TOV Withstand 5s U <sub>T</sub>	175V	337V	403V	871V
TOV 120 min U <sub>T/mode</sub>	229V/safe fail	442V/safe fail	529V/safe fail	1143/safe fail
Number of Ports	1			
Mechanical				
Operating Temperature Range T <sub>a</sub>	-31°F to 185°F (-35°C	C to 85°C)		
Permissible Operating Humidity RH	5%95%			
Altitude	6562 ft [2000 m]			
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5 Nm]			
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid) / 25 m	m² (Stranded), 2 AWG (	Solid) / 4 AWG (Stranded	d)
Mounting	35 mm DIN Rail, EN 60	0715		
Degree of Protection	IP 20			
Housing Material	Thermoplastic: Extingi	uishing Degree UL 94 V	-0	
Thermal Protection	Yes			
Operating State / Fault Indication	Green Flag / Not Green	n Flag		
Remote Contacts (RC)	Yes			
RC Switching Capacity	AC: 250V/ 1A, 125V/ 1A	A; DC: 48V/0.5A, 24V/0.	5A, 12V/0.5A	
RC Conductor Cross Section (max)	1.5 mm <sup>2</sup> (Solid) / 16 AV			
Single Unit Weight pounds	0.717	0.779	0.849	0.880
Single Unit Weight grams	325	353	385	399

### DT1 DIN Rail Surge Protection IEC Class I+II, 3+0 Mode





### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

**Certification Details:** IEC 61643-11 Class I+II

EN 61643-11 Type 1+2 UL 1449, 5th Edition Type 1CA

Complies with: IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4


**Protection Modes:** L-PE, N-PE, L-L



Part Number	DT115030R	DT130030R	DT135030R	DT148030R	DT175030R	
UL Electrical						
UL Nominal Voltage	208/120V 3Y 240/120V 1S	415/240 3Y 240V 3D	480/277V 3Y	690/400V 3Y	600V 3D 480V 3D	
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	480V/960V	750V/1500V	
Voltage Protection Rating VPR	500V/1000V	900V/1800V	1200V/2000V	1500V/3000V	2500V/5000V	
Nominal Discharge Current (8/20 µs) In	20 kA	20 kA	20 kA	20 kA	20 kA	
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	150 kA	200 kA	150 kA	
EC Electrical						
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	120V	240V	277V	400V	600V	
Maximum Continuous Operating Voltage (AC) U <sub>c</sub>	150V	300V	350V	480V	750V	
Nominal Discharge Current (8/20 µs) In	20 kA	·	•			
Maximum Discharge Current (8/20 μs) I <sub>max</sub>	100 kA	100 kA	100 kA	100 kA	60 kA	
Impulse Discharge Current (10/350 µs) I <sub>imp</sub>	12.5 kA	12.5 kA	12.5 kA	10 kA	5 kA	
Specific Energy W/R	39 kJ/Ω	39 kJ/Ω	39 kJ/Ω	25 kJ/Ω	6.25 kJ/Ω	
Charge Q	6.25 As	6.25 As	6.25 As	5 As	2.5 As	
/oltage Protection Level U <sub>p</sub>	1000V	1400V	1500V	2000V	2700V	
Response Time t <sub>A</sub>	< 25 ns					
Back-Up Fuse (max)	315A / 250A gG 250A gG					
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA				50 kA	
TOV Withstand 5s U <sub>™</sub>	175V	337V	403V	581V	871V	
TOV 120 min U <sub>T/mode</sub>	229V/safe fail	442V/safe fail	529V/safe fail	762V/safe fail	1143/safe fail	
Number of Ports	1					
Mechanical						
Operating Temperature Range T <sub>a</sub>	-31°F to 185°F (	(-35°C to 85°C)				
Permissible Operating Humidity RH	5%95%					
Altitude	6562 ft [2000 m	]				
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5 N	lm]				
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid)	<sup>25</sup> mm <sup>2</sup> (Stranded	d), 2 AWG (Solid) /	4 AWG (Stranded)		
Mounting	35 mm DIN Rail	, EN 60715				
Degree of Protection	IP 20					
Housing Material	Thermoplastic: I	Extinguishing Degr	ee UL 94 V-0			
Thermal Protection	Yes					
Operating State / Fault Indication	Green Flag / No	t Green Flag				
Remote Contacts (RC)	Yes					
RC Switching Capacity	AC: 250V/ 1A, 12	25V/ 1A; DC: 48V/0	.5A, 24V/0.5A, 12V	7/0.5A		
RC Conductor Cross Section (max)	1.5 mm <sup>2</sup> (Solid)	/ 16 AWG (Solid)				
Single Unit Weight pounds	1.041	1.133	1.239	1.266	1.286	
Single Unit Weight grams	472	514	562	574	583	

### DT1 DIN Rail Surge Protection IEC Class I+II, 4+0 Mode





### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

Certification Details: IEC 61643-11 Class I+II

EN 61643-11 Type 1+2

UL 1449, 5th Edition Type 1CA

**Complies with:** IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4

**Protection Modes:** L-PE, N-PE, L-L


# CE & cRus

Part Number	DT115040R	DT130040R	DT135040R	DT148040R		
UL Electrical	<u>'</u>	'		<u>'</u>		
UL Nominal Voltage	208/120V 3Y	415/240 3Y	480/277V 3Y	690/400V 3Y		
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	480V/960V		
Voltage Protection Rating VPR	500V/1000V	900V/1800V	1200V/2000V	1500V/2500V		
Nominal Discharge Current (8/20 µs) In	20 kA	20 kA	20 kA	20 kA		
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	150 kA	200 kA		
IEC Electrical						
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	120V	240V	277V	400V		
Maximum Continuous Operating Voltage (AC) U <sub>c</sub>	150V	300V	350V	480V		
Nominal Discharge Current (8/20 µs) In	20 kA		'			
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	100 kA	100 kA	100 kA	100 kA		
Impulse Discharge Current (10/350 µs) I <sub>imp</sub>	12.5 kA	12.5 kA	12.5 kA	10 kA		
Specific Energy W/R	39 kJ/Ω	39 kJ/Ω	39 kJ/Ω	25 kJ/Ω		
Charge Q	6.25 As	6.25 As	6.25 As	5 As		
Voltage Protection Level Up	1000V	1400V	1500V	2000V		
Response Time t <sub>A</sub>	< 25 ns					
Back-Up Fuse (max)	315A / 250A gG					
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA					
TOV Withstand 5s UT	175V	337V	403V	581V		
TOV 120 min U <sub>T/mode</sub>	229V/safe fail	442V/safe fail	529V/safe fail	762V/safe fail		
Number of Ports	1	'		·		
Mechanical						
Operating Temperature Range T <sub>a</sub>	-31°F to 185°F (-35°C	C to 85°C)				
Permissible Operating Humidity RH	5%95%					
Altitude	6562 ft [2000 m]					
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5 Nm]					
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid) / 25 m	m² (Stranded), 2 AWG (S	Solid) / 4 AWG (Stranded	d)		
Mounting	35 mm DIN Rail, EN 60	0715				
Degree of Protection	IP 20					
Housing Material	Thermoplastic: Exting	uishing Degree UL 94 V-	0			
Thermal Protection	Yes					
Operating State / Fault Indication	Green Flag / Not Gree	n Flag				
Remote Contacts (RC)	Yes					
RC Switching Capacity	AC: 250V/ 1A, 125V/ 1A	A; DC: 48V/0.5A, 24V/0.	5A, 12V/0.5A			
RC Conductor Cross Section (max)	1.5 mm <sup>2</sup> (Solid) / 16 AV	WG (Solid)				
Single Unit Weight pounds	1.396	1.519	1.661	1.696		
Single Unit Weight grams	633	689	753	769		
*Other voltages and configurations available upon request						

<sup>\*</sup>Other voltages and configurations available upon request

## DT2 DIN Rail Surge Protection IEC Class II, 1+0 Mode





### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

**Certification Details:** IEC 61643-11 Class I+II

EN 61643-11 Type 1+2

UL 1449, 5th Edition Type 1CA

**Complies with:** IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4


Protection Modes: L-N, N-PE, L-L

C E 🕮 c 🕶
-----------

Part Number	DT27510R	DT215010R	DT230010R	DT235010R	DT248010R	DT255010R	DT275010
UL Electrical							
UL Nominal Voltage	60V	120V	240V	277V	400V	480V	600V
Maximum Continuous Operating Voltage (AC) MCOV	75V	150V	300V	350V	480V	550V	750V
Voltage Protection Rating VPR	330V	600V	900V	1000V	1500V	2000V	2500V
Nominal Discharge Current (8/20 µs) In	20 kA	'	'	'		'	'
Short-Circuit Current Rating (AC) SCCR	100 kA	200 kA	150 kA	200 kA	200 kA	200 kA	200 kA
IEC Electrical							
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	60V	120V	240V	277V	400V	480 V	600V
Maximum Continuous Operating Voltage (AC) Uc	75V	150V	300V	350V	480V	550 V	750V
Nominal Discharge Current (8/20 µs) In	20 kA						
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	75 kA	75 kA	65 kA	65 kA	65 kA	50 kA	50 kA
Voltage Protection Level U <sub>p</sub>	800V	1250V	1500V	1750V	2300V	2,500 V	3400V
Response Time t <sub>A</sub>	< 25 ns	1	,				'
Back-Up Fuse (max)	315A / 250A	gG					
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA						
TOV Withstand 5s U <sub>⊤</sub>	114V	229V	337V	403V	581V	697 V	871V
TOV 120 min U <sub>T/mode</sub>	114V/ withstand	229V/safe fail	442V/safe fail	529V/safe fail	762V/safe fail	915 V Safe fail	1143V safe fail
Number of Ports	1						
Mechanical							
Operating Temperature Range T <sub>a</sub>	-31°F to 185°	F (-35°C to 85	5°C)				
Permissible Operating Humidity RH	5%95%						
Altitude	6562 ft [2000	m]					
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.	5 Nm]					
Conductor Cross Section (max)	35 mm² (Solid	d) / 25 mm² (S	tranded), 2 AW	'G (Solid) / 4 A'	WG (Stranded)		
Mounting	35 mm DIN R	ail, EN 60715					
Degree of Protection	IP 20						
Housing Material	Thermoplasti	c: Extinguishin	g Degree UL 9	4 V-0			
Thermal Protection	Yes						
Operating State / Fault Indication	Green Flag / I	Not Green Flag	1				
Remote Contacts (RC)	Yes						
RC Switching Capacity	AC: 250V/ 1A	, 125V/ 1A; DC:	48V/0.5A, 24V	//0.5A, 12V/0.5	ōΑ		
RC Conductor Cross Section (max)	1.5 mm² (Soli	d) / 16 AWG (S	olid)				
Single Unit Weight pounds	0.274	0.283	0.298	0.309	0.320	0.335	0.355
Single Unit Weight grams	124	128	135	140	145		161

## DT2 DIN Rail Surge Protection IEC Class II, 2+0 Mode





#### **Features**

- · Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

**Certification Details:** IEC 61643-11 Class II

EN 61643-11 Type 2

UL 1449, 5th Edition Type 1CA

Complies with: IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4


**Protection Modes:** L-PE, N-PE, L-L

$\epsilon$	Ø <sub>E</sub>	c <b>SN</b> ° us
	تت	C TUS

Part Number	DT27520R	DT215020R	DT230020R	DT235020R	DT255020R	DT275020R
UL Electrical						
UL Nominal Voltage	60V	240/120V 1S 208/120V 3Y	415/240V 3Y 240V 3D	480/277V 3Y 240V 3D	480V 3D	690/400V 3Y 600V 3D
Maximum Continuous Operating Voltage (AC) MCOV	75V/150V	150V/300V	300V/600V	350V/700V	550V/1100V	750V/1500V
Voltage Protection Rating VPR	330V/700V	600V/1000V	900V/1800V	1000V/2000V	2000/4000V	2500V/5000V
Nominal Discharge Current (8/20 µs) In	20 kA					
Short-Circuit Current Rating (AC) SCCR	100 kA	200 kA	150 kA	200 kA	200 kA	200 kA
IEC Electrical						
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	60V	120V	240V	277V	480 V	600V
Maximum Continuous Operating Voltage (AC) U <sub>c</sub>	75V	150V	300V	350V	550 V	750V
Nominal Discharge Current (8/20 µs) In	20 kA			•		•
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	75 kA	75 kA	65 kA	65 kA	50 kA	50 kA
Voltage Protection Level U <sub>p</sub>	800V	1250V	1500V	1750V	2,500 V	3400V
Response Time t <sub>A</sub>	< 25 ns	'	'	'	'	
Back-Up Fuse (max)	315A / 250A g0	3				
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA					
TOV Withstand 5s U <sub>⊤</sub>	114V	229V	337V	403V	697 V	871V
TOV 120 min U <sub>T/mode</sub>	114V/ withstand	229V/ withstand	442V/safe fail	529V/safe fail	915 V Safe fail	1143/safe fail
Number of Ports	1			•		•
Mechanical						
Operating Temperature Range T <sub>a</sub>	-31°F to 185°F	(-35°C to 85°C)				
Permissible Operating Humidity RH	5%95%					
Altitude	6562 ft [2000 r	n]				
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5 l	Nm]				
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid)	/ 25 mm² (Stran	ded), 2 AWG (Soli	d) / 4 AWG (Strar	nded)	
Mounting	35 mm DIN Rai	il, EN 60715				
Degree of Protection	IP 20					
Housing Material	Thermoplastic:	Extinguishing D	egree UL 94 V-0			
Thermal Protection	Yes					
Operating State / Fault Indication	Green Flag / No	ot Green Flag				
Remote Contacts (RC)	Yes					
RC Switching Capacity	AC: 250V/ 1A, 1	25V/ 1A; DC: 48\	//0.5A, 24V/0.5A,	12V/0.5A		
RC Conductor Cross Section (max)	1.5 mm <sup>2</sup> (Solid)	/ 16 AWG (Solid	)			
Single Unit Weight pounds	0.538	0.556	0.587	0.609	0.586	0.702
		252		276		318

## DT2 DIN Rail Surge Protection IEC Class II, 3+0 Mode





### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

Certification Details: IEC 61643-11 Class II

EN 61643-11 Type 2

UL 1449, 5th Edition Type 1CA

**Complies with:** IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4


**Protection Modes:** L-PE/N, L-L



Part Number	DT215030R	DT230030R	DT235030R	DT248030R	DT255030R	DT275030R
UL Electrical						
UL Nominal Voltage	208/120V 3Y 240/120V 1S	415/240 3Y 240V 3D	480/277V 3Y	690/400V 3Y	480V 3D	600V 3D
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	480V/960V	550V/1100V	750V/1500V
Voltage Protection Rating VPR	600V/1000V	900V/1800V	1000V/2000V	1500V/3000V	2000/4000V	2500V/5000\
Nominal Discharge Current (8/20 µs) In	20 kA					
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	200 kA	200 kA	200 kA	200 kA
IEC Electrical						
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	120V	240V	277V	400V	480 V	600V
Maximum Continuous Operating Voltage (AC) U <sub>c</sub>	150V	300V	350V	480V	550 V	750V
Nominal Discharge Current (8/20 µs) I <sub>n</sub>	20 kA					
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	75 kA	65 kA	65 kA	65 kA	65 kA	50 kA
Voltage Protection Level U <sub>p</sub>	1250V	1500V	1750V	2300V	2,500 V	3400V
Response Time t <sub>A</sub>	< 25 ns					
Back-Up Fuse (max)	315A / 250A g0	ì				
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA					
TOV Withstand 5s U <sub>T</sub>	229V	337V	403V	581V	697V	871V
TOV 120 min U <sub>T/mode</sub>	229V/ withstand	442V/safe fail	529V/safe fail	762V/safe fail	915 V Safe fail	1143/safe fail
Number of Ports	1					
Mechanical						
Operating Temperature Range T <sub>a</sub>	-31°F to 185°F	(-35°C to 85°C)				
Permissible Operating Humidity RH	5%95%					
Altitude	6562 ft [2000 r	n]				
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5	Nm]				
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid)	/ 25 mm² (Stran	ided), 2 AWG (Sc	olid) / 4 AWG (St	randed)	
Mounting	35 mm DIN Rai	l, EN 60715				
Degree of Protection	IP 20					
Housing Material	Thermoplastic:	Extinguishing D	egree UL 94 V-0			
Thermal Protection	Yes					
Operating State / Fault Indication	Green Flag / No	ot Green Flag				
Remote Contacts (RC)	Yes					
RC Switching Capacity	AC: 250V/ 1A, 1	25V/ 1A; DC: 48\	V/0.5A, 24V/0.5A	A, 12V/0.5A		
RC Conductor Cross Section (max)		/ 16 AWG (Solid				
Single Unit Weight pounds	0.783	0.829	0.862	0.896	0.900	1.001
Single Unit Weight grams	355	376	391	406		454

<sup>\*</sup>Other voltages and configurations available upon request

## DT2 DIN Rail Surge Protection IEC Class II, 4+0 Mode



#### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

**Certification Details:** IEC 61643-11 Class I+II

EN 61643-11 Type 1+2 UL 1449, 5th Edition Type 1CA

Complies with: IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4


L-PE, N-PE, L-L **Protection Modes:** 



Part Number	DT215040R	DT230040R	DT235040R	DT248040R	DT255040R
UL Electrical					
UL Nominal Voltage	208/120V 3Y	415/240 3Y	480/277V 3Y	690/400V 3Y	690/400V 3Y
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	480V/960V	550V/1100V
Voltage Protection Rating VPR	600V/1000V	900V/1800V	1000V/2000V	1500V/3000V	2000/4000V
Nominal Discharge Current (8/20 µs) In	20 kA		·		·
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	200 kA	200 kA	200 kA
IEC Electrical					
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	120V	240V	277V	400V	480V
Maximum Continuous Operating Voltage (AC) Uc	150V	300V	350V	480V	550V
Nominal Discharge Current (8/20 µs) In	20 kA				
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	75 kA	65 kA	65 kA	65 kA	65 kA
Voltage Protection Level Up	1250V	1500V	1750V	2300V	2500V
Response Time t <sub>A</sub>	< 25 ns				
Back-Up Fuse (max)	315A / 250A gG				
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA				
TOV Withstand 5s U <sub>T</sub>	229V	337V	403V	581V	697V
TOV 120 min U <sub>T/mode</sub>	229V/withstand	442V/safe fail	529V/safe fail	762V/safe fail	915 V Safe fail
Number of Ports	1				
Mechanical					
Operating Temperature Range T <sub>a</sub>	−31°F to 185°F (−3	5°C to 85°C)			
Permissible Operating Humidity RH	5%95%				
Altitude	6562 ft [2000 m]				
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5 Nm]				
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid) / 25	5 mm² (Stranded), 2	2 AWG (Solid) / 4 AW	'G (Stranded)	
Mounting	35 mm DIN Rail, EN	N 60715			
Degree of Protection	IP 20				
Housing Material	Thermoplastic: Ext	inguishing Degree I	JL 94 V-0		
Thermal Protection	Yes				
Operating State / Fault Indication	Green Flag / Not G	reen Flag			
Remote Contacts (RC)	Yes				
RC Switching Capacity	AC: 250V/ 1A, 125V	// 1A; DC: 48V/0.5A	, 24V/0.5A, 12V/0.5A	·	
RC Conductor Cross Section (max)	1.5 mm <sup>2</sup> (Solid) / 16	5 AWG (Solid)			
Single Unit Weight pounds	1.052	1.114	1.158	1.202	1.200
Single Unit Weight grams	477	505	525	545	

# DT2 DIN Rail Surge Protection Class II, 1+0 Mode, 100 kA





Surges and voltage transients are a major cause of expensive electronic equipment failure and business disruption. Damage may result in the loss of capital outlays, such as computers and communications equipment, as well as consequential loss of revenue and profits due to unscheduled system down-time. nVent ERICO offers multiple series of surge protective devices (SPDs) suitable for a vast range of applications that provide reliable protection from voltage transients on power

#### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- External back-up fuse is not required up to 315 A (IEC only)
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring


distribution systems. The DT2 Series DIN Rail Surge Protective Devices provide reliable and efficient protection against voltage transients within the IEC Class II and UL Type 1CA environments. Tested and independently certified to the IEC and UL standards, the DT2 Series provides a range of safety and performance features for the harshest environments and suitable for protection within a wide range of applications.

Catalog Number	DT2150R100	DT2350R100	DT2550R100	DT2300R100
Nominal System Voltage (Un)	120 V	277 V	480 V	240 V
Max Continuous Operating Voltage (Uc)	150 V	350 V	550 V	300 V
Nominal Discharge Current (In), IEC	40 kA 8/20 μs			
Max Discharge Current (Imax), IEC	100 kA 8/20 μs			
Voltage Protection Level (Up)	1,250 V	1,750 V	2,500 V	1,500 V
Frequency	50 - 60 Hz			
Response Time	25 ns Max			
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25	5 kA		
Protection Modes	L-PE N-PE L-N L-PEN	L-PE N-PE L-N L-PEN	L-PE N-PE (TN-S) L-PEN L-N	L-PE N-PE L-N L-PEN
Short Circuit Current Rating (Isccr)	25 kA 50 kA			
Temporary Over Voltage 120 min (Ut/mode)	229 V Safe Fail	529 V Safe Fail	915 V Safe Fail	442 V Safe Fail
Temporary Over Voltage Withstand 5 s (Ut)	229 V	403 V	697 V	337 V
Technology	Thermal Disconnect			
Torque (TQ)	4.50 N-m			
Connection, Solid	35 mm² Max			
Connection, Stranded	25 mm² Max			
Humidity	5 – 95 % RH			
Temperature	-40 to 70°C			
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail	35 mm DIN Rail, EN 60715	35 mm top hat DIN rail
Enclosure Rating	IP 20			
Enclosure Material	UL® 94V-0 Thermoplastic			
Remote Contacts	Yes			
Status Indication	Mechanical flag			
Remote Contact Switching Capacity	1.0 A @ 250 VAC 1.0 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC	1.0 A @ 250 VAC 1.0 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC	1.0 A @ 250 VAC 1.0 A @ 125 V 0.5 A @ 48 VDC 0.5 A @ 24 V 0.5 A @ 12 V	1.0 A @ 250 VAC 1.0 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC
Dimensions H x D x W	89.92 mm x 69.09 mm x 3	6.070 mm		
Unit Weight	0.128 kg	0.140 kg	0.152 kg	0.135 kg Min
Complies With	EN 61643-11 Type 2 IEC® 6	1643-11 Class II		
Replacement Module	DT2150M	DT2350M	DT2550M	DT2300M

<sup>\*</sup>Other voltages and configurations available upon request

# EDT2 Enhanced DIN Rail Surge Protection IEC Class II, 1+0 Mode





#### **Features**

- · Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

**Certification Details:** IEC 61643-11 Class I+II

EN 61643-11 Type 1+2

UL 1449, 5th Edition Type 1CA

Complies with: IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4

**Protection Modes:** L-N, N-PE, L-L




Part Number	EDT27510R	EDT215010R	EDT230010R	EDT235010R	EDT248010R	EDT255010R	EDT275010
UL Electrical							
UL Nominal Voltage	60V	120V	240V	277V	400V	480V	600V
Maximum Continuous Operating Voltage (AC) MCOV	75V	150V	300V	350V	480V	550V	750V
Voltage Protection Rating VPR	600V	700V	1200V	1200V	1500V	1800V	2500V
Nominal Discharge Current (8/20 µs) In	20 kA						
Short-Circuit Current Rating (AC) SCCR	85 kA	200 kA	150 kA	200 kA	200 kA	200 kA	200 kA
IEC Electrical							
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	60V	120V	240V	277V	400V	480V	600V
Maximum Continuous Operating Voltage (AC) $\rm U_c$	75V	150V	300V	350V	480V	550V	750V
Nominal Discharge Current (8/20 µs) In	20 kA	'	'			1	
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	75 kA	75 kA	65 kA	65 kA	65 kA	65 kA	50 kA
Voltage Protection Level U <sub>p</sub>	800V	1250V	1650V	1750V	2300V	2500V	3500V
Response Time t <sub>A</sub>	< 25 ns						
Back-Up Fuse (max)	315A / 250A	gG					
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA	4					
TOV Withstand 120 min U <sub>⊤</sub>	150V	300V	442V	529V	762V	918V	1200V
Number of Ports	1						
Mechanical							
Operating Temperature Range T <sub>a</sub>	−31°F to 185°	°F (-35°C to 85	5°C)				
Permissible Operating Humidity RH	5%95%						
Altitude	6562 ft [2000	) m]					
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.	5 Nm]					
Conductor Cross Section (max)	35 mm² (Soli	d) / 25 mm² (S	Stranded), 2 AW	/G (Solid) / 4 A	.WG (Stranded	)	
Mounting	35 mm DIN F	Rail, EN 60715					
Degree of Protection	IP 20						
Housing Material	Thermoplast	ic: Extinguishir	ng Degree UL 9	4 V-0			
Thermal Protection	Yes						
Operating State / Fault Indication	Green Flag /	Not Green Flag	9				
Remote Contacts (RC)	Yes						
RC Switching Capacity	AC: 250V/ 1A	, 125V/ 1A; DC	: 48V/0.5A, 24\	V/0.5A, 12V/0.	5A		
RC Conductor Cross Section (max)		id) / 16 AWG (S					
Single Unit Weight pounds	0.287	0.296	0.307	0.325	0.331	0.342	0.364
Single Unit Weight grams	130	134	139	147	150	155	165

<sup>\*</sup>Other voltages and configurations available upon request

# EDT2 Enhanced DIN Rail Surge Protection IEC Class II, 2+0 Mode





### **Features**

- Includes nVent ERICO TD Technology to ensure reliability throughout adverse voltage conditions
- Enhanced temporary over voltage (TOV) withstand capability
- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

Certification Details: UL® 1449 Edition 5 Type 1CA

**Complies with:** EN 61643-11 Type 2

IEC® 61643-11 Class II

**Protection Modes:** L-N, N-PE, L-L


(		c <b>FU</b> ®us
---	--	-----------------

Part Number	EDT215020R	EDT230020R	EDT235020R	EDT248020R	EDT255020R	EDT275020R
UL Electrical						
UL Nominal Voltage	208/120V 3Y 240/120V 1S	415/240V 3Y 240V 3D	480/277V 3Y 240V 3D	690/400V 3Y	690/400V 3Y 480V 3D	600V 3D
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	480V/960V	550V/1100V	750V/1500V
Voltage Protection Rating VPR	600V/1200V	1200V/1800V	1200V/2000V	1500V/3000V	1800V/3000V	2500V/5000°
Nominal Discharge Current (8/20 µs) In	20 kA					
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	200 kA	200 kA	200 kA	200 kA
IEC Electrical						
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	120V	240V	277V	400V	400V	600V
Maximum Continuous Operating Voltage (AC) $U_{\rm c}$	150V	300V	350V	480V	550V	750V
Nominal Discharge Current (8/20 µs) In	20 kA					
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	75 kA	65 kA	65 kA	65 kA	65 kA	50 kA
Voltage Protection Level Up	1250V	1650V	1750V	2300V	2500V	3500V
Response Time t <sub>A</sub>	< 25 ns					
Back-Up Fuse (max)	315A / 250A g0	3				
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA					
TOV Withstand 120 min $U_T$	300V	442V	529V	762V	918V	1200V
Number of Ports	1			'		'
Mechanical						
Operating Temperature Range T <sub>a</sub>	−31°F to 185°F	(-35°C to 85°C)				
Permissible Operating Humidity RH	5%95%					
Altitude	6562 ft [2000 r	n]				
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5	Nm]				
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid)	/ 25 mm² (Stran	ded), 2 AWG (Sol	id) / 4 AWG (Stra	anded)	
Mounting	35 mm DIN Ra	I, EN 60715				
Degree of Protection	IP 20					
Housing Material	Thermoplastic:	Extinguishing De	egree UL 94 V-0			
Thermal Protection	Yes					
Operating State / Fault Indication	Green Flag / No	ot Green Flag				
Remote Contacts (RC)	Yes					
RC Switching Capacity	AC: 250V/ 1A, 1	25V/ 1A; DC: 48\	//0.5A, 24V/0.5A	12V/0.5A		
RC Conductor Cross Section (max)	1.5 mm <sup>2</sup> (Solid) / 16 AWG (Solid)					
Single Unit Weight pounds	0.583	0.605	0.640	0.653	0.675	0.719
Single Unit Weight grams	264	274	290	296	306	326

<sup>\*</sup>Other voltages and configurations available upon request

# EDT2 Enhanced DIN Rail Surge Protection IEC Class II, 3+0 Mode





#### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

Certification Details: IEC 61643-11 Class II

EN 61643-11 Type 2

UL 1449, 5th Edition Type 1CA

**Complies with:** IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4

**Protection Modes:** L-PE/N, L-L




Part Number	EDT215030R	EDT230030R	EDT235030R	EDT248030R	EDT255030R	EDT275030R
UL Electrical	•					
UL Nominal Voltage	208/120V 3Y 240/120V 1S	415/240 3Y 240V 3D	480/277V 3Y	690/400V 3Y	480V 3D	600V 3D
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	480V/960V	550V/1100V	750V/1500V
Voltage Protection Rating VPR	700V/1500V	1200V/2000V	1200V/2000V	1500V/2500V	1800V/3000V	2500V/5000V
Nominal Discharge Current (8/20 µs) I <sub>n</sub>	20 kA					
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	200 kA	200 kA	200 kA	200 kA
IEC Electrical						
Nominal AC Voltage (50/60Hz) U <sub>o</sub> / U <sub>n</sub>	120V	240V	277V	400V	400V	600V
Maximum Continuous Operating Voltage (AC) U <sub>c</sub>	150V	300V	350V	480V	550V	750V
Nominal Discharge Current (8/20 µs) In	20 kA					
Maximum Discharge Current (8/20 μs) I <sub>max</sub>	75 kA	65 kA	65 kA	65 kA	65 kA	50 kA
Voltage Protection Level U <sub>p</sub>	1250V	1650V	1750V	2300V	2500V	3500V
Response Time t <sub>A</sub>	< 25 ns					
Back-Up Fuse (max)	315A / 250A gG	i				
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA					
TOV Withstand 120 min U <sub>T</sub>	300V	442V	529V	762V	918V	1200V
Number of Ports	1	'			'	
Mechanical						
Operating Temperature Range T <sub>a</sub>	-31°F to 185°F (	(-35°C to 85°C)				
Permissible Operating Humidity RH	5%95%					
Altitude	6562 ft [2000 m	٦]				
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5 l	Nm]				
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid)	/ 25 mm² (Strand	ded), 2 AWG (Soli	d) / 4 AWG (Strai	nded)	
Mounting	35 mm DIN Rai	l, EN 60715				
Degree of Protection	IP 20					
Housing Material	Thermoplastic:	Extinguishing De	gree UL 94 V-0			
Thermal Protection	Yes					
Operating State / Fault Indication	Green Flag / No	t Green Flag				
Remote Contacts (RC)	Yes					
RC Switching Capacity	AC: 250V/ 1A, 1:	25V/ 1A; DC: 48V	/0.5A, 24V/0.5A,	12V/0.5A		
RC Conductor Cross Section (max)		/ 16 AWG (Solid)				
Single Unit Weight pounds	0.823	0.856	0.909	0.929	0.962	1.028
Single Unit Weight grams	373	388	412	421	436	466

<sup>\*</sup>Other voltages and configurations available upon request

# EDT2 Enhanced DIN Rail Surge Protection IEC Class II, 4+0 Mode





### **Features**

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

Certification Details: IEC 61643-11 Class II

EN 61643-11 Type 2

UL 1449, 5th Edition Type 1CA

**Complies with:** IEC 61643-11:2011

EN 61643-11:2012 UL 1449, 5th Edition CSA C22.2 No. 269-4

**Protection Modes:** L-PE, N-PE, L-L


	$\epsilon$	₽E	c <b>FL</b> us
--	------------	----	----------------

Part Number	EDT215040R	EDT230040R	EDT235040R	EDT248040R	EDT255040R
UL Electrical					
UL Nominal Voltage	208/120V 3Y	415/240 3Y	480/277V 3Y	690/400V 3Y	690/400V 3Y
Maximum Continuous Operating Voltage (AC) MCOV	150V/300V	300V/600V	350V/700V	480V/960V	550V/1100V
Voltage Protection Rating VPR	600V/1000V	1200V/2000V	1200V/2000V	1500V/2500V	1800V/3000V
Nominal Discharge Current (8/20 µs) In	20 kA				
Short-Circuit Current Rating (AC) SCCR	200 kA	150 kA	200 kA	200 kA	200 kA
IEC Electrical					
Nominal AC Voltage (50/60Hz) $U_o / U_n$	120V	240V	277V	400V	400V
Maximum Continuous Operating Voltage (AC) Uc	150V	300V	350V	480V	550V
Nominal Discharge Current (8/20 µs) In	20 kA				
Maximum Discharge Current (8/20 µs) I <sub>max</sub>	75 kA	65 kA	65 kA	65 kA	65 kA
Voltage Protection Level U <sub>p</sub>	1250V	1650V	1750V	2300V	2500V
Response Time t <sub>A</sub>	< 25 ns				
Back-Up Fuse (max)	315A / 250A gG				
Short-Circuit Current Rating (AC) I <sub>SCCR</sub>	25 kA / 50 kA				
TOV Withstand 120 min $U_T$	300V	442V	529V	762V	918V
Number of Ports	1				
Mechanical					
Operating Temperature Range T <sub>a</sub>	−31°F to 185°F (-	-35°C to 85°C)			
Permissible Operating Humidity RH	5%95%				
Altitude	6562 ft [2000 m]				
Terminal Screw Torque M <sub>max</sub>	39.9 lbf·in [4.5 N	m]			
Conductor Cross Section (max)	35 mm <sup>2</sup> (Solid) /	25 mm² (Stranded	), 2 AWG (Solid) / 4	AWG (Stranded)	
Mounting	35 mm DIN Rail,	EN 60715			
Degree of Protection	IP 20				
Housing Material	Thermoplastic: E	Extinguishing Degre	ee UL 94 V-0		
Thermal Protection	Yes				
Operating State / Fault Indication	Green Flag / Not	Green Flag			
Remote Contacts (RC)	Yes				
RC Switching Capacity	AC: 250V/ 1A, 12	5V/ 1A; DC: 48V/0.	5A, 24V/0.5A, 12V/	0.5A	
RC Conductor Cross Section (max)	1.5 mm <sup>2</sup> (Solid) /	16 AWG (Solid)			
Single Unit Weight pounds	1.105	1.149	1.220	1.246	1.290
Single Unit Weight grams	501	521	553	565	585

<sup>\*</sup>Other voltages and configurations available upon request

# EDT2 Enhanced DIN Rail Surge Protection Class II, 1+0 Mode, 100kA





### **Features**

- Includes nVent ERICO TD Technology to ensure reliability throughout adverse voltage conditions
- Enhanced temporary over voltage (TOV) withstand capability
- External back-up fuse is not required up to 315 A (IEC only)
- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring


Part Number	EDT2150R100	EDT2300R100	EDT2350R100	EDT2550R100
Nominal System Voltage (Un)	120 V	240 V	277 V	480 V
Max Continuous Operating Voltage (Uc)	150 V	300 V	350 V	550 V
Nominal Discharge Current (In), IEC	40 kA 8/20 μs		'	
Max Discharge Current (Imax), IEC	100 kA 8/20 μs			
Voltage Protection Level (Up)	1,250 V	1,500 V	1,750 V	2,500 V
Back-Up Fuse @ Isccr	250 A @ 50 kA 315 A @ 25 kA			
Frequency	50 – 60 Hz			
Response Time	25 ns Max			L DE
Protection Modes	L-PE N-PE L-N L-PEN			L-PE N-PE (TN-S) L-PEN L-N
Short Circuit Current Rating (Isccr)	25 kA 50 kA			
Temporary Over Voltage 120 min (Ut/mode)	229 V Safe Fail	442 V Safe Fail	529 V Safe Fail	915 V Safe Fail
Temporary Over Voltage Withstand 5 s (Ut)	229 V	337 V	403 V	697 V
Technology	Thermal Disconnec	et		
Connection, Solid	35 mm² Max			
Connection, Stranded	25 mm² Max			
Torque (TQ)	4.5 N-m			
Humidity	5 – 95 % RH			
Temperature	-40 to 70°C			
Enclosure Material	UL® 94V-0 Thermor	plastic		
Enclosure Rating	IP 20			
Mounting	35 mm top hat DIN	rail		35 mm DIN Rail, EN 60715
Remote Contact Switching Capacity	1.0 A @ 250 VAC 1.0 A @ 125 VAC 0.5 A @ 48 VDC 0.5 A @ 24 VDC 0.5 A @ 12 VDC			1.0 A @ 250 VAC 1.0 A @ 125 V 0.5 A @ 48 VDC 0.5 A @ 24 V 0.5 A @ 12 V
Remote Contacts	Yes			
Status Indication	Mechanical flag			
Depth (D)	69.09 mm			
Height (H)	89.92 mm			
Width (W)	36.07 mm			
Unit Weight	0.128 kg	0.135 kg	0.140 kg	0.152 kg
Complies With	EN 61643-11 Type 2			
Replacement Module	DT2150M	DT2300M	DT2350M	DT2550M

IEC is a registered trademark of the International Electrotechnical Commission.

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

# PVT1 Photovoltaic Surge Protection Class I






- Uniquely designed for protection of centralized solar inverters on the DC input side and string boxes
- Thermal protection included to ensure safe failure modes
- Compact, yet high surge rated pluggable design, using minimum DIN rail width



Part Number	PVT11000R	PVT11500R	
Max Continuous Operating Voltage (Ucpv)	1,100 V	1,500 VDC	
Maximum Discharge Current (8/20 µs) Imax	50 kA	50 kA	
Nominal Discharge Current (In), IEC	20 kA 8/20 μs		
Impulse Current (limp)	6.25 kA 10/350 µs	5.00 kA 10/350 μs	
Total Discharge Current (Itotal)	12.5 kA 10/350 µs; 50.0 kA 8/20 µs	10.0 kA 10/350 μs; 40.0 kA 8/20 μs	
Voltage Protection Level (Up)	4,000 V	5,000 V	
Response Time	25 ns Max		
Short Circuit Current Rating (Isccr)	11 kA		
Max Continuous Operating Voltage (Vpvdc)	1,100 VDC	1,500 VDC	
Voltage Protection Rating (VPR)	2,500 V	4,000 V	
Nominal Discharge Current (In), UL	20 kA 8/20 μs		
Short Circuit Current Rating (SCCR)	50 kA	65 kA	
Protection Modes	-ve to PE; -ve to +ve; +ve to PE		
Altitude	6,562' Max		
Humidity	5 – 95 % RH		
Temperature	-40°F to 185°F (-40°C to 85°C)		
Connection, Flexible	#4		
Connection, Solid	#2		
Connection, Stranded	#2		
Enclosure Material	UL® 94V-0 Thermoplastic		
Enclosure Rating	IP 20		
Mounting	35 mm top hat DIN rail		
Torque (TQ)	3.3 ft lb Max		
Remote Contact Switching Capacity	1.0 A @ 125 VAC; 1.0 A @ 250 VAC; 0.5 A @ 12	VDC; 0.5 A @ 24 VDC; 0.5 A @ 48 VDC	
Remote Contacts	Yes		
Status Indication	Mechanical flag		
Depth (D)	3.35"		
Height (H)	3.54"		
Width (W)	2.13"		
Unit Weight	1.02 lb 1.10 lb		
Replacement Module	PVT1500M; PVT1500SM	PVT1750M; PVT1750SM	
Certification Details	UL® 1449 Edition 5 Type 1CA		
Complies With	EN 50539-11 Type 1, Type 2		

# PVT2 Photovoltaic Surge Protection Class II





- Suited for use at the DC input of distributed string inverters in solar arrays
- Thermal protection included to ensure safe failure modes
- Compact, yet high surge rated pluggable design, using minimum DIN rail width




		C 😑 U 🖊 Us			
Part Number	PVT21000R	PVT21500R			
Max Continuous Operating Voltage (Ucpv)	1,100 V	1,500 VDC			
Nominal Discharge Current (In), IEC	20 kA 8/20 μs				
Max Discharge Current (Imax)	50 kA 8/20 μs	50 kA 8/20 μs			
Total Discharge Current (Itotal)	50 kA 8/20 μs	40 kA 8/20 μs			
Voltage Protection Level (Up)	4,000 V	5,000 V			
Response Time	25 ns Max				
Short Circuit Current Rating (Isccr)	11 kA				
Max Continuous Operating Voltage (Vpvdc)	1,100 VDC	1,500 VDC			
Voltage Protection Rating (VPR)	3,000 V	4,000 V			
Nominal Discharge Current (In), UL	20 kA 8/20 μs				
Short Circuit Current Rating (SCCR)	50 kA	65 kA			
Protection Modes	-ve to PE; -ve to +ve; +ve to PE				
Altitude	6,562' Max				
Humidity	5 – 95 % RH	5 – 95 % RH			
Temperature	-40°F to 185°F (-40°C to 85°C)				
Connection, Flexible	#4	#4			
Connection, Solid	#2	#2			
Connection, Stranded	#2	#2			
Enclosure Material	UL® 94V-0 Thermoplastic				
Enclosure Rating	IP 20				
Mounting	35 mm top hat DIN rail				
Torque (TQ)	3.3 ft lb Max				
Remote Contact Switching Capacity	1.0 A @ 125 VAC; 1.0 A @ 250 VAC; 0.5 A @	) 12 VDC; 0.5 A @ 24 VDC; 0.5 A @ 48 VDC			
Remote Contacts	Yes				
Status Indication	Mechanical flag				
Depth (D)	2.72"				
Height (H)	3.54"				
Width (W)	2.13"				
Unit Weight	0.9 lb	1.0 lb			
Replacement Module	PVT2500M	PVT2750M			
Certification Details	UL® 1449 Edition 5 Type 1CA				
Complies With	EN 50539-11 Type 2				

# Transient Discriminating Surge Diverter, 20 kA Three Mode








- 20 kA 8/20 µs surge rating provides robust surge protection
- TD Technology with thermal disconnect protection
- Compact package, modular DIN rail mounting for limited space requirements
- Three modes of protection: L-N, L-PE and N-PE
- Indication flags and voltage-free contacts provide remote status monitoring
- Separate plug and base design facilitates replacement of a failed surge module




Part Number	TDS1301T150	TDS1301T240	TDS1301TR150	TDS1301TR240		
Nominal System Voltage (Un)	120 - 150 VAC	220 - 240 VAC	120 - 150 VAC	220 - 240 VAC		
Max Continuous Operating Voltage (Uc)	170 VAC	275 VAC	170 VAC	275 VAC		
Stand-off Voltage	230 VAC	440 VAC	230 VAC	440 VAC		
Voltage Protection Rating (VPR)	800 V @ 3 kA L-N 500 V @ 3 kA L+N-PE	1,500 V @ 3 kA L-N 800 V @ 3 kA L+N-PE	800 V @ 3 kA L-N 500 V @ 3 kA L+N-PE	1,500 V @ 3 kA L-N 800 V @ 3 kA L+N-PE		
Nominal Discharge Current (In), Per Mode	8 kA 8/20 μs					
Max Discharge Current (Imax)	20 kA 8/20 µs L-N, 20 k	(A 8/20 μs L-PE				
Back-Up Overcurrent Protection	63 A					
Short Circuit Current Rating (SCCR)	200 kA					
Frequency	0 – 100 Hz					
Protection Modes	L-N L-PE N-PE					
Response Time	5 ns Max					
Technology	TD technology with the	rmal disconnect				
Connection, PE Solid	#2 Max	#2 Max				
Connection, PE Stranded	#4 Max					
Connection, Solid	#10 Max					
Connection, Stranded	#10 Max	#10 Max				
Mounting	35 mm top hat DIN rail					
Enclosure Material	UL® 94V-0 Thermoplas	tic				
Enclosure Rating	IP 20 NEMA®-1					
Remote Contacts	No		Yes			
Status Indication	Mechanical flag					
Temperature	−40 to 176°F					
Module Width	1 M					
Depth (D)	2.68"					
Height (H)	3.54"					
Width (W)	0.71"					
Unit Weight	0.26 lb					
Certification Details	UL® 1449 Edition 5, Typ	e 4CA				
Complies With	ANSI®/IEEE® C62.41.2-2	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B IEC® 61643-1 Class III				
Replacement Module	TDS130M150	TDS130M240	TDS130M150	TDS130M240		

# Surge Diverter, 24/48 DC






- 40 kA 8/20 µs surge rating per mode, 80 kA per line, 120 kA total per pair
- Suitable for exposed DC wiring
- Indication flag provides clear visual indication of life status
- Suitable for both 24 VDC and 48 VDC distribution systems





Part Number	DSD1402BR24/48
Nominal System Voltage (Un)	0 - 48 VDC
Max Continuous Operating Voltage (Uc)	60 VAC; 60 VDC
Max Discharge Current (Imax), Per Mode	40 kA 8/20 μs
Nominal Discharge Current (In)	20 kA 8/20 μs
Voltage Protection Level (Up), + to - @ In	600 V
Voltage Protection Level (Up), L-N	280 V @ 3 kA
Frequency	0 – 60 Hz
Protection Modes	Common Differential
Short Circuit Current Rating (SCCR)	25 kA
Technology	MOV with thermal disconnect
Connection, Solid	#2 Max
Connection, Stranded	#4 Max
Mounting	35 mm top hat DIN rail
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20 NEMA®-1
Status Indication	Mechanical flag
Terminal Torque	31 ft lb Max
Remote Contacts	Yes
Temperature	-40 to 176°F
Module Width	2 M
Depth (D)	2.68"
Part Number	DSD1402BR24/48
Height (H)	3.54"
Width (W)	1.42"
Unit Weight	0.45 lb
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C; ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 2, 20 kA 8/20 µs, 2 kA 10/350 µs IEC® 61643-1 Class II
Certifications	CE, DSD140; Qualifoudre
Standard Packaging Quantity	1 pc
UPC	78285652474
EAN-13	8711893029802

# Transient Surge Filter



Ν


- Compact, space saving design
- Replaceable surge module reduces down time and unprotected time during maintenance
- Compliance to the latest UL 1449 Edition 5 and IEC 61643-11 surge standards and UL 1283 Electromagnetic Interference Filters (EMI) standard
- Low let-through voltages on the critical line to neutral mode
- Transient Discriminating (TD) Technology provides increased service life
- All modes protected at 20 kA 8/20 µs
- Form C Relay Contacts for Remote Monitoring
- Two Terminals per line




Part Number	TSF6A24V	TSF6A120V	TSF20A120V	TSF6A240V	TSF20A240V	
Nominal System Voltage (Un)	24 V	120 V	•	240 V	•	
Rated Load Current (IL)	6 A		20 A	6 A	20 A	
Max Continuous Operating Voltage (Uc)	30 VAC/38 VDC	170 V		275 V		
Stand-off Voltage	_	230		440		
Filtering	-65 dB @ 100 kHz		-50 dB @ 100 kHz	-65 dB @ 100 kHz	-50 dB @ 100 kHz	
Frequency	0 – 100 Hz					
Max Discharge Current (Imax)	40 kA 8/20 μs, per μ	ohase				
Voltage Protection Rating (VPR) L-N	_	330v	400v	_	_	
Measured Limiting Voltage (MLV) L-N	_	_	_	620v	680v	
Nominal Discharge Current (In)	3 kA 8/20 µs, all mo	odes				
Distribution System	1Ph 2W+G	1Ph 2W+G				
Connection, Solid	2.5 mm <sup>2</sup> - 6.0 mm <sup>2</sup> ;	2.5 mm <sup>2</sup> - 6.0 mm <sup>2</sup> ; #14 - #10				
Connection, Stranded	2.5 mm <sup>2</sup> - 6.0 mm <sup>2</sup> ;	2.5 mm <sup>2</sup> - 6.0 mm <sup>2</sup> ; #14 - #10				
Mounting	35 mm top hat DIN	35 mm top hat DIN rail				
Status Indication	Mechanical flag					
Enclosure Material	UL® 94V-0 Thermop	olastic				
Enclosure Rating	IP 20					
Temperature	−31 − 104°F					
Module Width	3 M					
Depth (D) x Height (H) x Width (W)	95 mm x 123 mm x	54 mm				
Unit Weight	508 grams					
Replacement Module	TSF24MDSD	TSF120MTDS		TSF240MTDS		
Certifications	CE	CE, cURus, UL 1449	Ed 5, UL 1283 Ed 7			

### Surge Reduction Filter N-Series, Single Phase








- High-performance protection incorporating Spark Gap and Transient Discriminating (TD) technologies
- High surge rating ideal for exposed critical service entrance applications
- Reduces let-through voltages and rate-of-voltage rise (dv/dt) and helps provide optimum protection for electronic equipment
- Extreme reliability and simplified design with direct connection from input to output
- Comprehensive front panel status and internal diagnostic LEDs




Part Number	SRF163N	SRF1125N	
Nominal System Voltage (Un)	220 - 240 VAC		
Distribution System	1Ph 2W+G		
System Compatibility	TN-C, TN-C-S, TN-S, TT		
Frequency	50 – 60 Hz		
Short Circuit Current Rating (SCCR)	43 kA		
Heat Dissipation	25 W		
Filtering	-40 dB @ 100 kHz		
Protection Modes	All modes protected		
Technology	Spark Gap, In-line series low pass sine wave filte (50 kA 8/20us secondary stage)	er, TD technology with thermal disconnect	
Enclosure Material	Metal		
Enclosure Rating	IP 65		
Mounting	Wall mount		
Status Indication	Front panel LED, Internal diagnostic primary and contact (Form C dry), 250 VAC/30 VDC/5 A, 4 kV		
Rated Load Current (IL)	63 A	125 A	
Rate of Voltage Rise (dV/dt)	3 V/μs Max	8 V/µs Max	
Voltage Protection Level (L-N)	150 V @ 3 kA 8/20 µs 200 V @ 20 kA 8/20 µs	250 V @ 3 kA 8/20 μs 350 V @ 20 kA 8/20 μs	
Input Connection	10 - 35 mm²	25 - 120 mm²	
Output Connection	25 - 120 mm²		
Depth (D)	200 mm		
Height (H)	300 mm		
Width (W)	400 mm		
Unit Weight	10.3 kg	12.3 kg	
Complies With	IEC® 61643-11 Class I, Class II ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposur	re 3, 100 kA 8/20 µs, 10 kA 10/350 µs	

# Surge Reduction Filter N-Series, Three Phase








- High-performance protection incorporating Spark Gap and Transient Discriminating (TD) technologies
- High surge rating ideal for exposed critical service entrance applications
- Reduces let-through voltages and rate-of-voltage rise (dv/dt) and helps provide optimum protection for electronic equipment
- Extreme reliability and simplified design with direct connection from input to output
- Comprehensive front panel status and internal diagnostic LEDs




Part Number	SRF363N	SRF3125N	SRF3250N	SRF3500N	SRF3800N		
Nominal System Voltage (Un)	220/380 - 240/415 VAC						
Distribution System	3Ph Y 4W+G	3Ph Y 4W+G					
System Compatibility	TN-C, TN-C-S, TN-S, T	Т					
Frequency:	50 – 60 Hz						
Short Circuit Current Rating (SCCR)	43 kA						
Filtering	-40 dB @ 100 kHz						
Protection Modes	All modes protected						
Technology	Spark Gap, In-line ser (50 kA 8/20us secon	ies low pass sine wave dary stage)	e filter, TD technology v	vith thermal disconnec	t		
Enclosure Material	Metal						
Mounting	Wall mount						
Status Indication	Front panel LED, Internal diagnostic primary and secondary protection LEDs, Change-over contact (Form C dry 250 VAC/30 VDC/5 A, 4 kV isolation						
Rated Load Current (IL)	63 A	125 A	250 A	500 A	800 A		
Heat Dissipation	34 W	56 W	98 W	215 W	260 W		
Rate of Voltage Rise (dV/dt)	5 V/μs Max	10 V/µs Max	11 V/µs Max	10 V/µs Max			
Voltage Protection Level (L-N)	200 V @ 3 kA 8/20 µs 250 V @ 20 kA 8/20 µs	300 V @ 3 kA 8/20 µs 380 V @ 20 kA 8/20 µs	300 V @ 3 kA 8/20 µs 500 V @ 20 kA 8/20 µs	320 V @ 3 kA 8/20 µs 550 V @ 20 kA 8/20 µs	320 V @ 3 kA 8/20 µs 550 V @ 20 kA 8/20 µs		
Input Connection	10 - 35 mm <sup>2</sup>	25 - 120 mm²		10 mm Stud	(2) 10 mm studs		
Output Connection	10 - 35 mm²	25 - 120 mm²		10 mm Stud	(2) 10 mm studs		
Enclosure Rating	IP 65			IP 32			
Depth (D)	200 mm			300 mm			
Height (H)	500 mm		800 mm	1000 mm	1200 mm		
Width (W)	400 mm		600 mm	800 mm			
Unit Weight	17.7 kg	21.6 kg	41.7 kg	76.6 kg	97.2 kg		
Complies With	IEC® 61643-11 Class I, Class II ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μs, 10 kA 10/350 μs						

# High Speed Data Line Protector









- Multi-stage protection with primary or combination primary/secondary protectors
- 10 pair protector
- Provides both L-L and L-PE protection modes for comprehensive protection Simple installation into Krone® LSA disconnect block
- Data Line Terminator (DLT) available where screw terminal connections are required









Doub Name hou	HSP10K12	HSP10K36	LICD10K72	HSP10K230
Part Number			HSP10K72	
Max Continuous Operating Voltage (Uc)	13 VDC	40 VDC	65 VDC	190 VDC
Max Discharge Current (Imax), L+L-PE	20 kA 8/20 μs			
Rated Load Current (IL)	150 mA			
Frequency	12 MHz Max			
Transmission Rate	8 Mb/s			
Protection Modes	L-L, L-PE			
Technology	Multi-stage			
Connection Type	Krone® LSA-PLUS			
Impedance Balance	55 dB Max			
Insertion Loss	.4 dB Max			
Return Loss	20 dB Max			
Certifications	UL 497B			

# Subscriber Line Protector, Single Stage








- Single stage protection with primary or combination primary/secondary protectors
- 10 pair protector
- Simple installation into Krone® LSA disconnect block
- Data Line Terminator (DLT) available where screw terminal connections are required




Part Number	SLP10K1F
Max Continuous Operating Voltage (Uc)	190 VDC
Max Discharge Current (Imax), L+L-PE	20 kA 8/20 μs
Rated Load Current (IL)	1,000 mA
Frequency	12 Hz Max
Transmission Rate	8 Mb/s
Protection Modes	L-L
Technology	Single-stage
Connection Type	Krone® LSA-PLUS
Impedance Balance	48 dB Max
Insertion Loss	.75 dB Max
Return Loss	22 dB Max
Loop Resistance	0.2 Ω
Temperature	-20 to 60°C
Enclosure Material	UL® 94V-0 Thermoplastic
Depth (D)	21 mm
Height (H)	34.5 mm
Width (W)	125 mm
Unit Weight	22.7 g
Certification Details	UL 497B
Certifications	RCM, CE, cULus
Standard Packaging Quantity	1 pc
UPC	78285647508
EAN-13	9321098000460

### Telephone Line Protector






- RJ11 sockets provide simple plug-in connection for 4 or 6 position RJ plugs
- Includes patch cord and adhesive mounting strips
- Provides both L-L and L-PE protection modes for comprehensive protection
- Automatic over-current protection

















### Coaxial Surge Protector



### **SPECIFICATIONS**

Max Discharge Current (Imax), Per Mode: 20 kA 8/20 µs Rated Nominal Discharge Current (In): 20 kA 8/20 µs

Frequency: 0 - 3 GHz Capacitance: 1.5 pF

Insulation Resistance: 10 GΩ

Impulse Life: 400 @ 500 A 10/1000 µs

Enclosure Material: Metal

Enclosure Rating: IP 20; NEMA®-1

Temperature: -40 to 90°C Certification: UL 497E

### **Features**

- Simple plug-in installation
- · Supplied with mounting bracket and flying lead ground
- Low insertion and return loss
- · Wide operating frequency spectrum
- · Low spark over voltage, better clamping
- Field-serviceable with replaceable GDT arrestor

Note: To select the appropriate protection voltage, use the following procedure:


- 1. Determine the transmitter power in Watts (P).
- 2. Determine the VSWR. If unsure, use 1.5.
- 3. Vpeak = VSWR x 1.4 x √(50P).
- 4. If Vpeak < 72 V, use CSP XXX 90. If Vpeak > 72 V and < 480 V, use CSP XXX 600.
- 5. Taking this value of VSWR and allowing a little margin, this means that typically the 90V protector is used for Receivers and Transmitters up to 20 W, while the 600W protector can be used for transmitters up to 900 W.



Part Number	Connection Type	Spark-Over Voltage @ 100 V/µs	Spark-Over Voltage @ 100 V/s	Depth D	Height H	Width W	Unit Weight
CSP1NB90	N-Type, Female/Female	450 V	72 – 108 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1NMF90	N-Type, Male/Female	450 V	72 – 108 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1BNC90	BNC, Male/Female	450 V	72 – 108 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1BNC600	BNC, Male/Female	1,100 V	480 – 720 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1SMA90	SMA, Male/Female	450 V	72 – 108 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1NB600	N-Type, Female/Female	1,100 V	480 – 720 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1F90	F-Type, Male/Female	450 V	72 – 108 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1F600	F-Type, Male/Female	1,100 V	480 – 720 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1NBM90	N-Bulkhead, Male/Female	450 V	72 – 108 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1NBM600	N-Bulkhead, Male/Female	1,100 V	480 – 720 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1NMF600	N-Type, Male/Female	1,100 V	480 – 720 V	25.4 mm	25 mm	25 mm	133.4 g
CSP1SMA600	SMA, Male/Female	1,100 V	480 – 720 V	25.4 mm	25 mm	25 mm	133.4 g

### Closed Circuit Television Protector






- Robust high energy protection
- Compact package for limited space requirements
- Isolated ground prevents introduction of unwanted noise


Part Number	CCTV12
Nominal System Voltage (Un)	+/- 12 VDC
Max Continuous Operating Voltage (Uc)	+/- 14 VDC
Voltage Protection Level (Up)	60 V @ 5 kA
Nominal Discharge Current (In)	10 kA 8/20 µs
Frequency	100 MHz Max
Transmission Rate	16 Mb/s
Impedance	50 – 75 Ω
Connection Type	BNC, Female
Mounting	In-line insertion
Temperature	−25 to 70°C
Enclosure Material	Metal
Enclosure Rating	IP 20 NEMA®-1
Depth (D)	27.9 mm
Height (H)	90 mm
Width (W)	22.1 mm
Unit Weight	60 g
Standard Packaging Quantity	1 pc
UPC	78285647021
EAN-13	8711893014204

# LAN Surge Protector






- Rugged, metallic enclosure provides both environmental and electrical shielding
- Up to CAT6 and POE (Power Over Ethernet) protection in one product
- Simple, bi-directional installation






Part Number	LANRJ45C6P	
Nominal System Voltage (Un)	48 VDC	
Max Continuous Operating Voltage (Uc)	50 VDC	
Voltage Protection Rating (VPR), L-L	150 V	
Voltage Protection Rating (VPR), L-PE	550 V	
Nominal Discharge Current (In), L-L	150 A 8/20 μs	
Max Discharge Current (Imax), L-PE	10 kA 8/20 μs	
Impulse Current (limp)	1 kA 10/350 μs	
Rated Load Current (IL)	1 A	
Frequency	250 MHz Max	
Baud Rates	10, 100, 1000, 10000 Mbps	
Temperature	-40 to 80°C	
Connection Type	RJ45	
Enclosure Material	Metal	
Enclosure Rating	IP 20	
Depth (D)	45.5 mm	
Height (H)	75 mm	
Width (W)	19 mm	
Complies With	IEC® 61643-21 UL 497B	
Standard Packaging Quantity	1 pc	
UPC	78285693008	
EAN-13	0782856930082	

# Data Equipment Protector




- Models to cover RS-232, RS-423, RS-422 and RS-485 protocols
- Designed to provide both line to signal-ground and signal-ground to protective-earth protection
- Plug-in protection is simple to install




Part Number	DEPRS2322525D	DEPRS23299D	DEPRS42299D
Nominal Discharge Current (In)	300 A 8/20 μs		400 A 8/20 μs
Max Continuous Operating Voltage (Uc)	15 VDC		6 VDC
Capacitance	30 pF Max		
Protection Modes	All pins to ground		
Connection Type	DB25, Male/Female DB9, Male/Female		
Depth (D)	2.4"		
Height (H)	0.66"		
Width (W)	2.11" 1.20"		
Unit Weight	0.17 lb	0.12 lb	

# Universal Transient Barrier, Single Pair





- Compact design universal transient barrier provides protection of low-voltage circuits and transducers
- Separate plug and base design allows hot swappable module replacement
- Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment
- Common-mode and differential-mode protection protects against both possible surge conditions
- Surge rating to 20 kA 8/20 µs is ideal for exposed wiring
- Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space







Part Number	UTB5SP	UTB15SP	UTB30SP	UTB60SP	UTB110SP
Nominal System Voltage (Un)	0 - 3 VAC 0 - 5 VDC	3 - 10 VAC 5 - 15 VDC	10 - 21 VAC 15 - 30 VDC	21 - 42 VAC 30 - 60 VDC	100 - 120 VAC 60 - 154 VDC
Max Continuous Operating Voltage (Uc)	5 VAC 7 VDC	12 VAC 18 VDC	23 VAC 33 VDC	45 VAC 64 VDC	150 VAC 170 VDC
Frequency	0.5 MHz	1.0 MHz	2.0 MHz	3.0 MHz	3.0 MHz
Rated Load Current (IL)	2A				
Loop Resistance	1 Ω				
Max Discharge Current (Imax), L+L-PE	20 kA 8/20 μs				
Protection Modes	Common, Differentia	I			
Technology	Gas Discharge Tube	(GDT), Metal Oxide Va	aristor (MOV), Silicon A	Avalanche Diode (SAD	)
Connection, Stranded	1.0 mm <sup>2</sup> - 4.0 mm <sup>2</sup> ; #	±18 - #12			
Mounting	35 mm top hat DIN r	35 mm top hat DIN rail			
Temperature	-20 to 65°C				
Enclosure Material	UL® 94V-0 Thermopl	UL® 94V-0 Thermoplastic			
Enclosure Rating	IP 20, NEMA®-1				
Depth (D)	72 mm				
Height (H)	90 mm				
Width (W)	12 mm				
Unit Weight	68 g				
Certification Details	UL® 497B				
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C				
Voltage Protection Level (Up), L-L	10 V @ 3 kA	25 V @ 3 kA	44 V @ 3 kA	85 V @ 3 kA	220 V @ 3 kA
Replacement Module	UTB5SPM	UTB15SPM	UTB30SPM	UTB60SPM	UTB110SPM
Certifications	CE NOM UR	CE UR	CE NOM UR	CE UR	CE NOM UR

### Universal Transient Barrier, Dual Pair








- · Compact design universal transient barrier provides protection of low-voltage circuits and transducers
- Separate plug and base design allows hot swappable module replacement
- Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment
- Common-mode and differential-mode protection protects against both possible surge conditions
- $\bullet$  Surge rating to 20 kA 8/20  $\mu s$  is ideal for exposed wiring
- Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space




Part Number	UTB5DP	UTB15DP	UTB30DP	UTB60DP	UTB110DP
Nominal System Voltage (Un)	0 - 3 VAC 0 - 5 VDC	3 - 10 VAC 5 - 15 VDC	10 - 21 VAC 15 - 30 VDC	21 - 42 VAC 30 - 60 VDC	100 - 120 VAC 60 - 154 VDC
Max Continuous Operating Voltage (Uc)	5 VAC 7 VDC	12 VAC 18 VDC	23 VAC 33 VDC	45 VAC 64 VDC	150 VAC 170 VDC
Rated Load Current (IL)	800 mA				
Frequency	0.5 MHz	1.0 MHz	2.0 MHz	3.0 MHz	
Loop Resistance	0.6 Ω				
Max Discharge Current (Imax), L+L-PE	20 kA 8/20 μs				
Protection Modes	Common Differentia				
Technology	Gas Discharge Tube	(GDT); Metal Oxide Va	aristor (MOV); Silicon	Avalanche Diode (SAD	)
Voltage Protection Level (Up), L-L	10 V @ 3 kA	25 V @ 3 kA	44 V @ 3 kA	85 V @ 3 kA	220 V @ 3 kA
Connection, Stranded	#18 - #12				
Mounting	35 mm top hat DIN r	ail			
Temperature	-4 to 149°F				
Enclosure Material	UL® 94V-0 Thermopl	astic			
Enclosure Rating	IP 20 NEMA®-1				
Depth (D)	3.35"				
Height (H)	3.54"				
Width (W)	0.47"				
Unit Weight	0.2 lb				
Certification Details	UL® 497B				
Complies With	ANSI®/IEEE® C62.41.	2-2002 Cat A, Cat B, 0	Cat C		
Replacement Module	UTB5DPM	UTB15DPM	UTB30DPM	UTB60DPM	UTB110DPM
Certifications	CE, NOM, UR	CE, UR	CE, NOM, UR	CE, UR	CE, NOM, UR

### Universal Transient Barrier, Dual Pair Single Power







### **Features**

- Compact design universal transient barrier provides protection of low-voltage circuits and transducers
- Separate plug and base design allows hot swappable module replacement
- Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment
- Common-mode and differential-mode protection protects against both possible surge conditions
- Designed for compact protection of signal and power supply in one compact housing





Part Number	UTB30DPS
Nominal System Voltage (Un)	24 - 48 VAC; 12 - 60 VDC
Max Continuous Operating Voltage (Uc)	48 VAC; 60 VDC
Rated Load Current (IL)	5 A
Frequency	0 - 60 Hz
Loop Resistance	0 Ω
Max Discharge Current (Imax), Per Mode	15 kA 8/20 μs
Protection Modes	Common; Differential
Technology	Gas Discharge Tube (GDT) Metal Oxide Varistor (MOV) Silicon Avalanche Diode (SAD)
Voltage Protection Level (Up), L-L	220 V @ 3 kA
Connection, Stranded	#18 - #12
Mounting	35 mm top hat DIN rail
Temperature	-4 to 149°F
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20; NEMA®-1
Depth (D)	3.35"
Height (H)	3.54"
Width (W)	0.47"
Unit Weight	0.2 lb
Certification Details	UL® 497B
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C
Replacement Module	UTB30DPSM

The electrical specifications shown are specific to the power supply (PS) circuit of the product.

### Universal Transient Barrier, Single Pair Isolated Ground







- Compact design universal transient barrier provides protection of low-voltage circuits and transducers
- Separate plug and base design allows hot swappable module replacement
- Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment
- Common-mode and differential-mode protection protects against both possible surge conditions
- $\bullet$  Surge rating to 20 kA 8/20  $\mu s$  is ideal for exposed wiring
- Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space




Part Number	UTB5SPG	UTB15SPG	UTB30SPG	UTB60SPG	UTB110SPG
Nominal System Voltage (Un)	0 - 3 VAC 0 - 5 VDC	3 - 10 VAC 5 - 15 VDC	10 - 21 VAC 15 - 30 VDC	21 - 42 VAC 30 - 60 VDC	100 - 120 VAC 60 - 154 VDC
Max Continuous Operating Voltage (Uc)	5 VAC 7 VDC	12 VAC 18 VDC	23 VAC 33 VDC	45 VAC 64 VDC	150 VAC 170 VDC
Rated Load Current (IL)	2 A				
Frequency	0.5 MHz	1.0 MHz	2.0 MHz	3.0 MHz	
Loop Resistance	1 Ω				
Max Discharge Current (Imax), L+L-PE	20 kA 8/20 μs				
Protection Modes	Common Differential				
Technology	Gas Discharge Tube	(GDT) Metal Oxide Va	ristor (MOV) Silicon Av	valanche Diode (SAD)	
Voltage Protection Level (Up), L-L	10 V @ 3 kA	25 V @ 3 kA	44 V @ 3 kA	85 V @ 3 kA	220 V @ 3 kA
Connection, Stranded	#18 - #12				
Mounting	35 mm top hat DIN rail				
Temperature	-4 to 149°F	-4 to 149°F			
Enclosure Material	UL® 94V-0 Thermopl	JL® 94V-0 Thermoplastic			
Enclosure Rating	IP 20 NEMA®-1	P 20 NEMA®-1			
Depth (D)	2.83"				
Height (H)	3.54"				
Width (W)	0.47"	0.47"			
Unit Weight	0.15 lb	0.15 lb			
Certification Details	UL® 497B				
Complies With	ANSI®/IEEE® C62.41.	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C			
Replacement Module	UTB5SPGM	UTB15SPGM	UTB30SPGM	UTB60SPGM	UTB110SPGM


# Universal Transient Barrier, Modem/Telephone





- General purpose barrier provides protection of low-voltage circuits and transducers
- Separate plug and base design allows hot swappable module replacement
- Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment













		NYCE	
Part Number	UTBSA	UTBTA	
Max Continuous Operating Voltage (Uc)	5 VAC 7 VDC	280 V	
Frequency	15 MHz		
Voltage Protection Level (Up), L-L	340 V @ 3 kA	480 V @ 3 kA	
Rated Load Current (IL)	160 mA		
Loop Resistance	1 Ω		
Max Discharge Current (Imax)	20 kA 8/20 μs L+L-PE	0.5 kA 8/20 μs Per Mode	
Protection Modes	Common, Differential		
Technology	Gas Discharge Tube (GDT), PTC		
Connection, Stranded	#18 - #12	#18 - #12	
Mounting	35 mm top hat DIN rail	35 mm top hat DIN rail	
Temperature	-4 to 149°F		
Enclosure Material	UL® 94V-0 Thermoplastic		
Enclosure Rating	IP 20, NEMA®-1		
Depth (D)	2.68"		
Height (H)	3.54"		
Width (W)	0.7"		
Unit Weight	0.22 lb		
Certification Details	UL® 497B	UL® 497A	
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, C	at C	
Replacement Module	UTBSM	UTBTM	
Certifications	CE; NOM	CE	

### nVent ERICO Protection Device, F-Series







#### **Features**


- Protects sensitive electronic equipment
- Reduced operating and maintenance costs
- Visual indicator
- Open-circuit end-of-life mode
- Proven hybrid technology comprised of gap-type and varistor-type components
- Epoxy coating ensures stability under adverse environmental conditions
- Two operating voltages
- 50 kA 8/20 µs maximum surge rating
- AREMA® binding post terminals
- Exceeds AREMA® recommendations for arrestor applications
- 5-year limited warranty

nVent ERICO is a world leader in grounding, bonding, surge and lightning protection in the railway industry, offering an extensive line of wayside surge protection. The EPD F-Series provides transient protection from surges induced or conducted onto low-voltage signal circuits for trackside signaling equipment. This series of surge-protection devices is ideal for microprocessor-based train-control and indication circuits, train inspection systems, communications systems, highway crossing controls and other operationally sensitive systems. Wayside rail-industry electronicequipment environments are prone to dangerous and damaging voltage surges and transients. The EPD F-Series proven hybrid technology diverts surge currents to minimize the likelihood of

system damage, reducing system down time and repair costs. nVent ERICO's design safeguards the devices against shorts. provides status indication at a glance and ensures uninterrupted signal operation when the device reaches end of life. Visual inspection is a key design feature. The device cover is color-coded and marked with the operating voltage and part number, which allows easy identification for proper application. nVent ERICO is committed to providing engineered high quality and technologically advanced solutions to the unique applications of the railway industry and has served the worldwide market for over 100 years. Railway systems around the world depend on nVent ERICO solutions to keep their systems running safely and efficiently.

Part Number	EPD2050F	EPD2170F	
Nominal System Voltage (Un)	50 VDC; 35 VAC	170 VDC; 120 VAC	
Max Continuous Operating Voltage (Uc)	90 VDC; 65 VAC	220 VDC; 150 VAC	
Voltage Protection Level (Up)	250 V @ 3 kA	500 V @ 3 kA	
Nominal Discharge Current (In)	30 kA 8/20 μs	20 kA 8/20 μs	
Max Discharge Current (Imax)	50 kA 8/20 μs		
Leakage Current @ Un	1 nA Max		
Frequency	5 MHz Max		
Protection Modes	Single, L-L or L-PE		
Technology	Metal Oxide Varistor (MOV); Gas Discharge Tube	(GDT)	
Connection Type	AREMA® Stud-Type Terminals – 2 Post Terminal	Block	
Status Indication	Mechanical flag		
Enclosure Material	UL® 94V-0 Thermoplastic		
Enclosure Rating	IP 20; NEMA®-1		
Humidity	0 – 95 % RH		
Temperature	-40 to 176°F		
Length 1 (L1)	2 %"		
Length 2 (L2)	3"		
Length 3 (L3)	1.3"		
Width 1 (W1)	0.95"		
Width 2 (W2)	0.63"		
Height 1 (H1)	2"		
Height 2 (H2)	2.2"		
Unit Weight	0.15 lb		
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C; AREMA® requirements		
Color	Transparent Blue	Transparent Yellow	

### Electronic Track Signal Protector



The nVent ERICO Electronic Track Signal Protector series provides transient protection from surges induced or conducted onto low-voltage signal circuits for trackside signaling equipment. The series of surge-protection devices is ideal for protecting DC-responsive track relays, train-detection systems, microprocessor-based train-control and indication circuits, train inspection systems, communications systems, highway crossing

#### **Features**


- Includes hybrid technology comprised of gap-type voltage switching and varistor-type voltage clamping components
- Designed with a fail-safe, isolated from ground failure modes as required for critical signal circuits
- Protects sensitive electronic equipment in exposed locations
- Epoxy coating helps ensure stability of operation under adverse conditions and in locations of high humidity
- Exceeds the AREMA® specifications for both arrestor and equalizer applications
- Provides a 50 kA 8/20 maximum surge rating for protection that is suitable for exposed trackside equipment


controls and other operationally sensitive systems. nVent ERICO Electronic Track Signal Protector devices help ensure that surges do not pose a safety threat in the event of component failure. Indicators on the device help safeguard the device against shorts and provide status indication at a glance. The device cover is marked with the operating voltage and part number, which allows easy identification as to proper application.


Part Number	ETSP330170
Nominal System Voltage (Un)	170 VDC; 120 VAC
Max Continuous Operating Voltage (Uc)	220 VDC; 150 VAC
Voltage Protection Level (Up)	550 V @ 3 kA
Nominal Discharge Current (In)	20 kA 8/20 µs L+L-PE
Max Discharge Current (Imax)	50 kA 8/20 μs L+L-PE
Leakage Current @ Un	1 nA Max
Frequency	5 MHz Max
Protection Modes	Two Mode, L1-PE and L2-PE
Technology	Metal Oxide Varistor (MOV); Gas Discharge Tube (GDT)
Connection Type	AREMA® Stud-Type Terminals – 2 Post Terminal Block
Status Indication	Dual spring thermal disconnect
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20; NEMA®-1
Humidity	0 – 90 % RH
Temperature	-40 to 176°F
Depth (D)	0.98"
Height (H)	2.96"
Width (W)	2.16"
Unit Weight	0.24 lb
Complies With	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C; IEC® 61643-1 Class II; AREMA® requirements
Color	Yellow

Frequency @ 3 dB / 120  $\Omega$ .

### **RTBN Rail Transient Barrier**








- · Surge module easily snaps into place
- Mechanical flag will protrude to indicate the module needs to be replaced
- Thermal disconnect releases the indicator when the device reaches end-of-life, disconnecting itself from the circuit to prevent it from becoming a short or shunt
- · Surge module attaches to the base with a latching mechanism that easily locks the device into place, preventing the module from disconnecting during
- Integration of GDT (gas discharge tube) technology and MOV (metal oxide varistors), a combination that delivers consistency and the capability to protect against fast spikes
- Screw-less cage clamp terminal allows for easy connection, solid or stranded wires are simply pushed in to lock into place, reducing installation time by as much as 75%
- DIN rail grounding connection eliminates the need for extra grounding wires

Part Number	RTB12N	RTB30N	RTB50N	RTB130N
Nominal System Voltage (Un)	12 VDC; 9 VAC	30 VDC; 21 VAC	50 VDC; 35 VAC	130 VDC; 110 VAC
Max Continuous Operating Voltage (Uc)	18 VDC; 12 VAC	33 VDC; 23 VAC	65 VDC; 50 VAC	170 VDC; 130 VAC
Max Discharge Current (Imax)	40 kA 8/20 μs			
Rated Load Current (IL)	15 A			
Voltage Protection Rating (VPR)	65 V @ 3 kA L-L 245 V @ 3 kA L+L-PE	105 V @ 3 kA L-L 245 V @ 3 kA L+L-PE	230 V @ 3 kA L-L 245 V @ 3 kA L+L-PE	530 V @ 3 kA L-L 495 V @ 3 kA L+L-PE
Loop Resistance	900 μΩ			
Mounting	35 mm top hat DIN rail;	G type DIN rail		
Protection Modes	L-L; L+L-PE			
Status Indication	Mechanical flag; Remot	Mechanical flag; Remote Contacts		
Connection, Solid	#18 - #12	#18 - #12		
Connection, Stranded	#18 - #12	#18 - #12		
Enclosure Material	UL® 94V-0 Thermoplast	UL® 94V-0 Thermoplastic		
Enclosure Rating	IP 20	IP 20		
Temperature	-40 to 185°F	−40 to 185°F		
Depth (D)	4.22"	4.22"		
Height (H)	4.33"			
Width (W)	0.71"	0.71"		
Unit Weight	0.22 lb	0.22 lb		
Complies With	AREMA® C&S Manual P	AREMA® C&S Manual Parts 11.5.1, 11.3.2, 14.1.2; ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C		
Color	Red	Black	Purple	Yellow
Replacement Module	RTBN12M	RTBN30M	RTBN50M	RTBN130M

### Remote Transmitter Protector








- Three stage protection and fine over-voltage protection helps ensure lowest residual surge voltage reaches sensitive equipment
- Flexible installation allows enclosure to be installed "dead ended", "T" configured or in-line
- Optimized for protection of 2-wire industrial 4-20 mA loops and suitable for exposed locations
- Supports line currents up to 145 mA and protects 24 VDC powered equipment



Part Number	RTP3034
Nominal System Voltage (Un)	21 VAC 30 VDC
Max Continuous Operating Voltage (Uc)	23 VAC 33 VDC
Voltage Protection Level (Up), L-L	44 V @ 3 kA
Max Discharge Current (Imax), L+L-PE	20 kA 8/20 μs
Rated Load Current (IL)	145 mA
Loop Resistance	14 Ω
Protection Modes	Common Differential
Technology	Gas Discharge Tube (GDT); Metal Oxide Varistor (MOV); Silicon Avalanche Diode (SAD)
Enclosure Material	Stainless Steel
Enclosure Rating	IP 55
Temperature	−40 to 149°F
Thread Size (TS)	3/4 NPT
Diameter (Ø)	1.38"
Height (H)	5"
Designed to Meet	ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C
Certifications	CE; Qualifoudre
Standard Packaging Quantity	1 pc
UPC	78285652666
EAN-13	8711893027549


### **Load Cell Protector**





### **Features**

- Six wires and shield protection works with four or six wire systems
- Suitable for compression or tension cells
- Low series impedance, loadcells do not need recalibration
- NEMA®-12 (IP-55) rated, suitable for outdoor use
- · Helps protect against excitation overvoltage and prevent loadcell damage






	NERIS 1023116012083
Part Number	LCP01A
Max Discharge Current (Imax), Shield to Ground	10 kA 8/20 μs
Max Discharge Current (Imax), Signal to Shield	0.3 kA 8/20 μs
Voltage Protection Level (Up), Shield to Ground	90 V
Voltage Protection Level (Up), Signal to Shield	30 V
Voltage Protection Level (Up), Signal to Signal	15 V
Loop Resistance	0.3 Ω
Technology	Silicon Avalanche Diode (SAD)
Material	Acrylonitrile Butadiene Styrene
Enclosure Rating	NEMA® 12 (IP55)
Depth (D)	4.33"
Height (H)	2.2"
Width (W)	2.95"
Unit Weight	0.55 lb
Temperature	-40 to 176°F
Certifications	Qualifoudre
Standard Packaging Quantity	1 pc
UPC	78285644014
EAN-13	9321098000804

NEMA is a registered service mark of National Electrical Manufacturers Association.

# Surge Counter, Digital Display






- Records time and date of transient surge events
- Resettable counter
- Snap on, hall effect transducer

Part Number	DSCL2
Trip Threshold	100 A 8/20 μs
Status Indication	LED
Connection, Stranded	2/0 Max
Lead Length	20"
Enclosure Material	UL® 94V-0 Thermoplastic
Enclosure Rating	IP 20 NEMA®-1
Mounting	35 mm top hat DIN rail
Temperature	-4 to 158°F
Module Width	2 M
Depth (D)	2.68"
Height (H)	3.54"
Width (W)	1.42"
Unit Weight	0.42 lb
Standard Packaging Quantity	1 pc
UPC	78285680444
EAN-13	8711893146950

# Potential Equalization Clamp





### **Features**

- · High peak current capability provides long service life
- Weatherproof enclosure is suitable for direct burial
- The PEC100 is ATEX approved and suitable for use in potentially explosive atmospheres










	(Ex) C E GUAITOUCE
Part Number	PEC100
Spark-Over Voltage @ 100 V/s	350 V
Max Discharge Current (Imax)	100 kA 8/20 µs
Technology	Gas Discharge Tube (GDT)
Insulation Resistance	1 GΩ Min
Capacitance	15 pF Max
Voltage Protection Level (Up)	800 V @ 1,000 V/µs
Impulse Current (limp)	25 kA 10/350 μs
Lead Length	17"
Lead Size	#5
Enclosure Rating	IP 66; IP 67
Temperature	−22 to 158°F
Diameter 1 (Ø1)	1.1"
Diameter 2 (Ø2)	0.64"
Length (L)	37 ½"
Unit Weight	1.1 lb
Complies With	IEC® 61643-1 Class I, Class II IEC® 62561-3
Certifications	ATEX Baseefa13ATEX0113X CE; IECEx BAS 13.0065X; Qualifoudre
EAN-13	9321098000804
Standard Packaging Quantity	1 pc
UPC	78285656478
EAN-13	8711893027570

Spark-over voltage has a tolerance of +/- 20%.
IEC is a registered trademark of the International Electrotechnical Commission.

### MOV/GDT/SAD Tester MGATESTER1





### **Features**

- Measurement of metal oxide varistors, gas discharge tubes, and avalanche diodes
- · Ability to display up to 50 measurements
- Adjustable test settings
- Rechargeable battery

nVent ERICO testers are designed for rapid testing of the integrity of surge protection device components. Because standard metal oxide varistors, gas arresters, and avalanche diodes do not provide the user with a visual indication of the integrity of the protection capacity, an external means of testing is required. It is impossible to predict when these failures will occur without some form of testing. As MOVs approach the end

of their life cycle, they exhibit a change in tolerance levels. nVent ERICO testing products are specifically designed to identify these situations and allow the operator to effect remedial replacement to the devices which are nearing the end of their life cycle. They can test both components, as well as replacement modules such as the TDS or DSD

Part Number	MGATESTER1
Test Voltage	1,500 VDC Max
GDT Voltage Ramp	100 V/s 1,000 V/s
MOV/SAD Test Current	0.1 mA 0.5 mA 1.0 mA
Enclosure Rating	IP 20
Temperature	14 – 122°F
Depth (D)	3.23"
Height (H)	8.07"
Width (W)	8.66"
Unit Weight	2.09 lb
Standard Packaging Quantity	1 pc
UPC	78285691000

### Glossary of Terminology

### 8/20 us CURRENT WAVESHAPE

A current impulse with a virtual front time of 8µs and a time to half-value of 20 us.

#### AGGREGATE SURGE RATING

The sum of the surge ratings of individual voltage limiting components, connected in parallel, in the device.

Note: This figure does not indicate the maximum discharge current (Imax) of the device. It does however provide an indication of the expected SPD life. Users should be aware that certain manufacturers may incorrectly claim the aggregate surge rating of MOV material used in their device as its Imax. Non-perfect current sharing between parallel MOVs, and the inability of series over-current or thermal disconnects to carry the full surge current, generally means that the maximum discharge current which the SPD can withstand is less than its aggregate surge rating.

#### **ATTENUATION**

The ability of an SPD to reduce electrical noise interference, measured in decibels. Attenuation varies with frequency, so it is usual to specify the attenuation of the SPD at a particular frequency; commonly 100kHz.

#### **BACKUP OVERCURRENT PROTECTION**

An external overcurrent protective device installed prior to the SPD. Such a device may be required if the overcurrent limiting device on the service is larger than that required by the SPD or connecting wiring.

#### Class I test

SPD tested with maximum impulse current (Imp) and nominal discharge current (In).

### Class II test

SPD tested with maximum discharge current (Imax) and nominal discharge current (In).

#### Class III test

SPD tested with combination wave.

### **DISTRIBUTION SYSTEM**

Defines the electrical power distribution system. The distribution system is usually described by configuration of the phases, neutral and ground conductor configuration on the secondary side of the supply transformer. Refer to pages 10-12 for further information.

### FOLLOW CURRENT (IF)

The current supplied by the electrical power distribution system which flows through the SPD after a discharge current impulse. The follow current is significantly higher than the operating current, and is normally high for voltage switching type SPDs (e.g. spark gaps) since the arc voltage falls below the AC supply voltage after firing.

### IMPULSE CURRENT (IMP)

Peak impulse current withstand with a 10/350 µs current waveshape. This is often used for the classification of SPDs tested to Test Class I, but is not the only acceptable waveshape.

### **INSERTION LOSS**

The insertion loss of an SPD is usually only stated for two port devices for use on low voltage data systems. It is a measure of the ratio of voltage at the output to the input at the device under test. The insertion loss is usually stated for a given frequency and measured in decibels.

#### LEAKAGE CURRENT

The current flowing to the ground conductor when the SPD is connected to the nominal supply voltage Un.

### **LET-THROUGH VOLTAGE**

Another term often used to describe the measured limiting voltage.

Note: This measurement may be carried out with, or without, the presence of the nominal AC power (Un) being applied to the SPD. As such, the results may be different and the user should take cognizance of this in making any comparative assessments

#### **LOCATION CATEGORIES**

Various standards attempt to define the electrical environment at which an SPD may be installed, into location categories or zones.

Note: The user should be aware that international consensus has not been reached on these classifications, nor on the size of expected surge activity, which may occur. Further, the user should note that the demarcation of these zones do not form literal boundaries, but are rather a gradual transition.

### MAXIMUM CONTINUOUS OPERATING **VOLTAGE (Uc)**

The maximum r.m.s. or d.c. voltage which may be continuously applied to the SPD's mode of protection without degradation or inhibiting its correct operation.

Note: Specifications given in the catalog generally are phase (L-N) voltages.

### MAXIMUM DISCHARGE CURRENT (IMAX)

The maximum single shot current, having an 8/20 µs waveshape, which the SPD can safely divert.

#### MEASURED LIMITING VOLTAGE

The maximum voltage measured across the SPD's terminals during the application of an impulse of specified waveshape and amplitude.

### MODES OF PROTECTION

SPDs may provide protection line-to-ground, line-to-neutral, neutral-toground or in combinations thereof. These paths are referred to as the modes of protection.

Note: The user is advised that not all modes require protection, and more is not necessarily better when selecting an SPD. As an example, the N-G mode is not required when the SPD is installed at the primary service entrance of a TN-C-S electrical distribution system, due to the Neutral-Ground bond at this point. The L-L mode is generally not provided for systems with neutral conductors since the L-N modes also protect the L-L modes. Similarly, the L-G mode can be protected via the L-N and N-G modes.

#### NOMINAL DISCHARGE CURRENT (IN)

The peak value of the current flowing through the SPD during the application an 8/20 µs waveshape.

Note: IEC 61643-1 requires SPDs tested to Test Class II, to withstand 15 impulses at In followed by 0.1, 0.25, 0.5, 0.75 and 1.0 times Imax,

### NOMINAL (SYSTEM) VOLTAGE (UN)

The L-N voltage by which an electrical power system is designated. Under normal system conditions, the voltage at the supply terminals may differ from the nominal voltage as determined by the tolerance of the supply system (normally +/- 10%).

### Glossary of Terminology

#### **ONE-PORT SPD**

An SPD connected in shunt (parallel) with the circuit to be protected. A one port device may have separate input and output terminals, but without a specific series impedance between these terminals. This type of connection is also known as a Kelvin connection. Operating Current

The current drawn (per phase) by the SPD when energized at the nominal operating voltage  $U_n$ .

Note: For SPDs with integral series filtering, the total current drawn may be greater than the real rms current consumption (i.e. VA may be greater than Watts). This is due to the presence of the internal filtering capacitance.

#### **OVER-CURRENT PROTECTION**

An over-current device, such as a fuse or circuit-breaker, which could be part of the electrical distribution system located externally and upstream of the SPD. May provide protection to the SPD, the connecting wiring and provide a means of externally isolating the SPD.

### PROTECTIVE EARTH (PE)

The IEC® 60364 series characterizes low-voltage distribution systems by their grounding methods and the configuration of the neutral and protective conductors. The Protective Earth is commonly referred to as "ground", or "earth", in many regions.

### RATED LOAD CURRENT (IL)

Maximum continuous rated current that can be supplied to a load connected to the protected output of an SPD. Normally only stated for two port, series connected, SPDs.

#### **RESIDUAL VOLTAGE**

In IEC terminology this refers to the peak value of the voltage that appears between the terminals of an SPD due to the passage of discharge current In. NZS/AS 1768 refers to this as the let-through voltage, a measurement obtained when the stated test impulse is superimposed on top of the nominal system voltage Un.

### **SECONDARY SURGE ARRESTER**

A loosely used term given to SPDs intended for operation on medium voltage systems (>1kV). Within the USA, a secondary surge arrester defines an SPD Listed by Underwriters Laboratories Inc. for use on LV and MV systems at locations prior to the main overcurrent disconnect to the facility.

Note: Secondary Surge Arrester Listing is generally considered to have less demanding safety requirements than those for UL® 1449 Transient Voltage Surge Arrester Listing.

### SHORT CIRCUIT CURRENT RATING (SCCR)

The short-circuit current rating of the SPD. Required by USA National Electric Code (NEC $^{\circ}$ ) for TVSS devices.

### **SPD DISCONNECTOR**

An IEC term used to describe a device (internal and/or external) for disconnecting an SPD from the electrical power system.

Note: This disconnecting device is not required to have isolating capability. It is to prevent a persistent fault on the system and is used to give an indication of the SPD failure. There may be more than one disconnector function, for example an over-current protection function and a thermal protection function. These functions may be integrated into one unit or performed in separate units.

#### **SPARK-OVER VOLTAGE**

The voltage at which a switching type SPD (generally of the spark gap type) will initiate conduction. This value is normally specified for a voltage increasing at 1kV/s.

#### STATUS INDICATOR

A device(s) that indicates the operational status of the SPD, or of a particular mode of its protection.

Note: Such indicators may be local with visual and/or audible alarms and/or may have remote signaling and/or output contact capability.

#### SUPPRESSED VOLTAGE RATING (SVR)

A special case of the measured limiting voltage specific to the UL 1449 Listing of an SPD.

Note: This test is performed using a small 500 A 8/20  $\mu$ s current limited impulse, and the clamping voltage recorded at the ends of 6" connecting leads. The result obtained is rounded up to the nearest value given in a table.

### SURGE PROTECTION DEVICE (SPD)

An IEC term used to describe a device intended to limit transient overvoltages and divert surge currents. It contains at least one non-linear component.

### **SURGE (REDUCTION) FILTER**

A two-port series filtering type of SPD specifically designed to reduce the rate-of-rise of voltage (dv/dt) of the pre-clamped waveform. Such a device normally contains a filter with low-pass performance.

#### TWO-PORT SPD

An SPD with two sets of terminals, input and output (line and equipment), and with a specific impedance inserted between these terminals. These are often referred to as series (in-line) connected SPDs and generally contain wave-shaping filters in addition to simple shunt-only protection.


### **VOLTAGE PROTECTION LEVEL (UP)**


Similar to the measured limiting voltage, the voltage protection level characterizes the performance of an SPD in limiting the voltage across its terminals.


Note: The voltage protection level is the measured limiting voltage recorded under a specified current magnitude and waveshape, and rounded up to the next highest voltage selected from a list of preferred values found in IEC 61643-1 Standard for surge protective devices connected to low-voltage power distribution systems. For SPDs tested to Test Class I, Up is generally stated using a 10/350 Imp and for SPDs tested to Test Class II, using an 8/20 µs Imax.

### **VOLTAGE PROTECTION RATING (VPR)**

A rating selected from a list of preferred values as given in Table 63.1 of ANSI $^{\circ}$ /UL 1449 and assigned to each mode of protection. The value of the VPR is determined as the nearest highest value taken from Table 63.1 to the measured limiting voltage determined during the transient-voltage surge suppression test using the combination wave generator at a setting of 6 kV, 3 kA.









Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER



nVent.com/ERICO